







GENERAL TOLERANCE										USED ON
10 MAX	30 MAX	50 MAX	70 MAX	100 MAX	120 MAX	250 MAX	250 OVR	ANGLE	ECCENT	
±0.15	±0.20	±0.30	±0.40	±0.50	±0.75	±0.90	±1.4	±0.5°	0.1	



- NOTES:
1. MATERIALS : POLYESTER (PBT), GLASS FILLED,UL 94V-0
 2. MATES WITH : 502352, 560020 SERIES
 3. APPLICABLE TERMINAL : 560124-0101, 560124-0131
 4. APPLICABLE ISL : 560125-0300, 560125-0301
 5. GENERAL TOLERANCES : SEE TABLE
 6. ELV AND RoHS COMPLIANT
 7. PRODUCT SPECIFICATION : PS-560123-001
 8. PACKING SPECIFICATION : PK-560123-001

ORDER NO.	MATERIAL NO.	COLOR
560123-0300	5601230300	WHITE
560123-0301	5601230301	BLACK
560123-0302	5601230302	RED
560123-0304	5601230304	BLUE

ADDED OPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION	
EC NO: KTR2016-0056		▼=0		mm INCH		DRAWN BY DATE		TITLE		NEW 2.0 PITCH W/B CONN.		REC. 3WAY HSG	
DRWNS:JLEE06		▽=0		4 PLACES ± --- ± ---		YIBA EK 2014/07/08		2 PLACES ± --- ± ---		DURACLIK™ ISL SERIES		MOLEX INCORPORATED	
2016/02/23				3 PLACES ± --- ± ---		CHECKED BY DATE		2 PLACES ± --- ± ---					
CHYKB:BCY00N				2 PLACES ± --- ± ---		BCY00N 2014/07/08		APPROVED BY DATE					
2016/02/23				1 PLACE ± --- ± ---		SRTAK 2014/08/26		MOLEX					
APPR: JYCH01				ANGULAR ± ---°		MATERIAL NO.		DOCUMENT NO.				SHEET NO.	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-560123-003				1 OF 1	
REV						SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					