




REVISIONS			
ISS	ZONE	DESCRIPTION\PER REQUEST\DATE	
A1	A-2	No.2 WAS CHANGED\N/A\09-28-04'	



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER QQ-B-626
2. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
3. BERYLLIUM COPPER PER QQ-C-530
4. GOLD PL. 30 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER NICKEL STRIKE
5. TEFLON MIL-P-19468

						DIMENSIONS ARE IN MILLIMETERS				PART NO.		Amphenol Danbury,CT,USA-Tainan,Taiwan-Shenzhen,China			
						UNLESS OTHERWISE SPECIFIED TOLERANCES				APPROVED				DATE	
						0.5-6 = ±0.2				<i>Loe</i>				<i>09-28-04</i>	
						6-30 = ±0.4				CHECKED				DATE	
						30-120 = ±0.6				<i>Chenley</i>				<i>09-28-04</i>	
						120-315 = ±1				DRAWN		DATE			
						315-1000 = ±1.6				<i>Derrill</i>		<i>09-28-04</i>			
						1000-2000 = ±2.4				FILE NO. F:		DWG\MCX\6251B1\014\50\3GT30GA1SZ			
3	CONTACT PIN	NOTE 3	NOTE 4	1	CP08AAF10A	SCALE	6/1	ISSUE	A1				TITLE		
2	INSULATOR	NOTE 5	NATURAL	1	MCX6251B1-2T-50-B							MCX P.C. BOARD RECEPT. JACK			
1	BODY	NOTE 1	NOTE 2	1	BD08AAG05A							DRAWING NO.			
												MCX6251B1-014-3GT30G-50			
												ITEM NO.			
												086251AAZ02GE5F			