



4		3		2		1	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		-		-	
© COPYRIGHT		BY TYCO ELECTRONICS CORPORATION.		ALL RIGHTS RESERVED.			
HOUSING MOUNTING NUT LOCKWASHER		STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303		PASSIVATE PER ASTM-A-380			
DIELECTRIC		PTFE FLUOROCARBON PER ASTM-D-1457		N/A			
CENTER CONTACT		BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H		GOLD PLATE PER ASTM-B-488			
COMPONENT		MATERIAL		FINISH			

LOC	DIST	REVISIONS					
DF	X0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REV PER ECO 08-028827	24NOV08	PK	DW



ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 310.2	TEMPERATURE RATING +125°C
Frequency Range (GHz) DC to 18 GHz	Recommended Mating Torque 7-10	Vibration MIL-STD-202, Method 204, Condition A
Volt Rating (VRMS MAX) @ Sea Level 335	Mating Characteristics:	Shock MIL-STD-202, Method 213, Condition I
VSWR 1.05 + .008X FGHz	Insertion (MAX Oz) 48	Thermal Shock MIL-STD-202, Method 107, Condition A, Except High Temp
Insertion Loss (dB MAX) .15 √ F(GHz)	Withdrawal (MIN Oz) 4	Moisture Resistance MIL-STD-202, Method 106
RF Leakage (dB MIN) -90 @ 2-3 GHz	Force to Engage and Disengage (In-Lbs MAX) 2	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray
Corona, 70,000 Ft (VRMS MIN)	Center Contact Captivation	
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000	Axial (Lbs) 6.0	
Contact Resistance (Milliohms MAX)	Radial (In-Oz) 4.0	
Center Contact 12.0	Cable Retention	
Outer Contact 4.0	Axial Force (Lbs) N/A	
Cable to Housing N/A	Torque (In-Oz) N/A	
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670	Weight (Grams) TBD	
I.R.(Megohms MIN) 5000		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 8-5-07	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES [mm]		CHK D.WILSON 8-5-07				
		APVD D.WILSON 8-5-07				
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	NAME SMA BULKHEAD FEEDTHRU JACK TO JACK ADAPTER WITH CAPTURED CENTER CONTACT			
0 PLC ± -		—	SIZE A2	CAGE CODE 00779	DRAWING NO C-1883077	RESTRICTED TO —
1 PLC ± -		—				
2 PLC ± -		—				
3 PLC ± .005 [0.13]		—				
4 PLC ± -		—				
ANGLES ± -		—				
FINISH		—				
MATERIAL SEE CALLOUTS		WEIGHT —				
SEE CALLOUTS		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 of 1	REV B	