

**Surface Mount Quadrature Hybrid,
200 - 400 MHz**

Rev. V3

Features


- Fully Hermetic
- Octave Bandwidth
- Low VSWR: 1.1:1 Typical
- Impedance: 50 Ohms Nominal
- Input Power: 5 Watts Max @ +25°C, Derated to 1 Watt @ +85°C
- Typical Phase Linearity: 3° from straight line
- MIL-STD-202 Screening Available

Description

3 dB Hybrids are ideal for dividing a signal into two signals of equal amplitude and a constant 90° or 180° phase differential and for Quadrature combining or performing summation/differential combining.

Phasing Diagram

IN \ OUT	A	B	C	D
A	ISO	-90°	0°	
B	ISO	0°	-90°	
C	-90°	0°	ISO	
D	0°	-90°	ISO	

SF-1


Dimensions in mm are in mm
Unless Otherwise Noted: $\text{XXX} \pm 0.010$
 $\text{XX} \pm 0.02$
WEIGHT (APPROX) 0.07 OUNCES 2 GRAMS

Pin Configuration

Pin No.	Function	Pin No.	Function
1	A	3	D
2	B	4	C

Electrical Specifications¹: $T_A = -55^\circ\text{C}$ to $+85^\circ\text{C}$

Parameter	Test Conditions	Frequency	Units	Min	Typ	Max
Insertion Loss ²	Less Coupling	200–400 MHz	dB	—	—	0.5
Isolation	—	200–400 MHz	dB	18	—	—
Amplitude Balance	—	200–400 MHz	dB	—	—	1.0
VSWR	—	200–400 MHz	Ratio	—	—	1.3:1
Deviation from Quadrature	—	200–400 MHz	°	—	—	4

1. All specifications apply with 50 ohm source and load impedance.

2. Average of coupled output less 3 dB.

This product contains elements protected by United States Patent Number 3,484,724.

ADVANCED: Data Sheets contain information regarding a product M/A-COM Technology Solutions is considering for development. Performance is based on target specifications, simulated results, and/or prototype measurements. Commitment to develop is not guaranteed.


PRELIMINARY: Data Sheets contain information regarding a product M/A-COM Technology Solutions has under development. Performance is based on engineering tests. Specifications are typical. Mechanical outline has been fixed. Engineering samples and/or test data may be available. Commitment to produce in volume is not guaranteed.

• **North America** Tel: 800.366.2266 • **Europe** Tel: +353.21.244.6400
• **India** Tel: +91.80.4155721 • **China** Tel: +86.21.2407.1588



Visit www.macomtech.com for additional data sheets and product information.

M/A-COM Technology Solutions Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Typical Performance Curves



Deviation from Quadrature



Ordering Information

Part Number	Package
JHS-142 PIN	SF-1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MACOM:](#)

[JHS-142-PIN](#)