


DO NOT SCALE

DIMENSIONS IN mm


METRIC

THIRD ANGLE
PROJECTION



NOTES:

- 1 FOR MINI-APPLICATOR-CRIMPING.
2 UNDERCOATING:1,25µm Ni,SELECTIVE:0,8µm Au,
ZONE 1: 0,5µm MIN. GOLDFLASH.
3 UNDERCOATING:1,25µm Ni,SELECTIVE:0,8µm Au,
REMAINDER:GOLDFLASH.
4 UNDERCOATING:1,25µm Ni,SELECTIVE:0,4µm Au, NO GOLDFLASH.
5 UNDERCOATING:1,25µm Ni,SELECTIVE:2,0µm Au,
REMAINDER:GOLDFLASH.
6 PRE-TINPLATED:2,0µm.
7 ZONE 1:BRIGHT TIN/LEAD PLATED.
8 MATERIAL:PHOSPHORBRONZE
9 FOR STANDARD-APPLICATOR-CRIMPING.
10 FOR REELFED-HANDTOOL-CRIMPING, 500 CONTACTS ON A SMALL REEL.
11 24-20 AWG (0,20-0,56 mm²) WITH .055 CRIMPER.
26 AWG (0,12-0,14 mm²) WITH .042 CRIMPER.
12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



WIRE RANGE
11
INSUL.RANGE
1,4 MAX.DIA.

GOLD	2	1-141708-2	5-167301-4	12	10
TIN	6	1-141708-1	5-167301-2	12	10
GOLD	5	≠	2-167301-6	12	1
			2-167301-5	9	
GOLD	2	1-141708-2	2-167301-4	1	
			2-167301-3	12	9
TIN	6	1-141708-1	2-167301-2	1	
			2-167301-1	9	
GOLD	4	7	≠	1-167301-6	1
				1-167301-5	9
GOLD	3	141708-1	167301-4	1	
			167301-3	9	

				FINISH		LOOSE PIECE		PARTNUMBER			
						CUSTOMER DRAWING			FOR REFERENCE ONLY WILL NOT BE UPDATED		
						© COPYRIGHT — BY					
						ALL INTERNATIONAL RIGHTS RESERVED.					
						THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION — ,19 —					
						TE Connectivity					
						NAME					
J2	REVISED PER ECO-11-005294			RK	HMR	13APR11	AMPMODU MOD.4 RECEPTACLE,S.C.P. STRIP				
LTR.		REVISION RECORD		DR.	CHK.	DATE					
DR.: R.VISSER		CHK.: J.v.LIEMPT		APP.: L.v.SOEST		DWG.No.		REV.LTR.		SHEET	
DATE: 11-11-87		DATE: -		DATE: -		C-167301		J2		1 OF 1	A3