

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	60		C1	REVISED PER ECO-11-004917	11MAR11	RK	HMR

- 1


ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL: 2.54μm [.000100] MINIMUM TIN PLATED COPPER ALLOY, 0.74-0.79 [.030±.001] THICK.
3.

WIRE BARREL ACCEPTS ONE 10 OR 12 AWG STRANDED COPPER WIRE.
- 4

CONTACTS ON REEL SHALL BE CRIMPED USING APPLICATOR TOOL 567256.
- 5

LOOSE PIECE CONTACTS SHALL BE CRIMPED USING TOOLS AND DIE SETS LISTED BELOW.
HAND TOOL: AMP PART NO. 69710
PNEUMATIC TOOL: AMP PART NO. 69365
DIE SET 10 AWG: AMP PART NO. 58491-1
DIE SET 12 AWG: AMP PART NO. 58490-1



2000/REEL		4	556880-2	
LOOSE PIECE 200/BOX		5	556880-1	
DESCRIPTION			PART NO	
DWN D. STRAUSSER		5-30-91	TE TE Connectivity	
CHK B. FOX		8-23-91		
APVD M. MILLER		8-26-91		
PRODUCT SPEC				
APPLICATION SPEC			CONTACT, DUAL BEAM, 10-12 AWG, WTB, AMPINNERGY TM	
114-6044			SIZE	RESTRICTED TO
WEIGHT			CAGE CODE	
CUSTOMER DRAWING			DRAWING NO	
			SCALE	
			SHEET	
			REV	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1
	1 PLC ± - 2
	2 PLC ± - 3
	3 PLC ± - 4
	4 PLC ± - ANGLES ± -
MATERIAL	FINISH
2	2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[556880-1](#) [556880-2](#)