

PROGRAMMABLE OSCILLATORS (SMD • Ceramic Package)

RoHS compliant

CSX-750P SERIES


2000pcs/reel




FEATURES

- Wide range of output frequency by PLL technology.
- Quick sample delivery and short lead time in mass production.
- Low current consumption with output enable function (OE) or stand by function (STAND-BY).
- Suitable for various applications such as communication devices, AV devices and measuring instruments.

DIMENSION [mm]



SOLDER PAD LAYOUT [mm]



STANDARD SPECIFICATIONS * Model is determined by the selection for the output enable or stand-by function, the frequency stability and the supply voltage.

Item	Model	OE	CSX-750 PT (＊)	CSX-750 PC (＊)	CSX-750 PB (＊)
		STAND-BY	CSX-750 PK (＊)	CSX-750 PD (＊)	CSX-750 PJ (＊)
Frequency Range			1.000MHz ～ 125.000MHz		1.000MHz～100.000MHz
Supply Voltage			Vdd : 5.0V±0.5V		Vdd : 3.3V±0.3V
Frequency Stability (＊)			B : ±50ppm, C : ±100ppm, E : ±50ppm (－ 40℃～+ 85℃) , F : ±100ppm (－ 40℃～+ 85℃)		
Operating Temperature Range			－20℃～+70℃ (－40℃～+85℃)		
Storage Temperature Range			－55℃～+125℃		
Current consumption			45mA Max.		25mA Max.
Duty	TTL level (1.4V)		45～55%	—	
	CMOS level (1/2 Vdd)		—	45～55%	
Output Voltage	V _{OH}		0.9Vdd Min.		
	V _{OL}		0.4V Max.		0.1Vdd Max.
Output Load	TTL		5TTL Max.	—	
	CMOS		—	25pF Max.	15pF Max.
Rise and Fall Time			4 nsec Max.		
Start-up time			10 msec Max.		
Input Voltage	V _{IH}		2.0V Min.		0.7Vdd Min.
	V _{IL}		0.8V Max.		0.2Vdd Max.
Disable current			30mA Max.		15mA Max.
Stand-by current			50 μA Max.		20 μA Max.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Citizen:

[CSX750PTF-50.4-UB](#) [CSX750PBB-32.000M-UT](#) [CSX750PBF-10.949M-UB](#) [CSX750PBC-100.00-UB](#) [CSX750PBB-50.100M](#) [CSX750PCC7.3728M-UT](#) [CSX-750PBC-4.9152M-U](#) [CSX750PBF-8.000M-UB](#) [CSX750PBC-100.0-UB](#) [CSX750PBC-58.9824-UB](#) [CSX-750PBC-25MHZ](#) [CSX750PBF100.000M-UT](#) [CSX750PBC7.3728M-UT](#) [CSX750PBF-1.024MHz](#)