

MJD128T4 (PNP)

Preferred Device

Complementary Darlington Power Transistor

DPAK For Surface Mount Applications

Designed for general purpose amplifier and low speed switching applications.

- Monolithic Construction With Built-in Base-Emitter Shunt Resistors
- High DC Current Gain –
 $h_{FE} = 2500$ (Typ) @ $I_C = 4.0$ Adc
- Epoxy Meets UL 94, V-0 @ 0.125 in.
- ESD Ratings: Human Body Model, 3B > 8000 V
Machine Model, C > 400 V

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector-Emitter Voltage	V_{CEO}	120	Vdc
Collector-Base Voltage	V_{CB}	120	Vdc
Emitter-Base Voltage	V_{EB}	5	Vdc
Collector Current – Continuous Peak	I_C	8 16	Adc
Base Current	I_B	120	mAdc
Total Power Dissipation @ $T_C = 25^\circ\text{C}$ Derate above 25°C	P_D	20 0.16	W W/ $^\circ\text{C}$
Total Power Dissipation* @ $T_A = 25^\circ\text{C}$ Derate above 25°C	P_D	1.75 0.014	W W/ $^\circ\text{C}$
Operating and Storage Junction Temperature Range	T_J, T_{stg}	-65 to +150	$^\circ\text{C}$

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	6.25	$^\circ\text{C}/\text{W}$
Thermal Resistance, Junction-to-Ambient*	$R_{\theta JA}$	71.4	$^\circ\text{C}/\text{W}$

*These ratings are applicable when surface mounted on the minimum pad sizes recommended.




ON Semiconductor®

<http://onsemi.com>

SILICON
POWER TRANSISTOR
8 AMPERES
120 VOLTS
20 WATTS

MARKING DIAGRAM



Y = Year
WW = Work Week
J128 = Device Code

ORDERING INFORMATION

Device	Package	Shipping
MJD128T4	DPAK	2500/Tape & Reel

Preferred devices are recommended choices for future use and best overall value.

MJD128T4 (PNP)

ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS				
Collector–Emitter Sustaining Voltage ($I_C = 30 \text{ mA}_{\text{dc}}, I_B = 0$)	$V_{\text{CEO(sus)}}$	120	–	V _{dc}
Collector Cutoff Current ($V_{\text{CE}} = 120 \text{ Vdc}, I_B = 0$)	I_{CEO}	–	5	mA
Collector Cutoff Current ($V_{\text{CB}} = 100 \text{ Vdc}, I_E = 0$)	I_{CBO}	–	10	μA_{dc}
Emitter Cutoff Current ($V_{\text{BE}} = 5 \text{ Vdc}, I_C = 0$)	I_{EBO}	–	2	mA_{dc}
ON CHARACTERISTICS				
DC Current Gain ($I_C = 4 \text{ Adc}, V_{\text{CE}} = 4 \text{ Vdc}$) ($I_C = 8 \text{ Adc}, V_{\text{CE}} = 4 \text{ Vdc}$)	h_{FE}	1000 100	12,000 –	–
Collector–Emitter Saturation Voltage ($I_C = 4 \text{ Adc}, I_B = 16 \text{ mA}_{\text{dc}}$) ($I_C = 8 \text{ Adc}, I_B = 80 \text{ mA}_{\text{dc}}$)	$V_{\text{CE(sat)}}$	– –	2 4	V _{dc}
Base–Emitter Saturation Voltage (1) ($I_C = 8 \text{ Adc}, I_B = 80 \text{ mA}_{\text{dc}}$)	$V_{\text{BE(sat)}}$	–	4.5	V _{dc}
Base–Emitter On Voltage ($I_C = 4 \text{ Adc}, V_{\text{CE}} = 4 \text{ Vdc}$)	$V_{\text{BE(on)}}$	–	2.8	V _{dc}
DYNAMIC CHARACTERISTICS				
Current–Gain–Bandwidth Product ($I_C = 3 \text{ Adc}, V_{\text{CE}} = 4 \text{ Vdc}, f = 1 \text{ MHz}$)	$ h_{\text{fe}} $	4	–	MHz
Output Capacitance ($V_{\text{CB}} = 10 \text{ Vdc}, I_E = 0, f = 0.1 \text{ MHz}$)	C_{ob}	–	300	pF
Small–Signal Current Gain ($I_C = 3 \text{ Adc}, V_{\text{CE}} = 4 \text{ Vdc}, f = 1 \text{ kHz}$)	h_{fe}	300	–	–

1. Pulse Test: Pulse Width $\leq 300 \mu\text{s}$, Duty Cycle $\leq 2\%$.




Figure 1. Power Derating

TYPICAL ELECTRICAL CHARACTERISTICS




Figure 2. DC Current Gain




Figure 3. Collector Saturation Region




Figure 4. "On" Voltages




Figure 5. Temperature Coefficients




Figure 6. Collector Cut-Off Region




Figure 7. Small-Signal Current Gain

MJD128T4 (PNP)




Figure 8. Capacitance




Figure 9. Switching Times Test Circuit




Figure 10. Switching Times




Figure 11. Thermal Response

MJD128T4 (PNP)




Figure 12. Maximum Forward Bias Safe Operating REA

There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate $I_C - V_{CE}$ limits of the transistor that must be observed for reliable operation; i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure 12 is based on $T_{J(pk)} = 150^\circ\text{C}$; T_C is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided $T_{J(pk)} < 150^\circ\text{C}$. $T_{J(pk)}$ may be calculated from the data in Figure 11. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.





Figure 13. Darlington Schematic

MJD128T4 (PNP)

PACKAGE DIMENSIONS

DPAK CASE 369C-01 ISSUE O



NOTES:

1. DIMENSIONING AND TOLERANCING
PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.235	0.245	5.97	6.22
B	0.250	0.265	6.35	6.73
C	0.086	0.094	2.19	2.38
D	0.027	0.035	0.69	0.88
E	0.018	0.023	0.46	0.58
F	0.037	0.045	0.94	1.14
G	0.180 BSC		4.58 BSC	
H	0.034	0.040	0.87	1.01
J	0.018	0.023	0.46	0.58
K	0.102	0.114	2.60	2.89
L	0.090 BSC		2.29 BSC	
R	0.180	0.215	4.57	5.45
S	0.025	0.040	0.63	1.01
U	0.020	---	0.51	---
V	0.035	0.050	0.89	1.27
Z	0.155	---	3.93	---

STYLE 1:

- PIN 1. BASE
2. COLLECTOR
3. Emitter
4. COLLECTOR

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

PUBLICATION ORDERING INFORMATION

Literature Fulfillment:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

JAPAN: ON Semiconductor, Japan Customer Focus Center
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051
Phone: 81-3-5773-3850

ON Semiconductor Website: <http://onsemi.com>

For additional information, please contact your local
Sales Representative.