




LOC		DIST		REVISIONS					
—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
			S			REV PER ECO-15-016062	10NOV15	KG	CD

1. THIS PLUG IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308.
2. MAXIMUM WIRE INSULATION TO BE USED WITH THIS PLUG IS ϕ .068.
3. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS.
4. PACKAGE MARKED M 24308/4-263F.
5. THIS PLUG WILL ACCEPT SIZE 20 PIN CONTACT M39029/64-369 OR ANY TYCO ELECTRONICS HD-20 PIN CONTACT.
- 6 MFG,S PART NO. MARKED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS.
- 7 UL/CSA DESIGNATION MARKED IN THIS AREA.
- 8 FINISH: BRIGHT TIN PER ASTM-B-545 .000400-.000550 THK OVER COPPER PER AMS2418 .000050 MIN THK.
- 9 FRONT SHELL HAS GROUNDING INDENTS, 205170-4 ONLY, (NOT SHOWN).



OBSOLETE	-	8	STEEL PER ASTM-A-109	205170-5
	9	8	STEEL PER ASTM-A-109	205170-4
SUPSD BY 206804-2	-		CADMIUM PER QQ-P-416	BRASS
	6		CADMIUM PER QQ-P-416	STEEL PER ASTM-A-109
REMARKS		FINISH		SHELL MAT'L
				PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS CHK F.C.BALLEW APP'D F.C.BALLEW	08-DEC-87 10-DEC-87 10-DEC-87	TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC	± .005	PRODUCT SPEC	
		1 PLC	± .005	APPLICATION SPEC	
		2 PLC	± .005		
		3 PLC	± .005		
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS		SIZE A1	RESTRICTED TO
		WEIGHT -		CAGE CODE 00779	DRAWING NO 205170
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1