





LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED PER EC 0515-0049-05	20 APR 05	AWF	AWF



- △1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC.
- △2 CONTACT: PHOSPHOR BRONZE.
- △3 CONTACT FINISH: 0.00254[.000100] MIN NICKEL UNDERPLATE.
0.000762[.000030] MIN GOLD OVER NICKEL IN CONTACT AREA.
0.00254[.000100] MIN MATTE TIN OVER NICKEL ON SOLDER TAILS.
- △4 METAL HOLD DOWN: BRASS
- △5 METAL HOLD DOWN FINISH: 0.00127[.000050] MIN NICKEL UNDERPLATE,
0.00381[.000150] MIN MATTE TIN ALL OVER.
- △6 DISTANCE FROM CONTACT POINT TO BOTTOM OF CARD SLOT.
- △7 AMP PART NUMBER, DATE CODE AND CSA LOGO MARKED IN APPROXIMATE AREA SHOWN.




SECTION L-L
SCALE 8:1




5145246-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN AL FRANTUM 19 APR 05	tyco Electronics	Tyco Electronics Corporation Harriburg, Pa 17105-3608		
DIMENSIONS: mm			CHK AL FRANTUM 19 APR 05		NAME CONNECTOR ASSEMBLY, 92 DUAL POSITION, .050 SERIES, STANDARD EDGE SURFACE MOUNT		
TOLERANCES UNLESS OTHERWISE SPECIFIED:			PRODUCT SPEC				
0 PLC ± -			APPLICATION SPEC				
1 PLC ± 0.3[.01]			WEIGHT				
2 PLC ± 0.13[.005]							
3 PLC ± -							
4 PLC ± -							
ANGLES ± -							
FINISH			SIZE A1				
MATERIAL 			CAGE CODE 00779				
			DRAWING NO 5145246				
CUSTOMER DRAWING			RESTRICTED TO -				
			SCALE 4:1				
			SHEET 1 of 2				
			REV A				

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		—		SEE SHEET 1	—	—	—



RECOMMENDED CONNECTOR MOUNTING HOLE PATTERN
(CONNECTOR SIDE SHOWN)



RECOMMENDED MATING BOARD EDGE CONFIGURATION

