



SWITCH-BASIC

CATALOG LISTING
4 HS 26

4HS26

PAGE 1 OF 1

Z

**DRAWING
NUMBER**

X

153

REV
45

11 M

B	C
---	---

10	1
9	2

39

D/C

22

101

1

1

--	--

1

320

-50-

U

REPLACES

RELEASE NO.


CHECK

CHECK

CHECK

—

3



NOTE -

- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000±.002 CENTERS
- 2 - LEADS APPROPRIATELY MARKED FOR CIRCUIT IDENTIFICATION PER MIL-W-5088 AND CVA 127 B
- 3 - FOR USE IN AMBIENT TEMPERATURE RANGE FROM -65° TO +250° F
- ④ WEIGHT OF SWITCH ONLY IS 1.7 OZ MAX WEIGHT OF CONDUCTOR
GROUP ONLY IS 0.5 OZ MAX PER FOOT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA			SCALE FULL	
OPERATING FORCE — — — — 10 - 22 OZ		CONTACT ARRANGEMENT S P D T			DO NOT SCALE PRINT	
RELEASE FORCE — — — — 4 OZ MIN		LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	
DIFFERENTIAL TRAVEL — — — .020 MAX					TOLERANCES ARE:	
OVERTRAVEL — — — — .010 MIN		28 VDC	8 AMP	10 AMP	ONE PLACE (.0)	±.030
		125 VAC	1 AMP	.5 AMP	TWO PLACE (.00)	±.015
					THREE PLACE (.000)	±.005
					ANGLES	±
					WEIGHT	4

FO-50378
FORMTEK