



Home➤ Products > Stainless Steel Media Isolated➤ MLH> Product Page

MLH500PAB01A



MLH Series All Metal Pressure Sensor, Absolute, Amplified, 0 psi to 500 psi Pressure Range, 1/4 -18 NPT Port Style, 0.5 Vdc to 4.5 Vdc Ratiometric Output Type, Packard MetriPak Termination Type

Supporting Documentation
Documentation

Product Specifications	
Measurement Type	Absolute
Signal Conditioning	Amplified
Pressure Range	0 psi to 500 psi
Supply Voltage	5.0 Vdc
Maximum Overpressure	1500 psi
Burst Pressure	5000 psi
Port Style	1/4 -18 NPT
Temperature Compensation	Yes
Output Type	0.5 Vdc to 4.5 Vdc Ratiometric
Protection Circuitry	Reverse Polarity
Accuracy	± 0.25% full scale BFSL
Response Time	less than 2 ms
Output Impedance	25 Ohm max.
Output Calibration	Yes
Termination Type	Packard MetriPak
Weight	57 grams [2.0 ounces]
Full Scale Span	4 Vdc
Operating Temperature Range	- 40 °C to 125 °C [- 40 °F to 257 °F]
Compensated Temperature Range	- 40 °C to 125 °C [- 40 °F to 257 °F]
Storage Temperature Range	NO IDEA SHARED FORMULA EXP PTG
Media Compatibility	Compatible with most media. Wetted components are 300 Series stainless steel and Haynes 214 alloy.
Approvals	CE, UL
UNSPSC Code	411121
UNSPSC Commodity	411121 Transducers
Availability	Global
Series Name	MLH

My Links

Login to iCOM
Login as Rep/AD
Login as Guest
Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control▼

Product Search

Part number search:

Use (*) to expand search

Specification Search