

AD7506/AD7507

FEATURES

R_{ON}: 300Ω

Power Dissipation: 1.5mW

TTL/DTL/CMOS Direct Interface

Break-Before-Make Switching

Standard 28-Pin DIPs and 28-Terminal

Surface Mount Packages

GENERAL DESCRIPTION

The AD7506 is a monolithic CMOS 16-channel analog multiplexer packaged in a 28-pin DIP or a 28-terminal surface mount package. It switches a common output to one of 16 inputs, depending on the state of four address lines and an "enable." The AD7507 is identical to the AD7506 except it has two outputs switched to two of 16 inputs depending on three binary address states and an "enable."

ABSOLUTE MAXIMUM RATINGS*

(T_A = +25°C unless otherwise noted)

V_{DD} - GND +17V

V_{SS} - GND -17V

V Between Any Switch Terminals (see Note 1) 25V

Digital Input Voltage Range V_{DD} to GND

Overvoltage at V_{OUT} (V_S) V_{SS}, V_{DD}

Switch Current (I_S, Continuous One Channel) 20mA

Switch Current (I_S, Surge One Channel) 35mA

1ms Duration, 10% Duty Cycle 35mA

Power Dissipation (Any Package)

Up to +50°C 1000mW

Derates above +50°C by 10mW/°C

Operating Temperature

Commercial (KN Versions) 0 to +70°C

Industrial (KQ Versions) -25°C to +85°C

Extended (TQ, TE Versions) -55°C to +125°C

Storage Temperature -65°C to +150°C

Lead Temperature (Soldering, 10sec) +300°C

CAUTION:

¹Do not apply voltage higher than V_{DD} and V_{SS} to any other terminal, especially when V_{SS} = V_{DD} = 0V all other pins should be at 0V.


²The digital control inputs are diode protected; however, permanent damage may occur on unconnected units under high energy electrostatic fields. Keep unused units in conductive foam at all times.

*Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. Only one Absolute Maximum Rating may be applied at any one time.


REV. A

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices.

FUNCTIONAL DIAGRAMS



AD7506



AD7507

ORDERING GUIDE

Model ¹	Temperature Range	Package Option ²
AD7506KN	0°C to +70°C	N-28
AD7506KQ	-25°C to +85°C	Q-28
AD7506TQ	-55°C to +125°C	Q-28
AD7506TE	-55°C to +125°C	E-28A
AD7507KN	0°C to +70°C	N-28
AD7507KQ	-25°C to +85°C	Q-28
AD7507TQ	-55°C to +125°C	Q-28
AD7507TE	-55°C to +125°C	E-28A

NOTES

¹To order MIL-STD-883, Class B, processed parts, add/883B to part number. See Analog Devices Military Products Databook (1990) for military data sheet.

²N = Plastic DIP; Q = Cerdip; E = Leadless Ceramic Chip Carrier (LCCC).

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A.
 Tel: 617/329-4700 Fax: 617/326-8703 Twx: 710/394-6577
 Telex: 924491 Cable: ANALOG NORWOODMASS

AD7506/AD7507 — SPECIFICATIONS ($V_{DD} = +15V$, $V_{SS} = -15V$ unless otherwise noted.)

Parameter	Version ¹	Switch Condition	@ +25°C	Over Specified Temperature Range	Test Conditions	
ANALOG SWITCH						
R _{ON}	K T	ON ON	300Ω typ, 450Ω max 400Ω max	550Ω max 500Ω max	V _S =−10V to +10V, I _S =1mA	
R _{ON} vs. V _S	All	ON	15% typ		V _S =0V, I _S =1mA	
R _{ON} vs. Temperature	All	ON	0.5%/°C typ			
ΔR _{ON} Between Switches	All	ON	4% typ			
R _{ON} vs. Temperature Between Switches	All	ON	0.05%/°C typ			
I _S (OFF)	K T	OFF OFF	0.05nA typ, 5nA max 0.05nA typ, 1nA max	50nA max 50nA max	V _S =−10V, V _{OUT} =+10V and	
I _{OUT} (OFF)	AD7506 AD7507	K T K T	OFF OFF OFF OFF	0.3nA typ, 20nA max 0.3nA typ, 10nA max 0.3nA typ, 10nA max 0.3nA typ, 5nA max	500nA max 500nA max 250nA max 250nA max	V _S =+10V, V _{OUT} =−10V “Enable” Low
I _{OUT} −I _S (Any Switch ON)	AD7506 AD7507	K T K T	ON ON ON ON	0.3nA typ, 20nA max 0.3nA typ, 10nA max 0.3nA typ, 10nA max 0.3nA typ, 5nA max	500nA max 500nA max 250nA max 250nA max	V _S =0V
DIGITAL CONTROL						
V _{INL}	All			0.8V max		
V _{INH}	All			2.4V min		
I _{INL} or I _{INH}	All		10μA max	30μA max		
C _{IN}	All		3pF typ			
DYNAMIC CHARACTERISTICS ²						
t _{TRANSITION}	All		700ns typ, 1000ns max		V _{IN} : 0 to 3.0V	
t _{OPEN}	All		100ns typ			
t _{ON} (En)	All		1.5μs max		V _{EN} : 0 to 3.0V	
t _{OFF} (En)	All		1μs max			
“OFF” Isolation	All		70dB typ		V _{EN} =0, R _L =200Ω, C _L =3.0pF, V _S =3.0V rms, f=50kHz	
C _S	All	OFF	5pF typ			
C _{OUT}	AD7506 AD7507	All All	OFF OFF	40pF typ 20pF typ		
C _{S−OUT}	All	OFF	0.5pF typ			
C _{SS} Between Any Two Switches	All	OFF	0.5pF typ			
POWER SUPPLY						
I _{DD}	K T	OFF OFF	0.05mA typ, 1mA max 0.05mA typ, 1mA max	2mA max	All Digital Inputs Low	
I _{SS}	K T	OFF OFF	0.05mA typ, 1mA max 0.05mA typ, 1mA max	2mA max		
I _{DD}	K T	ON ON	0.3mA typ, 1mA max 0.3mA typ, 1mA max	2mA max	All Digital Inputs High	
I _{SS}	K T	ON ON	0.05mA typ, 1mA max 0.05mA typ, 1mA max	2mA max		

NOTES

¹KN Version specified for 0 to +70°C; KQ Version for -25°C to +85°C; and TQ, TE Versions for -55°C to +125°C.

²Sample tested to ensure compliance.

Specifications subject to change without notice.

CAUTION

ESD (electrostatic discharge) sensitive device. The digital control inputs are diode protected; however, permanent damage may occur on unconnected devices subject to high energy electrostatic fields. Unused devices must be stored in conductive foam or shunts. The protective foam should be discharged to the destination socket before devices are removed.




TRUTH TABLES


AD7506					
A ₃	A ₂	A ₁	A ₀	E _N	"ON"
0	0	0	0	1	1
0	0	0	1	1	2
0	0	1	0	1	3
0	0	1	1	1	4
0	1	0	0	1	5
0	1	0	1	1	6
0	1	1	0	1	7
0	1	1	1	1	8
1	0	0	0	1	9
1	0	0	1	1	10
1	0	1	0	1	11
1	0	1	1	1	12
1	1	0	0	1	13
1	1	0	1	1	14
1	1	1	0	1	15
1	1	1	1	1	16
X	X	X	X	0	None

AD7507				
A ₂	A ₁	A ₀	E _N	"ON"
0	0	0	1	1 & 9
0	0	1	1	2 & 10
0	1	0	1	3 & 11
0	1	1	1	4 & 12
1	0	0	1	5 & 13
1	0	1	1	6 & 14
1	1	0	1	7 & 15
1	1	1	1	8 & 16
X	X	X	0	None

PIN CONFIGURATIONS





LCCC




Typical Performance Characteristics


1. R_{ON} vs. V_S




2. I_{OUT} vs. V_{OUT}




3. I_{OUT} vs. T_A



4. t_{TRANSITION} vs. V_{IN}





5. P_D vs. Logic Frequency





AD7506/AD7507

TYPICAL SWITCHING CHARACTERISTICS

TEST CIRCUIT 1




TEST CIRCUIT 2




OUTLINE DIMENSIONS

Dimensions shown in inches and (mm).

28-Pin Plastic DIP (Suffix N)



28-Pin Cerdip (Q-28)



28-Terminal LCCC (E-28A)

