



Micro Commercial Components



Micro Commercial Components  
20736 Marilla Street Chatsworth  
CA 91311  
Phone: (818) 701-4933  
Fax: (818) 701-4939

# BZX84C2V4 THRU BZX84C(B)51

## Features

- Planar Die construction
- 350mW Power Dissipation
- Zener Voltages from 2.4V - 51V
- Ideally Suited for Automated Assembly Processes
- Halogen free available upon request by adding suffix "-HF"

## Mechanical Data

- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Lead Free Finish/RoHS Compliant ("P" Suffix designates RoHS Compliant. See ordering information)
- Weight: 0.008 grams (approx.)


### Maximum Ratings @ 25°C Unless Otherwise Specified

|                                     |                                   |                 |       |
|-------------------------------------|-----------------------------------|-----------------|-------|
| Maximum Forward Voltage@IF=10mA     | V <sub>F</sub>                    | 0.9             | V     |
| Power Dissipation (Note A)          | P <sub>(AV)</sub>                 | 350             | mWatt |
| Operation And Storage Temperature   | T <sub>J</sub> , T <sub>STG</sub> | -55°C to +150°C |       |
| Peak Forward Surge Current (Note B) | I <sub>FSM</sub>                  | 2.0             | A     |
| Thermal Resistance (Note C)         | R <sub>thja</sub>                 | 357             | °C/W  |

#### NOTES:

- A. Mounted on 5.0mm<sup>2</sup> (.013mm thick) land areas.  
B. Measured on 8.3ms, single half sine-wave or equivalent square wave, duty cycle = 4 pulses per minute maximum.  
C. Valid provided the terminals are kept at ambient temperature

\*Pin Configuration - Top View






## Silicon

350 mWatt


## Zener Diodes

### SOT-23



| DIM | INCHES |       | MM   |      | NOTE |
|-----|--------|-------|------|------|------|
|     | MIN    | MAX   | MIN  | MAX  |      |
| A   | .110   | .120  | 2.80 | 3.04 |      |
| B   | .083   | .104  | 2.10 | 2.64 |      |
| C   | .047   | .055  | 1.20 | 1.40 |      |
| D   | .035   | .041  | .89  | 1.03 |      |
| E   | .070   | .081  | 1.78 | 2.05 |      |
| F   | .018   | .024  | .45  | .60  |      |
| G   | .0005  | .0039 | .013 | .100 |      |
| H   | .035   | .044  | .89  | 1.12 |      |
| J   | .003   | .007  | .085 | .180 |      |
| K   | .015   | .020  | .37  | .51  |      |
| L   | .007   | .020  | .20  | .50  |      |

### Suggested Solder Pad Layout



## BZX84C2V4 thru BZX84C51

ELECTRICAL CHARACTERISTICS (Ta=25°C unless otherwise noted)

| Part Number | Marking | Nominal Zener Voltage   |       |       | Max. Zener Impedance              |    |                                   |    | Max.Reverse Leakage Current |       |
|-------------|---------|-------------------------|-------|-------|-----------------------------------|----|-----------------------------------|----|-----------------------------|-------|
|             |         | Vz(V) @ I <sub>ZT</sub> |       |       | Z <sub>ZT</sub> @ I <sub>ZT</sub> |    | Z <sub>ZK</sub> @ I <sub>ZK</sub> |    | IR @ VR                     |       |
|             |         | Nom.                    | Min.  | Max.  | Ohm                               | mA | Ohm                               | mA | μA                          | V     |
| BZX84C2V4   | W1/Z11  | 2.4                     | 2.28  | 2.52  | 100                               | 5  | 600                               | 1  | 50                          | 1.0   |
| BZX84C2V7   | W2/Z12  | 2.7                     | 2.5   | 2.9   | 100                               | 5  | 600                               | 1  | 20                          | 1.0   |
| BZX84C3V0   | W3/Z13  | 3                       | 2.8   | 3.2   | 95                                | 5  | 600                               | 1  | 10                          | 1.0   |
| BZX84C3V3   | W4/Z14  | 3.3                     | 3.1   | 3.5   | 95                                | 5  | 600                               | 1  | 5                           | 1.0   |
| BZX84C3V6   | W5/Z15  | 3.6                     | 3.4   | 3.8   | 90                                | 5  | 600                               | 1  | 5                           | 1.0   |
| BZX84C3V9   | W6/Z16  | 3.9                     | 3.7   | 4.1   | 90                                | 5  | 600                               | 1  | 3                           | 1.0   |
| BZX84C4V3   | W7/Z17  | 4.3                     | 4     | 4.6   | 90                                | 5  | 600                               | 1  | 3                           | 1.0   |
| BZX84C4V7   | W8/Z1   | 4.7                     | 4.4   | 5     | 80                                | 5  | 500                               | 1  | 3                           | 2.0   |
| BZX84C5V1   | W9/Z2   | 5.1                     | 4.8   | 5.4   | 60                                | 5  | 480                               | 1  | 2                           | 2.0   |
| BZX84C5V6   | WA/Z3   | 5.6                     | 5.2   | 6     | 40                                | 5  | 400                               | 1  | 1                           | 2.0   |
| BZX84C6V2   | WB/Z4   | 6.2                     | 5.8   | 6.6   | 10                                | 5  | 150                               | 1  | 3                           | 4.0   |
| BZX84C6V8   | WC/Z5   | 6.8                     | 6.4   | 7.2   | 15                                | 5  | 80                                | 1  | 2                           | 4.0   |
| BZX84C7V5   | WD/Z6   | 7.5                     | 7     | 7.9   | 15                                | 5  | 80                                | 1  | 1                           | 5.0   |
| BZX84C8V2   | WE/Z7   | 8.2                     | 7.7   | 8.7   | 15                                | 5  | 80                                | 1  | 0.7                         | 5.0   |
| BZX84C9V1   | WF/Z8   | 9.1                     | 8.5   | 9.6   | 15                                | 5  | 100                               | 1  | 0.5                         | 6.0   |
| BZX84C10    | WG/Z9   | 10                      | 9.4   | 10.6  | 20                                | 5  | 150                               | 1  | 0.2                         | 7.0   |
| BZX84C11    | WH/Y1   | 11                      | 10.4  | 11.6  | 20                                | 5  | 150                               | 1  | 0.1                         | 8.0   |
| BZX84C12    | WI/Y2   | 12                      | 11.4  | 12.7  | 25                                | 5  | 150                               | 1  | 0.1                         | 8.0   |
| BZX84C13    | WK/Y3   | 13                      | 12.4  | 14.1  | 30                                | 5  | 170                               | 1  | 0.1                         | 8.0   |
| BZX84C15    | WL/Y4   | 15                      | 13.8  | 15.6  | 30                                | 5  | 200                               | 1  | 0.1                         | 10.5  |
| BZX84C16    | WM /Y5  | 16                      | 15.3  | 17.1  | 40                                | 5  | 200                               | 1  | 0.1                         | 11.2  |
| BZX84C18    | WN/Y6   | 18                      | 16.8  | 19.1  | 45                                | 5  | 225                               | 1  | 0.1                         | 12.6  |
| BZX84C20    | WO/Y7   | 20                      | 18.8  | 21.2  | 55                                | 5  | 225                               | 1  | 0.1                         | 14.0  |
| BZX84C22    | WP/Y8   | 22                      | 20.8  | 23.3  | 55                                | 5  | 250                               | 1  | 0.1                         | 15.4  |
| BZX84C24    | WR/Y9   | 24                      | 22.8  | 25.6  | 70                                | 5  | 250                               | 1  | 0.1                         | 16.8  |
| BZX84C27    | WS/Y10  | 27                      | 25.1  | 28.9  | 80                                | 2  | 300                               | 1  | 0.1                         | 18.9  |
| BZX84C30    | WT /Y11 | 30                      | 28    | 32    | 80                                | 2  | 300                               | 1  | 0.1                         | 21.0  |
| BZX84C33    | WU/Y12  | 33                      | 31    | 35    | 80                                | 2  | 325                               | 1  | 0.1                         | 23.1  |
| BZX84C36    | WW/Y13  | 36                      | 34    | 38    | 90                                | 2  | 350                               | 1  | 0.1                         | 25.2  |
| BZX84C39    | WX/Y14  | 39                      | 37    | 41    | 130                               | 2  | 350                               | 1  | 0.1                         | 27.3  |
| BZX84C43    | WY/Y15  | 43                      | 40.85 | 45.15 | 150                               | 5  | 375                               | 1  | 0.1                         | 30.10 |
| BZX84C47    | WZ/Y16  | 47                      | 44.65 | 49.35 | 170                               | 5  | 375                               | 1  | 0.1                         | 32.90 |
| BZX84C51    | XA/Y17  | 51                      | 48.45 | 53.55 | 100                               | 5  | 400                               | 1  | 0.1                         | 35.70 |

NOTE:

- Standard zener voltage tolerance is +/- 5% with a 'C' suffix from BZX84C2V4-BZX84C51, suffix 'B' is +/- 2% tolerance from BZX84B4V3-BZX84B51.
- Zener Voltage (Vz) Measurement. Guarantees the zener voltage when measured at 90 seconds while maintaining the lead temperature (TL) AT 30 °C, from the diode body.
- Zener Impedance (Zz) Derivation. The zener impedance is derived from the 60 cycle ac voltage, which results when an AC current having an rms value equal to 10% of the dc zener current (Izt or Izk) is superimposed on Izt or Izk.
- Surge Current (IR) Non-Repetitive. The rating listed in the electrical characteristics table is maximum peak, non-repetitive, reverse surge current of 1/2 square wave or equivalent sine wave pulse of 1/120 second duration superimposed on the test current, Izt, per JEDEC registration; however, actual device capability is as described in Figure 5.

## BZX84B4V3 thru BZX84B51


ELECTRICAL CHARACTERISTICS (Ta=25°C unless otherwise noted)

| Part Number | Marking | Nominal Zener Voltage   |       |       | Max. Zener Impedance              |    |                                   |    | Max.Reverse Leakage Current |      |
|-------------|---------|-------------------------|-------|-------|-----------------------------------|----|-----------------------------------|----|-----------------------------|------|
|             |         | Vz(V) @ I <sub>ZT</sub> |       |       | Z <sub>ZT</sub> @ I <sub>ZT</sub> |    | Z <sub>ZK</sub> @ I <sub>ZK</sub> |    | IR @ VR                     |      |
|             |         | Nom.                    | Min.  | Max.  | Ohm                               | mA | Ohm                               | mA | μA                          | V    |
| BZX84B4V3   | W7      | 4.3                     | 4.21  | 4.39  | 90                                | 5  | 600                               | 1  | 3.0                         | 1.0  |
| BZX84B4V7   | W8/Z1   | 4.7                     | 4.61  | 4.79  | 80                                | 5  | 500                               | 1  | 3.0                         | 2.0  |
| BZX84B5V1   | W9/2Z2  | 5.1                     | 5.00  | 5.20  | 60                                | 5  | 480                               | 1  | 2.0                         | 2.0  |
| BZX84B5V6   | WA/2Z3  | 5.6                     | 5.49  | 5.71  | 40                                | 5  | 400                               | 1  | 1.0                         | 2.0  |
| BZX84B6V2   | WB/2Z4  | 6.2                     | 6.08  | 6.32  | 10                                | 5  | 150                               | 1  | 3.0                         | 4.0  |
| BZX84B6V8   | WC/2Z5  | 6.8                     | 6.66  | 6.94  | 15                                | 5  | 80                                | 1  | 2.0                         | 4.0  |
| BZX84B7V5   | WD/2Z6  | 7.5                     | 7.35  | 7.65  | 15                                | 5  | 80                                | 1  | 1.0                         | 5.0  |
| BZX84B8V2   | WE/2Z7  | 8.2                     | 8.04  | 8.36  | 15                                | 5  | 80                                | 1  | 0.7                         | 5.0  |
| BZX84B9V1   | WF/2Z8  | 9.1                     | 8.92  | 9.28  | 15                                | 5  | 100                               | 1  | 0.5                         | 6.0  |
| BZX84B10    | WG/2Z9  | 10                      | 9.80  | 10.20 | 20                                | 5  | 150                               | 1  | 0.2                         | 7.0  |
| BZX84B11    | WH/2Y1  | 11                      | 10.78 | 11.22 | 20                                | 5  | 150                               | 1  | 0.1                         | 8.0  |
| BZX84B12    | WI/2Y2  | 12                      | 11.76 | 12.24 | 25                                | 5  | 150                               | 1  | 0.1                         | 8.0  |
| BZX84B13    | WK/2Y3  | 13                      | 12.74 | 13.26 | 30                                | 5  | 170                               | 1  | 0.1                         | 8.0  |
| BZX84B15    | WL/2Y4  | 15                      | 14.70 | 15.30 | 30                                | 5  | 200                               | 1  | 0.1                         | 10.5 |
| BZX84B16    | WM/2Y5  | 16                      | 15.68 | 16.32 | 40                                | 5  | 200                               | 1  | 0.1                         | 11.2 |
| BZX84B18    | WN/2Y6  | 18                      | 17.64 | 18.36 | 45                                | 5  | 225                               | 1  | 0.1                         | 12.6 |
| BZX84B20    | WO/2Y7  | 20                      | 19.60 | 20.40 | 55                                | 5  | 225                               | 1  | 0.1                         | 14.0 |
| BZX84B22    | WP/Y8   | 22                      | 21.56 | 22.44 | 55                                | 5  | 250                               | 1  | 0.1                         | 15.4 |
| BZX84B24    | WR/Y9   | 24                      | 23.52 | 24.48 | 70                                | 5  | 250                               | 1  | 0.1                         | 16.8 |
| BZX84B27    | WS/Y10  | 27                      | 26.46 | 27.54 | 80                                | 5  | 300                               | 1  | 0.1                         | 18.9 |
| BZX84B30    | WT/Y11  | 30                      | 29.40 | 30.60 | 80                                | 5  | 300                               | 1  | 0.1                         | 21.0 |
| BZX84B33    | WU/Y12  | 33                      | 32.34 | 33.66 | 80                                | 5  | 325                               | 1  | 0.1                         | 23.1 |
| BZX84B36    | WW/Y13  | 36                      | 35.28 | 36.72 | 90                                | 5  | 350                               | 1  | 0.1                         | 25.2 |
| BZX84B39    | WX/Y14  | 39                      | 38.22 | 39.78 | 130                               | 5  | 350                               | 1  | 0.1                         | 27.3 |
| BZX84B43    | WY      | 43                      | 42.14 | 43.86 | 150                               | 5  | 375                               | 1  | 0.1                         | 30.1 |
| BZX84B47    | WZ      | 47                      | 46.06 | 47.94 | 170                               | 5  | 375                               | 1  | 0.1                         | 32.9 |
| BZX84B51    | XA      | 51                      | 49.98 | 52.02 | 100                               | 5  | 750                               | 1  | 0.1                         | 38.0 |


**NOTE:**

- Standard zener voltage tolerance is +/- 5% with a 'C' suffix from BZX84C2V4~BZX84C51, suffix 'B' is +/- 2% tolerance from BZX84B4V3~BZX84B51.
- Zener Voltage (Vz) Measurement. Guarantees the zener voltage when measured at 90 seconds while maintaining the lead temperature (TL) AT 30 °C, from the diode body.
- Zener Impedance (Zz) Derivation. The zener impedance is derived from the 60 cycle ac voltage, which results when an AC current having an rms value equal to 10% of the dc zener current (Izt or Izk) is superimposed on Izt or Izk.
- Surge Current (IR) Non-Repetitive. The rating listed in the electrical characteristics table is maximum peak, non-repetitive, reverse surge current of 1/2 square wave or equivalent sine wave pulse of 1/120 second duration superimposed on the test current, Izt, per JEDEC registration; however, actual device capability is as described in Figure 5.


# BZX84 Series




**TYPICAL REVERSE CURRENT**




**TEMPERATURE COEFFICIENTS**




**EFFECT OF ZENER VOLTAGE ON ZENER IMPEDANCE**



**TYPICAL FORWARD VOLTAGE**




**STEADY STATE POWER DERATING**




**TYPICAL CAPACITANCE**


# BZX84 Series



**ZENER VOLTAGE V.S. ZENER CURRENT**



**ZENER VOLTAGE V.S. ZENER CURRENT**



**TYPICAL LEAKGE CURRENT**

## Ordering Information :

| Device         | Packing               |
|----------------|-----------------------|
| Part Number-TP | Tape&Reel: 3Kpcs/Reel |

Note : Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp .** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp .** and all the companies whose products are represented on our website, harmless against all damages.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.