


KEMET[®]

CERAMIC
HIGH-RELIABILITY
GR900 SERIES
& MIL-C-123
CAPACITORS



KEMET on the INTERNET

<http://www.kemet.com>

E-Mail: capmaster@kemet.com

CERAMIC HIGH RELIABILITY

CERAMIC HIGH RELIABILITY PRODUCTS

Ceramic Chips, Radial Molded

KEMET Electronics Corporation has been known for many years as the leader in the ceramic high reliability products. KEMET produces high reliability monolithic ceramic capacitors under tightly-controlled manufacturing procedures. These capacitors achieve "State of the Art" performance by virtue of careful materials selection, conservative design rules, motivational training of employees, and scrupulous inspection of all processes as well as the finished product. KEMET not only manufactures its own high reliability ceramic capacitor (GR900), KEMET also manufactures MIL-C-123 product which is built to the highest military standard in the industry today.

BASIC REQUIREMENTS FOR KEMET'S HIGH RELIABILITY PRODUCTS ARE AS FOLLOWS:

- 1. Selected Raw Materials:** All raw materials are selected for characteristics known to produce the finest quality capacitors exhibiting the best electrical parameters and physical integrity. Materials traceability is maintained throughout the manufacturing process.
- 2. Batch Homogeneity:** Production is under batch control. Each batch is homogeneous with respect to materials, design and processing conditions.
- 3. Clean Room Processing:** All processes sensitive to particulate contamination take place in a clean room environment.
- 4. Special Designs:** Special design considerations such as dielectric thickness are strictly enforced. Only COG (BP) and X7R (BX) temperature characteristics are made.
- 5. Destructive Physical Analysis (DPA, or Cross-Sectioning):** All batches are sampled using EIA-469 as a minimum requirement. The samples remain on file and DPA Reports are shipped with the capacitors.
- 6. Ultrasonic Scanning:** Optional 100% screening may be performed using ultrasonic waves to detect voids or delaminations. Screened lots must pass a final sample DPA.
- 7. Batch Performance Monitoring:** All production batches are tested to generate electrical characteristics. Batches which show anomalous characteristics are rejected.
- 8. Special Customer Requirements:** Many special requirements such as serialization, DPA samples,

X-Ray plates, and special packaging can be accommodated.

9. Document Applicable: The high reliability product is implemented through various internal documents under revision control. The Manufacturing Instructions provide detailed descriptions of all operations and delineate requirements for process control and product performance at various points in the process flow. Inspector Operating Documents describe test procedures and sampling plans for inspection of raw materials, in-process material and finished product. Raw material specifications describe physical and chemical characteristics as well as the packaging and labeling needed to preserve characteristics and identity. Customer specifications are internal documents applicable only to products manufactured and inspected to requirements of individual customers; in effect, these documents translate customer drawings into modifications of the specified portions of KEMET standard procedures.

The Quality System in total is controlled by the KEMET Quality Manual and by various Quality Operating Documents. All documents, and revisions thereto, bear specified approval signatures.

DETAILED SPECIFICATION: Temperature Characteristics

Electrical stability with respect to temperature and voltage is related inversely to the packaging efficiency (capacitance X voltage in a given case size). COG (BP) is made from ceramic materials which are not ferroelectric, yielding superior stability but low packaging efficiency. X7R (BX) is made from materials which are ferroelectric, such as barium titanate, yielding a stable and high packaging efficiency.

Aging

If the temperature of a barium titanate dielectric is lowered after an excursion above its curie point, the ceramic crystalline structure gradually reverts to the tetragonal form typical of the low temperature conditions. The reversion requires a considerable length of time, and its effect in practical capacitors has become known as "Aging". The rate of aging is affected by both the temperature and the applied voltage experienced by the capacitor. The COG (BP) formulation is non-ferroelectric and does not exhibit aging. The X7R (BX) formulation exhibits its own

characteristic aging rate which describes a decrease in capacitance versus time. The capacitance of the X7R dielectric decreases approximately 1.0% during each decade of hours following a return to temperatures below the curie point. In other words, capacitance will decrease 1.0% between 1 and 10 hours, another 1.0% between 10 and 100 hours, another 1.0% between 100 and 1000 hours, etc.

KEMET takes into consideration the aging rate by designing capacitors to fall within the specified capacitance tolerance at 2400 hours. Inasmuch as the aging rate is exponential, very little change in capacitance will take place after 2400 hours.

Voltage Effects

Ferroelectric materials are also affected by applied voltage, both alternating and direct. Low values of voltage produce a slight increase in capacitance and dissipation factor. Higher voltages cause a decrease in capacitance. Typically, capacitors with X7R characteristic decrease in capacitance by approximately 10% when rated DC voltage is applied.

A small portion of the decrease in capacitance by the application of a high DC voltage persists after the voltage is removed and then disappears gradually.

Customer Testing

Because of temperature and voltage effects, caution must be used in establishing a testing sequence for ceramic capacitors. Insulation resistance measurements and tests of dielectric withstanding voltage both require application of high DC voltage and cause temporary changes in capacitance. These tests, therefore, should not be conducted until capacitance testing is completed. Alternatively, the capacitors can be "de-aged" at high temperature as described above. A stabilization time at room ambient of 24 hours should be used after de-aging.

See F-3101 Catalog for more details.

PERFORMANCE CHARACTERISTICS

General Information

Working Voltage:

COG (BP) - 50,100 & 200 volts

X7R (BX) - 50,100 & 200 volts

Temperature Characteristics:

COG (BP): 0 $\pm$ 30 ppm/°C from -55°C to +125°C.
(Limits widen below 20 pF.)

X7R (BX): $\pm$ 15%; from -55°C to +125°C.

Capacitance Tolerance:

COG (BP): C - $\pm$ 0.25pF; D - $\pm$ 0.5pF; F - $\pm$ 1%;

G - $\pm$ 2%; J - $\pm$ 5%; K - $\pm$ 10%; M - $\pm$ 20%.

X7R (BX): J - $\pm$ 5%; K - $\pm$ 10%; M - $\pm$ 20%.

Electrical

Capacitance: Within specified tolerance when measured with 1 volt RMS @ 1 kHz (1000pF or less @ 1 MHz for COG (BP)).

Dissipation Factor:

25°C @ 1 kHz (1000 pF or less at 1 MHz for COG (BP)).

COG (BP): 0.15% maximum

X7R (BX): 2.5% maximum

Insulation Resistance:

After 2 minutes electrification:

at 25°C and rated voltage:

COG (BP): 100K megohms or (1000 megohm X μ F), whichever is less.

X7R (BX): 100K megohms or (1000 megohm X μ F), whichever is less.

at 125°C and rated voltage:

COG (BP): 10K megohms or (100 megohm X μ F), whichever is less.

X7R (BX): 10K megohms or (100 megohm X μ F), whichever is less.

Dielectric Withstanding Voltage: 250% of rated voltage for 5 seconds with current limited to 50 MA at 25°C.

Aging Rate: % Delta Cap/Decade Hour, Typical

COG (BP): 0%

X7R (BX): 1.0%









IMPORTANT NOTICE

KEMET Electronics Corporation disclaims all warranties, whether express, implied, or statutory as to any manner whatsoever, including the condition of the equipment, its compatibility with specific requirements, its merchantability, or fitness for any particular purpose which extend beyond the description on the face hereof.

Furthermore, under no circumstances shall KEMET Electronics Corporation be liable for consequential, special, incidental or indirect damages resulting from the use or handling of this product.

Finally, KEMET Electronics Corporation does not assume any responsibility for the correctness of the information contained in this catalog. All design characteristics, specifications, tolerances, and the like are subject to change without notice.

MIL-C-123/GR900 TYPICAL PERFORMANCE CURVES



INTRODUCTION

MIL-C-123 specification covers the general requirements for high reliability, general purpose (BX) and temperature stable (BP) ceramic dielectric fixed capacitors for space, missile, and other high reliability applications. Capacitors covered by MIL-C-123 may be used in critical frequency determining applications, timing circuits, and other applications where absolute stability is required (BP) and in applications where appreciable variations in capacitance with respect to temperature, voltage, frequency, and life can be tolerated (BX).

SCREENING TESTS

Each lot has the following In-Process Inspections performed:

1. 100% Ultrasonic Scan
2. n-Process Destructive Physical Analysis
3. 100% visual inspection at a minimum of 10X magnification
4. Pre-encapsulation terminal strength evaluation (lead devices only). Radial lead capacitors must meet a minimum lead pull of 1.8 kg (4.0 lbs.).

The following Group A shall be performed on each lot:

1. **Thermal Shock**—Performed in accordance to MIL-STD-202, Method 107, Condition A, with step 3 being 125°C. Number of cycles shall be 20 (100% of lot).
2. **Voltage Conditioning**—The voltage conditioning shall consist of applying twice the rated voltage to the units at the maximum rated temperature of 125°C for a minimum of 168 hours and a maximum of 264 hours. The voltage conditioning may be terminated at any time during 168 hours to 264 hours time interval that confirmed failures meet the requirements for the PDA during the last 48 hours listed in Table I below (100% of lot).

Optional Voltage Conditioning (Accelerated Voltage Conditioning)—All conditions of the standard voltage conditioning apply with the exception of the increased voltage and the decreased test time. (Refer to Mil-C-123 for formula.)

*Step 5 is performed on chips at this point (100% of lot).

3. **Dielectric Withstanding Voltage** 250% of the dc rated voltage at 25°C (100% of lot).
4. **Insulation Resistance**—The 25°C measurement with rated voltage applied shall be the lesser of 100,000 megohms or 1000 megohm-microfarads (100% of lot).

*5. **Insulation Resistance**—The 125°C measurement with rated voltage applied shall be the lesser of 10,000 megohms or 100 megohm-microfarads (1000% of lot). For chips 125°C IR is performed prior to step 3 above.

6. **Capacitance** must be within specified tolerance at 25°C (100% of lot). **Cap Exclusion:** Capacitance values no more than 5% or .5 pF, whichever is greater, for BX characteristics or 1% or .3 pF, whichever is greater, for BP characteristics beyond specified tolerance limit shall be removed from the lot but shall not be considered defective for determination of the PDA.

7. **Dissipation Factor** shall not exceed 2.5% for X dielectric, 0.15% for G dielectric at 25°C (100% of lot).

8. **Percent Defective Allowable (PDA).** The following table lists the PDA requirements for MIL-C-123 Group A:

TABLE I			
KEMET STYLE	MIL STYLE	BURN IN PDA LAST 48 HOURS	PDA OVERALL
C052Z	CKS05	1 unit or 0.1%	3%
C062Z	CKS06	1 unit or 0.2%	5%
C512Z	CKS07	1 unit or 0.2%	5%
C0805Z	CKS51	1 unit or 0.1%	3%
C1210Z	CKS52	1 unit or 0.1%	3%
C1808Z	CKS53	1 unit or 0.1%	3%
C2225Z	CKS54	1 unit or 0.1%	3%

9. **Radiographic Inspection** (lead devices only) (100% of lot).

10. **Visual Inspection** per MIL-C-123 criteria.

11. **Destructive Physical Analysis** per EIA-469 and MIL-C-123.

SAMPLE TESTS

The following Group B tests shall be performed on samples from each lot, which have been subjected to and have passed Group A inspection.

1. **Thermal Shock**—Performed in accordance to MIL-STD-202, Method 107, Condition A, with step 3 being 125°C. Number of cycles shall be 100.
2. **Life Test per MIL-5TD-202, Method 108.** Test temperature and tolerance is +125°C +4, -0°C. Capacitors shall be subjected to 2X rated voltage for 1000 hours.
3. **Humidity, steady state, low voltage per MIL-STD-202, Method 103, Condition A.** Capacitors shall be subjected to an environment of 85°C with 85% relative humidity for 240 hours minimum. Cycling shall not be performed. A dc potential of 1.3 ±0.25 volts shall be applied continuously through a 100,000 ohm resistance to each device under test. At completion, 25°C IR and Cap are read.
4. **Voltage-temperature limits**—Capacitance is measured at various temperatures (-55°C to +125°C) with and without rated voltage.
5. **Moisture Resistance per MIL-STD-202, Method 106.** There shall be 20 continuous cycles. During the first 10 cycles only, a dc potential of 50 volts shall be applied across the capacitor terminals. Once each day, a check shall be performed to determine whether a capacitor has shorted. Vibration cycle of MIL-STD-202, Method 106, Step 7b shall not be performed. Upon completion of MIL-STD-202, Method 106, Step 6 of the final cycle, capacitors shall be measured for capacitance, dielectric withstanding voltage and insulation resistance.

The following Group C tests shall be performed on samples selected from lots that have passed Group A and have been submitted for Group B inspection. Samples shall be selected every two months.

1. Terminal Strength
2. Solderability
3. Resistance to Soldering Heat
4. Solvent Resistance (Lead devices only)

All lots shipped must have been subjected to and passed Group A and B testing.

STANDARD PACKAGING FOR MIL-C-123 IS AS FOLLOWS:


C052Z	tray	C0805Z	chip tray
C062Z	tray	C1210Z	chip tray
C512Z	1 pc. per bag	C1808Z	chip tray
		C2225Z	chip tray

DATA PACKAGE

A data package is sent with each shipment which contains:

1. Summary of Group A testing
2. Summary of Group B testing
3. Group B Variables Test Data
4. Lead Pull Data (Lead Devices Only)
5. Final Destructive Physical Analysis Report
6. Certificate of Compliance stating that the ceramic capacitors supplied meet all the requirements of MIL-C-123, the applicable slash sheet(s) and all associated documents.

CAPACITOR OUTLINE DRAWINGS - (RADIAL LEADS)



DIMENSIONS — INCHES & (MILLIMETERS)

CASE SIZE	MILITARY EQUIVALENT STYLES	H HEIGHT	L LENGTH	W WIDTH	S LEAD SPACING
C052	CKS05	.190 ± .010 (4.83 ± .25)	.190 ± .010 (4.83 ± .25)	.090 ± .010 (2.29 ± .25)	.200 ± .015 (5.08 ± .38)
C062	CKS06	.290 ± .010 (7.37 ± .25)	.290 ± .010 (7.37 ± .25)	.090 ± .010 (2.29 ± .25)	.200 ± .015 (5.08 ± .38)
C512	CKS07	.480 ± .020 (12.19 ± .51)	.480 ± .020 (12.19 ± .51)	.140 ± .010 (3.56 ± .25)*	.400 ± .020 (10.16 ± .51)

*0.200 maximum for some capacitance values.

ORDERING INFORMATION KEMET PART NUMBER

CERAMIC CASE SIZE — C 052 Z 102 K 5 G 5 C A

Radial
C052
C062
C512

SPECIFICATION — Z — Mil-C-123

CAPACITANCE — In picofarad code

CAPACITANCE TOLERANCE — Standard
C — ±0.25 pF J — ±5%
D — ±0.5 pF K — ±10%
F — ±1%

WORKING VOLTAGE — 5 — 50
1 — 100

FAILURE RATE — A — Standard — Not applicable

LEAD MATERIAL — C — Standard
Radial: solder coated copper

INTERNAL CONSTRUCTION — 5 — Ultra-High Temperature Solder

TEMPERATURE CHARACTERISTIC				
KEMET Designator	Military Equivalent	Capacitance Change With Temp.		
		Temp. Range, °C	Measured Without DC Bias Voltage	Measured With Bias (Rated) Voltage
G (Ultra Stable)	BP	-55 to +125	±30 ppm/°C	±30 ppm/°C
X (Stable)	BX	-55 to +125	±15%	+15% -25%

MIL-C-123 MILITARY PART NUMBER

M123 A 01 BX B 103 K C

MILITARY
SPECIFICATION
NUMBER

MODIFICATION LETTER

Indicates the latest characteristics
of the part in the specification sheet.

MIL-C-123 SLASH SHEET NUMBER

Slash Sheet #	KEMET Style	Mil-C-123 Style
01	C052	CKS05
02	C062	CKS06
03	C512	CKS07

TERMINATION

Molded

C — Solder-coated copper (radial)

TOLERANCE

C—±0.25pF J—±5%

D—±0.5pF K—±10%

F—±1%

CAPACITANCE

In picofarad code

VOLTAGE

B=50 C=100

VOLTAGE-TEMPERATURE CHARACTERISTICS

KEMET Designator	Military Equivalent	Capacitance Change With Temp.		
		Temp. Range, °C	Measured Without DC Bias Voltage	Measured (Rated) With Bias Voltage
G (Ultra Stable)	BP	-55 to +125	±30 ppm/°C	±30 ppm/°C
X (Stable)	BX	-55 to +125	±15%	+15% -25%

RATINGS & PART NUMBER REFERENCE

CAP. pF	KEMET PART NUMBER	MIL-C-123 PART NUMBER
100 VOLT - BP - C052 SIZE (MILITARY CKS05)		
4.7	C052Z479A1G5CA	M123A01BPC4R7A1C
5.1	C052Z519A1G5CA	M123A01BPC5R1A1C
5.6	C052Z569A1G5CA	M123A01BPC5R6A1C
6.2	C052Z629A1G5CA	M123A01BPC6R2A1C
6.8	C052Z689A1G5CA	M123A01BPC6R8A1C
7.5	C052Z759A1G5CA	M123A01BPC7R5A1C
8.2	C052Z829A1G5CA	M123A01BPC8R2A1C
9.1	C052Z919A1G5CA	M123A01BPC9R1A1C
10	C052Z100A1G5CA	M123A01BPC100A1C
11	C052Z110A1G5CA	M123A01BPC110A1C
12	C052Z120A1G5CA	M123A01BPC120A1C
13	C052Z130A1G5CA	M123A01BPC130A1C
15	C052Z150A1G5CA	M123A01BPC150A1C
16	C052Z160A1G5CA	M123A01BPC160A1C
18	C052Z180A1G5CA	M123A01BPC180A1C
20	C052Z200A1G5CA	M123A01BPC200A1C
22	C052Z220A1G5CA	M123A01BPC220A1C
24	C052Z240A1G5CA	M123A01BPC240A1C
27	C052Z270A1G5CA	M123A01BPC270A1C
30	C052Z300A1G5CA	M123A01BPC300A1C
33	C052Z330A1G5CA	M123A01BPC330A1C
36	C052Z360A1G5CA	M123A01BPC360A1C
39	C052Z390A1G5CA	M123A01BPC390A1C
43	C052Z430A1G5CA	M123A01BPC430A1C
47	C052Z470A1G5CA	M123A01BPC470A1C
51	C052Z510A1G5CA	M123A01BPC510A1C
56	C052Z560A1G5CA	M123A01BPC560A1C
62	C052Z620A1G5CA	M123A01BPC620A1C
68	C052Z680A1G5CA	M123A01BPC680A1C
75	C052Z750A1G5CA	M123A01BPC750A1C
82	C052Z820A1G5CA	M123A01BPC820A1C
91	C052Z910A1G5CA	M123A01BPC910A1C
100	C052Z101A1G5CA	M123A01BPC101A1C
110	C052Z111A1G5CA	M123A01BPC111A1C
120	C052Z121A1G5CA	M123A01BPC121A1C
130	C052Z131A1G5CA	M123A01BPC131A1C
150	C052Z151A1G5CA	M123A01BPC151A1C
160	C052Z161A1G5CA	M123A01BPC161A1C
180	C052Z181A1G5CA	M123A01BPC181A1C
200	C052Z201A1G5CA	M123A01BPC201A1C
220	C052Z221A1G5CA	M123A01BPC221A1C
240	C052Z241A1G5CA	M123A01BPC241A1C
50 VOLT - BP - C052 SIZE (MILITARY CKS05)		
270	C052Z271A1G5CA	M123A01BPC271A1C
300	C052Z301A1G5CA	M123A01BPC301A1C
330	C052Z331A1G5CA	M123A01BPC331A1C
360	C052Z361A1G5CA	M123A01BPC361A1C
390	C052Z391A1G5CA	M123A01BPC391A1C
430	C052Z431A1G5CA	M123A01BPC431A1C
470	C052Z471A1G5CA	M123A01BPC471A1C
510	C052Z511A1G5CA	M123A01BPC511A1C

CAP. pF	KEMET PART NUMBER	MIL-C-123 PART NUMBER
50 VOLT - BP - C052 SIZE (MILITARY CKS05) (Cont'd)		
560	C052Z561A1G5CA	M123A01BPC561A1C
620	C052Z621A1G5CA	M123A01BPC621A1C
680	C052Z681A1G5CA	M123A01BPC681A1C
750	C052Z751A1G5CA	M123A01BPC751A1C
820	C052Z821A1G5CA	M123A01BPC821A1C
910	C052Z911A1G5CA	M123A01BPC911A1C
1,000	C052Z102A1G5CA	M123A01BPC102A1C
1,100	C052Z112A1G5CA	M123A01BPC112A1C
1,200	C052Z122A1G5CA	M123A01BPC122A1C
1,300	C052Z132A1G5CA	M123A01BPC132A1C
1,500	C052Z152A1G5CA	M123A01BPC152A1C
1,600	C052Z162A1G5CA	M123A01BPC162A1C
1,800	C052Z182A1G5CA	M123A01BPC182A1C
2,000	C052Z202A1G5CA	M123A01BPC202A1C
2,200	C052Z222A1G5CA	M123A01BPC222A1C
2,400	C052Z242A1G5CA	M123A01BPC242A1C
2,700	C052Z272A1G5CA	M123A01BPC272A1C
100 VOLT - BP - C062 SIZE (MILITARY CKS06)		
270	C062Z271A1G5CA	M123A02BPC271A1C
300	C062Z301A1G5CA	M123A02BPC301A1C
330	C062Z331A1G5CA	M123A02BPC331A1C
360	C062Z361A1G5CA	M123A02BPC361A1C
390	C062Z391A1G5CA	M123A02BPC391A1C
430	C062Z431A1G5CA	M123A02BPC431A1C
470	C062Z471A1G5CA	M123A02BPC471A1C
510	C062Z511A1G5CA	M123A02BPC511A1C
560	C062Z561A1G5CA	M123A02BPC561A1C
620	C062Z621A1G5CA	M123A02BPC621A1C
680	C062Z681A1G5CA	M123A02BPC681A1C
750	C062Z751A1G5CA	M123A02BPC751A1C
820	C062Z821A1G5CA	M123A02BPC821A1C
910	C062Z911A1G5CA	M123A02BPC911A1C
1,000	C062Z102A1G5CA	M123A02BPC102A1C
1,100	C062Z112A1G5CA	M123A02BPC112A1C
1,200	C062Z122A1G5CA	M123A02BPC122A1C
1,300	C062Z132A1G5CA	M123A02BPC132A1C
1,500	C062Z152A1G5CA	M123A02BPC152A1C
1,600	C062Z162A1G5CA	M123A02BPC162A1C
1,800	C062Z182A1G5CA	M123A02BPC182A1C
2,000	C062Z202A1G5CA	M123A02BPC202A1C
2,200	C062Z222A1G5CA	M123A02BPC222A1C
2,400	C062Z242A1G5CA	M123A02BPC242A1C
50 VOLT - BP - C062 SIZE (MILITARY CKS06)		
2,700	C062Z272A1G5CA	M123A02BPC272A1C
3,000	C062Z302A1G5CA	M123A02BPC302A1C
3,300	C062Z332A1G5CA	M123A02BPC332A1C
3,600	C062Z362A1G5CA	M123A02BPC362A1C
3,900	C062Z392A1G5CA	M123A02BPC392A1C
4,300	C062Z432A1G5CA	M123A02BPC432A1C
4,700	C062Z472A1G5CA	M123A02BPC472A1C

To complete the part numbers, insert the following tolerances: (1) C, ±0.25pF; D, ±0.5pF (2) C, ±0.25pF; J, ±5%; K, ±10% (3) F, ±1%; J, ±5%; K, ±10%

RATINGS & PART NUMBER REFERENCE

CAP. pF	KEMET PART NUMBER	MIL-C-123 PART NUMBER
100 VOLT - BX - C052 SIZE (MILITARY CKS05)		
270	C052Z271K1X5CA	M123A01BXC271KC
330	C052Z331K1X5CA	M123A01BXC331KC
390	C052Z391K1X5CA	M123A01BXC391KC
470	C052Z471K1X5CA	M123A01BXC471KC
560	C052Z561K1X5CA	M123A01BXC561KC
680	C052Z681K1X5CA	M123A01BXC681KC
820	C052Z821K1X5CA	M123A01BXC821KC
1,000	C052Z102K1X5CA	M123A01BXC102KC
1,200	C052Z122K1X5CA	M123A01BXC122KC
1,500	C052Z152K1X5CA	M123A01BXC152KC
1,800	C052Z182K1X5CA	M123A01BXC182KC
2,200	C052Z222K1X5CA	M123A01BXC222KC
2,700	C052Z272K1X5CA	M123A01BXC272KC
3,300	C052Z332K1X5CA	M123A01BXC332KC
3,900	C052Z392K1X5CA	M123A01BXC392KC
4,700	C052Z472K1X5CA	M123A01BXC472KC
50 VOLT - BX - C052 SIZE (MILITARY CKS05)		
5,600	C052Z562K5X5CA	M123A01BXC562KC
6,800	C052Z682K5X5CA	M123A01BXC682KC
8,200	C052Z822K5X5CA	M123A01BXC822KC
10,000	C052Z103K5X5CA	M123A01BXC103KC

CAP. pF	KEMET PART NUMBER	MIL-C-123 PART NUMBER
100 VOLT - BP - C512 SIZE (MILITARY CKS07)		
2,700	C512Z272③1G5CA	M123A03BPC272③C
3,000	C512Z302③1G5CA	M123A03BPC302③C
3,300	C512Z332③1G5CA	M123A03BPC332③C
3,600	C512Z362③1G5CA	M123A03BPC362③C
3,900	C512Z392③1G5CA	M123A03BPC392③C
4,300	C512Z432③1G5CA	M123A03BPC432③C
4,700	C512Z472③1G5CA	M123A03BPC472③C
5,100	C512Z512③1G5CA	M123A03BPC512③C
5,600	C512Z562③1G5CA	M123A03BPC562③C
6,200	C512Z622③1G5CA	M123A03BPC622③C
6,800	C512Z682③1G5CA	M123A03BPC682③C
7,500	C512Z752③1G5CA	M123A03BPC752③C
8,200	C512Z822③1G5CA	M123A03BPC822③C
9,100	C512Z912③1G5CA	M123A03BPC912③C
10,000	C512Z103③1G5CA	M123A03BPC103③C
50 VOLT - BP - C512 SIZE (MILITARY CKS07)		
11,000	C512Z113③5G5CA	M123A03BPB113③C
12,000	C512Z123③5G5CA	M123A03BPB123③C
13,000	C512Z133③5G5CA	M123A03BPB133③C
15,000	C512Z153③5G5CA	M123A03BPB153③C
16,000	C512Z163③5G5CA	M123A03BPB163③C
18,000	C512Z183③5G5CA	M123A03BPB183③C
20,000	C512Z203③5G5CA	M123A03BPB203③C
22,000	C512Z223③5G5CA	M123A03BPB223③C
24,000	C512Z243③5G5CA	M123A03BPB243③C
27,000	C512Z273③5G5CA	M123A03BPB273③C
30,000	C512Z303③5G5CA	M123A03BPB303③C
33,000	C512Z333③5G5CA	M123A03BPB333③C
36,000	C512Z363③5G5CA	M123A03BPB363③C
39,000	C512Z393③5G5CA	M123A03BPB393③C
43,000	C512Z433③5G5CA	M123A03BPB433③C
47,000	C512Z473③5G5CA	M123A03BPB473③C
51,000	C512Z513③5G5CA	M123A03BPB513③C
56,000	C512Z563③5G5CA	M123A03BPB563③C
62,000	C512Z623③5G5CA	M123A03BPB623③C
68,000	C512Z683③5G5CA	M123A03BPB683③C
75,000	C512Z753③5G5CA	M123A03BPB753③C
82,000	C512Z823③5G5CA	M123A03BPB823③C
91,000	C512Z913③5G5CA	M123A03BPB913③C
100,000	C512Z104③5G5CA	M123A03BPB104③C

CAP. pF	KEMET PART NUMBER	MIL-C-123 PART NUMBER
100 VOLT - BX - C062 SIZE (MILITARY CKS06)		
5,600	C062Z562K1X5CA	M123A02BXC562KC
6,800	C062Z682K1X5CA	M123A02BXC682KC
8,200	C062Z822K1X5CA	M123A02BXC822KC
10,000	C062Z103K1X5CA	M123A02BXC103KC
12,000	C062Z123K1X5CA	M123A02BXC123KC
15,000	C062Z153K1X5CA	M123A02BXC153KC
18,000	C062Z183K1X5CA	M123A02BXC183KC
22,000	C062Z223K1X5CA	M123A02BXC223KC
27,000	C062Z273K1X5CA	M123A02BXC273KC
33,000	C062Z333K1X5CA	M123A02BXC333KC
39,000	C062Z393K1X5CA	M123A02BXC393KC
47,000	C062Z473K1X5CA	M123A02BXC473KC
56,000	C062Z563K1X5CA	M123A02BXC563KC
68,000	C062Z683K1X5CA	M123A02BXC683KC
82,000	C062Z823K1X5CA	M123A02BXC823KC
100,000	C062Z104K1X5CA	M123A02BXC104KC
50 VOLT - BX - C062 SIZE (MILITARY CKS06)		
56,000	C062Z563K5X5CA	M123A02BXC563KC
68,000	C062Z683K5X5CA	M123A02BXC683KC
82,000	C062Z823K5X5CA	M123A02BXC823KC
100,000	C062Z104K5X5CA	M123A02BXC104KC
120,000	C062Z124K5X5CA	M123A02BXC124KC
150,000	C062Z154K5X5CA	M123A02BXC154KC
180,000	C062Z184K5X5CA	M123A02BXC184KC
220,000	C062Z224K5X5CA	M123A02BXC224KC
270,000	C062Z274K5X5CA	M123A02BXC274KC
330,000	C062Z334K5X5CA	M123A02BXC334KC
390,000	C062Z394K5X5CA	M123A02BXC394KC
470,000	C062Z474K5X5CA	M123A02BXC474KC
560,000	C062Z564K5X5CA	M123A02BXC564KC
680,000	C062Z684K5X5CA	M123A02BXC684KC
820,000	C062Z824K5X5CA	M123A02BXC824KC
1,000,000	C062Z105K5X5CA	M123A02BXC105KC

CAP. pF	KEMET PART NUMBER	MIL-C-123 PART NUMBER
100 VOLT - BX - C512 SIZE (MILITARY CKS07)		
56,000	C512Z563K1X5CA	M123A02BXC563KC
68,000	C512Z683K1X5CA	M123A02BXC683KC
82,000	C512Z823K1X5CA	M123A02BXC823KC
100,000	C512Z104K1X5CA	M123A02BXC104KC
120,000	C512Z124K1X5CA	M123A02BXC124KC
150,000	C512Z154K1X5CA	M123A02BXC154KC
180,000	C512Z184K1X5CA	M123A02BXC184KC
220,000	C512Z224K1X5CA	M123A02BXC224KC
270,000	C512Z274K1X5CA	M123A02BXC274KC
330,000	C512Z334K1X5CA	M123A02BXC334KC
390,000	C512Z394K1X5CA	M123A02BXC394KC
470,000	C512Z474K1X5CA	M123A02BXC474KC
50 VOLT - BX - C512 SIZE (MILITARY CKS07)		
560,000	C512Z564K5X5CA	M123A02BXC564KC
680,000	C512Z684K5X5CA	M123A02BXC684KC
820,000	C512Z824K5X5CA	M123A02BXC824KC
1,000,000	C512Z105K5X5CA	M123A02BXC105KC

To complete the part numbers, insert the following tolerances: (1) C, $\pm 0.25\text{pF}$; D, $\pm 0.5\text{pF}$ (2) C, $\pm 0.25\text{pF}$; J, $\pm 5\%$; K, $\pm 10\%$ (3) F, $\pm 1\%$; J, $\pm 5\%$; K, $\pm 10\%$

MARKING INFORMATION

C052Z
M123A
01BPC
4R7CC
— MIL-C-123
Part Number


C062Z, C512Z
M123A
02BPC
271FC
JAN
— MIL-C-123
Part Number
"JAN"

CAGE =
Commercial and
Government Entity

JAN
XXXX*
31433
— "JAN"
— Date Lot Code
— CAGE

271F
JAN
XXXX*
31433
— Capacitance Code & Tolerance
— "JAN"
— Date Lot Code
— CAGE

CAPACITOR OUTLINE DRAWINGS



Military Designation - "S"; KEMET Designation - "H"

DIMENSIONS - INCHES

Chip Size	Military Equivalent Styles	L Length	W Width	T Thickness Maximum
0805	CKS51	0.080 + 0.035 - 0.015	0.050 + 0.030 - 0.015	0.070
1210	CKS52	0.120 + 0.040 - 0.015	0.100 + 0.030 - 0.015	0.080
1808	CKS53	0.180 + 0.040 - 0.015	0.080 + 0.030 - 0.015	0.080
2225	CKS54	0.220 + 0.040 - 0.015	0.250 + 0.030 - 0.015	0.085

MARKING

Capacitors shall be legibly laser marked in contrasting color with either a three-digit capacitance code or KEMET trademark and 2-digit capacitance symbol.

KEMET ORDERING INFORMATION

Ceramic Chip Size
0805, 1210, 1808, 2225

Specification
Z — Mil-C-123

Capacitance Picofarad Code
First two digits represent significant figures.
Third digit specifies number of zeros to follow.

Capacitance Tolerance
C — $\pm 0.25\text{pF}$ J — $\pm 5\%$
D — $\pm 0.5\text{ pF}$ K — $\pm 10\%$
F — $\pm 1\%$

Working Voltage
5 — 50

Termination
H = Nickel Guarded, Solder-Coated (Solderguard I)

Failure Rate
(%/1000 Hours)
A - Standard — Not Applicable

Temperature Characteristic

KEMET Designator	Military Equivalent	Temp. Range, °C	Measured Without DC Bias Voltage	Measured With Bias (Rated Voltage)
G (Ultra Stable)	BP	-55 to +125	± 30 ppm °C	± 30 ppm °C
X (Stable)	BX	-55 to +125	$\pm 15\%$	+15% -25%

Military Specification Number

Modification Number
Indicates the latest characteristics of the part in the specification sheet.

MIL-C-123 Slash Sheet Number

Slash Sheet#	KEMET Style	MIL-C-123 Style
10	C0805	CKS51
11	C1210	CKS52
12	C1808	CKS53
13	C2225	CKS54

Termination
S - Nickel Guarded, Solder

Tolerance
C - $\pm 0.25\text{pF}$; D - $\pm 0.5\text{pF}$; F - $\pm 1\%$; J - $\pm 5\%$; K - $\pm 10\%$

Capacitance Picofarad Code

Voltage
B - 50

Temperature Characteristic

KEMET Designator	Military Equivalent	EIA Equivalent	Temp. Range, °C	Capacitance Change with Temperature	
				Measured Without DC Bias Voltage	Measured With Bias (Rated Voltage)
G (Ultra Stable)	BP	C0G (NPO)	-55 to +125	± 30 ppm °C	± 30 ppm °C
X (Stable)	BX	X7R	-55 to +125	$\pm 15\%$	+15% -25%

RATINGS AND PART NUMBER REFERENCE

CAP. pF	KEMET PART NUMBER	MIL-C-123 PART NUMBER
50 VOLT - BP - C0805 SIZE (MILITARY CKS51)		
1.0	C0805Z109W5GAH	M123A10BPB1R0U
1.1	C0805Z119W5GAH	M123A10BPB1R1U
1.2	C0805Z129W5GAH	M123A10BPB1R2U
1.3	C0805Z139W5GAH	M123A10BPB1R3U
1.5	C0805Z159W5GAH	M123A10BPB1R5U
1.6	C0805Z169W5GAH	M123A10BPB1R6U
1.8	C0805Z189W5GAH	M123A10BPB1R8U
2.0	C0805Z209W5GAH	M123A10BPB2R0U
2.2	C0805Z229W5GAH	M123A10BPB2R2U
2.4	C0805Z249W5GAH	M123A10BPB2R4U
2.7	C0805Z279W5GAH	M123A10BPB2R7U
3.0	C0805Z309W5GAH	M123A10BPB3R0U
3.3	C0805Z339W5GAH	M123A10BPB3R3U
3.6	C0805Z369W5GAH	M123A10BPB3R6U
3.9	C0805Z399W5GAH	M123A10BPB3R9U
4.3	C0805Z439W5GAH	M123A10BPB4R3U
4.7	C0805Z479W5GAH	M123A10BPB4R7U
5.1	C0805Z519W5GAH	M123A10BPB5R1U
5.6	C0805Z569W5GAH	M123A10BPB5R6U
6.2	C0805Z629W5GAH	M123A10BPB6R2U
6.8	C0805Z689W5GAH	M123A10BPB6R8U
7.5	C0805Z759W5GAH	M123A10BPB7R5U
8.2	C0805Z829W5GAH	M123A10BPB8R2U
9.1	C0805Z919W5GAH	M123A10BPB9R1U
10	C0805Z100W5GAH	M123A10BPB100U
11	C0805Z110W5GAH	M123A10BPB110U
12	C0805Z120W5GAH	M123A10BPB120U
13	C0805Z130W5GAH	M123A10BPB130U
15	C0805Z150W5GAH	M123A10BPB150U
16	C0805Z160W5GAH	M123A10BPB160U
18	C0805Z180W5GAH	M123A10BPB180U
20	C0805Z200W5GAH	M123A10BPB200U
22	C0805Z220W5GAH	M123A10BPB220U
24	C0805Z240W5GAH	M123A10BPB240U
27	C0805Z270W5GAH	M123A10BPB270U
30	C0805Z300W5GAH	M123A10BPB300U
33	C0805Z330W5GAH	M123A10BPB330U
36	C0805Z360W5GAH	M123A10BPB360U
39	C0805Z390W5GAH	M123A10BPB390U
43	C0805Z430W5GAH	M123A10BPB430U
47	C0805Z470W5GAH	M123A10BPB470U
51	C0805Z510W5GAH	M123A10BPB510U
56	C0805Z560W5GAH	M123A10BPB560U
62	C0805Z620W5GAH	M123A10BPB620U
68	C0805Z680W5GAH	M123A10BPB680U
75	C0805Z750W5GAH	M123A10BPB750U
82	C0805Z820W5GAH	M123A10BPB820U
91	C0805Z910W5GAH	M123A10BPB910U
100	C0805Z101W5GAH	M123A10BPB101U
110	C0805Z111W5GAH	M123A10BPB111U
120	C0805Z121W5GAH	M123A10BPB121U
130	C0805Z131W5GAH	M123A10BPB131U
150	C0805Z151W5GAH	M123A10BPB151U
160	C0805Z161W5GAH	M123A10BPB161U
180	C0805Z181W5GAH	M123A10BPB181U
200	C0805Z201W5GAH	M123A10BPB201U
220	C0805Z221W5GAH	M123A10BPB221U
240	C0805Z241W5GAH	M123A10BPB241U
270	C0805Z271W5GAH	M123A10BPB271U
50 VOLT - BX - C0805 SIZE (MILITARY CKS51)		
330	C0805Z331K5XAH	M123A10BxB331KS
390	C0805Z391K5XAH	M123A10BxB391KS
470	C0805Z471K5XAH	M123A10BxB471KS
560	C0805Z561K5XAH	M123A10BxB561KS
680	C0805Z681K5XAH	M123A10BxB681KS
820	C0805Z821K5XAH	M123A10BxB821KS
1,000	C0805Z102K5XAH	M123A10BxB102KS
1,200	C0805Z122K5XAH	M123A10BxB122KS
1,500	C0805Z152K5XAH	M123A10BxB152KS
1,800	C0805Z182K5XAH	M123A10BxB182KS
2,200	C0805Z222K5XAH	M123A10BxB222KS
2,700	C0805Z272K5XAH	M123A10BxB272KS
3,300	C0805Z332K5XAH	M123A10BxB332KS
3,900	C0805Z392K5XAH	M123A10BxB392KS
4,700	C0805Z472K5XAH	M123A10BxB472KS
50 VOLT - BP - C1210 SIZE (MILITARY CKS52)		
300	C1210Z301W5GAH	M123A11BPPB301U
330	C1210Z331W5GAH	M123A11BPPB331U
360	C1210Z361W5GAH	M123A11BPPB361U
390	C1210Z391W5GAH	M123A11BPPB391U
430	C1210Z431W5GAH	M123A11BPPB431U
470	C1210Z471W5GAH	M123A11BPPB471U
510	C1210Z511W5GAH	M123A11BPPB511U
560	C1210Z561W5GAH	M123A11BPPB561U
620	C1210Z621W5GAH	M123A11BPPB621U
680	C1210Z681W5GAH	M123A11BPPB681U
750	C1210Z751W5GAH	M123A11BPPB751U
820	C1210Z821W5GAH	M123A11BPPB821U
910	C1210Z911W5GAH	M123A11BPPB911U
1,000	C1210Z102W5GAH	M123A11BPPB102U

CAP. pF	KEMET PART NUMBER	MIL-C-123 PART NUMBER
50 VOLT - BX - C1210 SIZE (MILITARY CKS52)		
5,600	C1210Z562K5XAH	M123A11BxB562KS
6,800	C1210Z682K5XAH	M123A11BxB682KS
8,200	C1210Z822K5XAH	M123A11BxB822KS
10,000	C1210Z103K5XAH	M123A11BxB103KS
12,000	C1210Z123K5XAH	M123A11BxB123KS
15,000	C1210Z153K5XAH	M123A11BxB153KS
18,000	C1210Z183K5XAH	M123A11BxB183KS
22,000	C1210Z223K5XAH	M123A11BxB223KS
27,000	C1210Z273K5XAH	M123A11BxB273KS
33,000	C1210Z333K5XAH	M123A11BxB333KS
47,000	C1210Z473K5XAH	M123A11BxB473KS
50 VOLT - BP - C1808 SIZE (MILITARY CKS53)		
300	C1808Z301W5GAH	M123A12BPPB301U
330	C1808Z331W5GAH	M123A12BPPB331U
360	C1808Z361W5GAH	M123A12BPPB361U
390	C1808Z391W5GAH	M123A12BPPB391U
430	C1808Z431W5GAH	M123A12BPPB431U
470	C1808Z471W5GAH	M123A12BPPB471U
510	C1808Z511W5GAH	M123A12BPPB511U
560	C1808Z561W5GAH	M123A12BPPB561U
620	C1808Z621W5GAH	M123A12BPPB621U
680	C1808Z681W5GAH	M123A12BPPB681U
750	C1808Z751W5GAH	M123A12BPPB751U
820	C1808Z821W5GAH	M123A12BPPB821U
910	C1808Z911W5GAH	M123A12BPPB911U
1,000	C1808Z102W5GAH	M123A12BPPB102U
50 VOLT - BX - C1808 SIZE (MILITARY CKS53)		
5,600	C1808Z562K5XAH	M123A12BxB562KS
6,800	C1808Z682K5XAH	M123A12BxB682KS
8,200	C1808Z822K5XAH	M123A12BxB822KS
10,000	C1808Z103K5XAH	M123A12BxB103KS
12,000	C1808Z123K5XAH	M123A12BxB123KS
15,000	C1808Z153K5XAH	M123A12BxB153KS
18,000	C1808Z183K5XAH	M123A12BxB183KS
22,000	C1808Z223K5XAH	M123A12BxB223KS
27,000	C1808Z273K5XAH	M123A12BxB273KS
33,000	C1808Z333K5XAH	M123A12BxB333KS
47,000	C1808Z473K5XAH	M123A12BxB473KS
56,000	C1808Z563K5XAH	M123A12BxB563KS
68,000	C1808Z683K5XAH	M123A12BxB683KS
82,000	C1808Z823K5XAH	M123A12BxB823KS
100,000	C1808Z104K5XAH	M123A12BxB104KS
50 VOLT - BP - C2225 SIZE (MILITARY CKS54)		
1,100	C2225Z112W5GAH	M123A13BPPB112U
1,200	C2225Z122W5GAH	M123A13BPPB122U
1,300	C2225Z132W5GAH	M123A13BPPB132U
1,500	C2225Z152W5GAH	M123A13BPPB152U
1,600	C2225Z162W5GAH	M123A13BPPB162U
1,800	C2225Z182W5GAH	M123A13BPPB182U
2,000	C2225Z202W5GAH	M123A13BPPB202U
2,200	C2225Z222W5GAH	M123A13BPPB222U
2,400	C2225Z242W5GAH	M123A13BPPB242U
2,700	C2225Z272W5GAH	M123A13BPPB272U
3,000	C2225Z302W5GAH	M123A13BPPB302U
3,300	C2225Z332W5GAH	M123A13BPPB332U
3,600	C2225Z362W5GAH	M123A13BPPB362U
3,900	C2225Z392W5GAH	M123A13BPPB392U
4,300	C2225Z432W5GAH	M123A13BPPB432U
4,700	C2225Z472W5GAH	M123A13BPPB472U
5,100	C2225Z512W5GAH	M123A13BPPB512U
5,600	C2225Z562W5GAH	M123A13BPPB562U
6,200	C2225Z622W5GAH	M123A13BPPB622U
6,800	C2225Z682W5GAH	M123A13BPPB682U
7,500	C2225Z752W5GAH	M123A13BPPB752U
8,200	C2225Z822W5GAH	M123A13BPPB822U
9,100	C2225Z912W5GAH	M123A13BPPB912U
10,000	C2225Z103W5GAH	M123A13BPPB103U
50 VOLT - BX - C2225 SIZE (MILITARY CKS54)		
120,000	C2225Z124K5XAH	M123A13BxB124KS
150,000	C2225Z154K5XAH	M123A13BxB154KS
180,000	C2225Z184K5XAH	M123A13BxB184KS
220,000	C2225Z224K5XAH	M123A13BxB224KS
270,000	C2225Z274K5XAH	M123A13BxB274KS
330,000	C2225Z334K5XAH	M123A13BxB334KS
390,000	C2225Z394K5XAH	M123A13BxB394KS
470,000	C2225Z474K5XAH	M123A13BxB474KS

To complete the part numbers, insert the following tolerances:

- (1) C, $\pm 0.25\text{pF}$; D, $\pm 0.5\text{pF}$
- (2) C, $\pm 0.25\text{pF}$; J, $\pm 5\%$; K, $\pm 10\%$
- (3) F, $\pm 1\%$; J, $\pm 5\%$; K, $\pm 10\%$

HIGH RELIABILITY — GR900

GR900 capacitors are intended for use in any application where the chance of failure must be reduced to the lowest possible level. While any well-made multilayer ceramic capacitor is an inherently reliable device, GR900 capacitors receive special attention in all phases of manufacture including:

- Raw Materials Selection
- Special Designs
- Clean Room Production
- Individual Batch Testing
- Ultrasonic Scanning (when applicable)
- Singular Batch Identity is Maintained
- Destructive Physical Analysis

These parts are well worth the added investment in comparison to the cost of a device or system failure.

Typical applications include:

1. Medical: heart pacemakers, pain control devices, life signs monitoring, eyesight improvement and electroencephalographic equipment.
2. Aerospace: space exploration (Viking, Apollo, Venus Lander, etc.); Communications Satellites; Space Shuttle/IUS; Sky Lab.

SCREENING AND SAMPLE TESTS

Each batch receives the following testing/inspections:

Preliminary:

1. Destructive Physical Analysis: (DPA) - A sample is pulled from each lot and examined per EIA-469 and KEMET's strict internal void and delamination criteria. Sampling plan is per MIL-C-123.
2. Ultrasonic Scanning - May be performed on batches failing to meet the DPA criteria for removal of marginal product. Not required on each lot.

Group A

1. Thermal Shock — Materials used in the construction of multilayer ceramic capacitors possess various thermal coefficients of expansion. To assure maximum uniformity, each part is temperature cycled in accordance to MIL-STD-202, Method 107, Condition A with Step 3 being 125°C. Number of cycles shall be 20 (100% of lot).

2. Voltage Conditioning — One of the most strenuous environments for any capacitor is the high temperature/high voltage test. All units are subject to twice-rated voltage to the units at the maximum rated temperature of 125°C for a minimum of 168 hours and a maximum of 264 hours. The voltage conditioning may be terminated at any time during 168 hours to 264 hours time interval that confirmed failures meet the requirements of the PDA during the last 48 hours of 1 unit or .4% (100% of lot).

Optional Voltage Conditioning (Accelerated Voltage Conditioning) — All conditions of the standard voltage conditioning apply with the exception of increased voltage and decreased test time. Refer to MIL-C-123 for the proper formula.

***Step 5 is performed on chips at this point (100% of lot).**

3. Dielectric Withstanding Voltage — 250% of the dc rated voltage at 25°C (100% of lot).

4. Insulation Resistance — The 25°C measurement with rated voltage applied shall be the lesser of 100,000 megohms or 1000 megohm-microfarads (100% of lot).

***5. Insulation Resistance** — The 125°C measurement with rated voltage applied shall be the lesser of 10,000 megohms or 100 megohm-microfarads (100% of lot). For chips, 125°C IR is performed prior to Step 3 above.

6. Storage at 150°C for 2 hours minimum without voltage applied followed by a 12-hour minimum stabilization period (temperature characteristic BX only).

7. Capacitance — Shall be within specified tolerance at 25°C (100% of lot). (Aging phenomenon is taken into account for BX dielectric to obtain capacitance.)

8. Dissipation Factor — Shall not exceed 2.5% for X7R (BX) dielectric, 0.15% for NPO (BP) dielectric at 25°C. (100% of lot.)

9. Percent Defective Allowable (PDA) — The overall PDA is 8% for parts outside the MIL-C-123 values. The PDA is per MIL-C-123 for all parts that are valid MIL-C-123 values. The PD includes steps 1 through 8 above with the following exceptions. Capacitance exclusion - capacitance values no more than 5% or .5pF, whichever is greater for BX characteristic or 1% or .3pF, whichever is greater for BP characteristic beyond specified tolerance limit, shall be removed from the lot but shall not be considered defective for determination of the PD.

Insulation Resistance at 25°C — Product which is not acceptable for twice the military limit but is acceptable per the military limit, is removed from the lot but shall not be considered defective for determination of the PD.

10. Visual and Mechanical Examination — Performed per MIL-C-123 criteria.

11. Radiographic Examination (Leaded Devices Only) — Radial devices receive a one-plane X-ray.

12. Destructive Physical Analysis (DPA) — A sample is examined on each lot per EIA-469. Sampling Plan is per MIL-C-123.

STANDARD PACKAGING


All products are packaged in trays except C512 capacitors which are packaged 1 piece per bag.

DATA PACKAGE

A data package is sent with each shipment which contains:

1. Final Destructive Physical Analysis (DPA) report.
2. Certificate of Compliance stating that the parts meet all applicable requirements of the appropriate military specification to the best failure level to which KEMET is approved.

CAPACITOR OUTLINE DRAWINGS



DIMENSIONS — INCHES & (MILLIMETERS) RADIAL LEAD

KEMET CASE SIZE	H HEIGHT	L LENGTH	W WIDTH	S LEAD SPACING	MILITARY STYLES		
					MIL-C-20	MIL-C-39014	MIL-C-123
C052	.190 ± .010 (4.83 ± .25)	.190 ± .010 (4.83 ± .25)	.090 ± .010 (2.29 ± .25)	.200 ± .015 (5.08 ± .38)	CCR05	CKR05	CKS05
C062	.290 ± .010 (7.37 ± .25)	.290 ± .010 (7.37 ± .25)	.090 ± .010 (2.29 ± .25)	.200 ± .015 (5.08 ± .38)	CCR06	CKR06	CKS06
C512	.480 ± .020 (12.19 ± .51)	.480 ± .020 (12.19 ± .51)	.140 ± .010 (3.56 ± .25)	.400 ± .020 (10.16 ± .51)	CCR07	—	CKS07

C 052 B 223 K 1 X 5 C A

MONOLITHIC CERAMIC CAPACITORS

PHYSICAL DIMENSIONS
(See above)

HI REL SPECIFICATIONS APPLY:
B—Leaded devices

CAPACITANCE PICOFARAD CODE
First two digits are significant figures of capacitance value and third digit is the number of zeros to follow in stating capacitance in picofarads. For example, "223" is 22,000 pF. The third-digit number "9" indicates a divisor of 10; for example, "229" is 2.2 pF.

CAPACITANCE TOLERANCE
M — ±20% G — ±2% (G(BP) Temperature Characteristic Only)
K — ±10% F — ±1% (G(BP) Temperature Characteristic Only)
J — ±5% *D—±0.5 pF (G(BP) Temperature Characteristic Only)
 *C—±0.25 pF (G(BP) Temperature Characteristic Only)

FAILURE RATE
A—Standard — Not Applicable

LEAD MATERIAL
C — Standard —
Radial: solder coated copper

INTERNAL CONSTRUCTION
5— Ultra-High Temperature Solder

TEMPERATURE CHARACTERISTICS
(See table below)


RATED VOLTAGE
1 — 100
2 — 200
5 — 50

*These tolerances available only for 1.0 through 9.1 pF capacitors.

TEMPERATURE CHARACTERISTICS CAPACITANCE CHANGE WITH TEMPERATURE -55° TO +125°C

PART NUMBER LETTER	WITHOUT D.C. BIAS	WITH RATED D.C. VOLTAGE APPLIED	OTHER NOMENCLATURE		
			EIA	MILITARY	COMMON
G	±30ppm/°C	±30ppm/°C	COG	CG,BP	NPO
X	±15%	+15%, -25%	X7R	BX	—

CAPACITOR MARKINGS



RATINGS & PART NUMBER REFERENCE

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP - STYLE C052	
1.0	C052B109(4)2G5CA
1.1	C052B119(4)2G5CA
1.2	C052B129(4)2G5CA
1.5	C052B159(4)2G5CA
1.8	C052B189(4)2G5CA
2.0	C052B209(4)2G5CA
2.2	C052B229(4)2G5CA
2.4	C052B249(4)2G5CA
2.7	C052B279(4)2G5CA
3.0	C052B309(4)2G5CA
3.3	C052B339(4)2G5CA
3.6	C052B369(4)2G5CA
3.9	C052B399(4)2G5CA
4.3	C052B439(4)2G5CA
4.7	C052B479(4)2G5CA
5.1	C052B519(4)2G5CA
5.6	C052B569(4)2G5CA
6.2	C052B629(4)2G5CA
6.8	C052B689(4)2G5CA
7.5	C052B759(4)2G5CA
8.2	C052B829(4)2G5CA
9.1	C052B919(4)2G5CA
10.0	C052B100(4)2G5CA
11.0	C052B110(4)2G5CA
12.0	C052B120(4)2G5CA
13.0	C052B130(4)2G5CA
15.0	C052B150(4)2G5CA
16.0	C052B160(4)2G5CA
18.0	C052B180(4)2G5CA
20.0	C052B200(4)2G5CA
22.0	C052B220(4)2G5CA
24.0	C052B240(4)2G5CA
27.0	C052B270(4)2G5CA
30.0	C052B300(4)2G5CA

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP - STYLE C052 (Cont'd)	
33.0	C052B330(4)2G5CA
36.0	C052B360(4)2G5CA
39.0	C052B390(4)2G5CA
43.0	C052B430(4)2G5CA
47.0	C052B470(4)2G5CA
51.0	C052B510(4)2G5CA
56.0	C052B560(4)2G5CA
62.0	C052B620(4)2G5CA
68.0	C052B680(4)2G5CA
75.0	C052B750(4)2G5CA
82.0	C052B820(4)2G5CA
91.0	C052B910(4)2G5CA
100	C052B101(4)2G5CA
110	C052B111(4)2G5CA
120	C052B121(4)2G5CA
130	C052B131(4)2G5CA
150	C052B151(4)2G5CA
160	C052B161(4)2G5CA
180	C052B181(4)2G5CA
200	C052B201(4)2G5CA
220	C052B221(4)2G5CA
240	C052B241(4)2G5CA
270	C052B271(4)2G5CA
300	C052B301(4)2G5CA
330	C052B331(4)2G5CA
360	C052B361(4)2G5CA
390	C052B391(4)2G5CA
430	C052B431(4)2G5CA
470	C052B471(4)2G5CA
510	C052B511(4)2G5CA
560	C052B561(4)2G5CA
620	C052B621(4)2G5CA
680	C052B681(4)2G5CA
750	C052B751(4)2G5CA

(1) Complete KEMET part number by inserting capacitance tolerance, as applicable as shown in ordering information on page 12

BP CAPACITANCE TOLERANCE: ±1%, ±2%, ±5%, ±10%, ±20% (±0.5pF & ±0.25pF tolerances available 1.0 thru 9.1pF only) TEMPERATURE CHARACTERISTIC "G"

BX CAPACITANCE TOLERANCE: ±5%, ±10%, ±20% TEMPERATURE CHARACTERISTIC "X"

(2) Capacitance values shown above are standard. Other capacitance values are available upon request.

RATINGS & PART NUMBER REFERENCE

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP - STYLE C052 (Cont'd)	
820	C052B821 μ 2G5CA
910	C052B911 μ 2G5CA
1000	C052B102 μ 2G5CA
1100	C052B112 μ 2G5CA
1200	C052B122 μ 2G5CA
1300	C052B132 μ 2G5CA
1500	C052B152 μ 2G5CA
100 VOLT - BP - STYLE C052	
1600	C052B162 μ 1G5CA
1800	C052B182 μ 1G5CA
2000	C052B202 μ 1G5CA
2200	C052B222 μ 1G5CA
2400	C052B242 μ 1G5CA
2700	C052B272 μ 1G5CA
3000	C052B302 μ 1G5CA
3300	C052B332 μ 1G5CA
3600	C052B362 μ 1G5CA
3900	C052B392 μ 1G5CA
4300	C052B432 μ 1G5CA
4700	C052B472 μ 1G5CA
5100	C052B512 μ 1G5CA
5600	C052B562 μ 1G5CA
200 VOLT - BX - STYLE C052	
470	C052B471 μ 2X5CA
560	C052B561 μ 2X5CA
680	C052B681 μ 2X5CA
820	C052B821 μ 2X5CA
1000	C052B102 μ 2X5CA
1200	C052B122 μ 2X5CA
1500	C052B152 μ 2X5CA
1800	C052B182 μ 2X5CA
2200	C052B222 μ 2X5CA
2700	C052B272 μ 2X5CA
3300	C052B332 μ 2X5CA
3900	C052B392 μ 2X5CA
4700	C052B472 μ 2X5CA
5600	C052B562 μ 2X5CA
6800	C052B682 μ 2X5CA
8200	C052B822 μ 2X5CA
10,000	C052B103 μ 2X5CA
12,000	C052B123 μ 2X5CA
15,000	C052B153 μ 2X5CA
100 VOLT - BX - STYLE C052	
18,000	C052B183 μ 1X5CA
22,000	C052B223 μ 1X5CA
27,000	C052B273 μ 1X5CA
33,000	C052B333 μ 1X5CA
39,000	C052B393 μ 1X5CA
47,000	C052B473 μ 1X5CA
50 VOLT - BX - STYLE C052	
56,000	C052B563 μ 5X5CA
68,000	C052B683 μ 5X5CA
82,000	C052B823 μ 5X5CA
100,000	C052B104 μ 5X5CA
120,000	C052B124 μ 5X5CA
150,000	C052B154 μ 5X5CA
200 VOLT - BP - STYLE C062	
330	C062B331 μ 2G5CA
360	C062B361 μ 2G5CA
390	C062B391 μ 2G5CA
430	C062B431 μ 2G5CA
470	C062B471 μ 2G5CA
510	C062B511 μ 2G5CA

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP - STYLE C062 (Cont'd)	
560	C062B561 μ 2G5CA
620	C062B621 μ 2G5CA
680	C062B681 μ 2G5CA
750	C062B751 μ 2G5CA
820	C062B821 μ 2G5CA
910	C062B911 μ 2G5CA
1000	C062B102 μ 2G5CA
1100	C062B112 μ 2G5CA
1200	C062B122 μ 2G5CA
1300	C062B132 μ 2G5CA
1500	C062B152 μ 2G5CA
1600	C062B162 μ 2G5CA
1800	C062B182 μ 2G5CA
2000	C062B202 μ 2G5CA
2200	C062B222 μ 2G5CA
2400	C062B242 μ 2G5CA
2700	C062B272 μ 2G5CA
3000	C062B302 μ 2G5CA
3300	C062B332 μ 2G5CA
3600	C062B362 μ 2G5CA
3900	C062B392 μ 2G5CA
4700	C062B472 μ 2G5CA
5100	C062B512 μ 2G5CA
5600	C062B562 μ 2G5CA
6200	C062B622 μ 2G5CA
6800	C062B682 μ 2G5CA
100 VOLT - BP - STYLE C062	
7500	C062B752 μ 1G5CA
8200	C062B822 μ 1G5CA
9100	C062B912 μ 1G5CA
10,000	C062B103 μ 1G5CA
11,000	C062B113 μ 1G5CA
12,000	C062B123 μ 1G5CA
13,000	C062B133 μ 1G5CA
15,000	C062B153 μ 1G5CA
16,000	C062B163 μ 1G5CA
18,000	C062B183 μ 1G5CA
20,000	C062B203 μ 1G5CA
22,000	C062B223 μ 1G5CA
200 VOLT - BX - STYLE C062	
3300	C062B332 μ 2X5CA
3900	C062B392 μ 2X5CA
4700	C062B472 μ 2X5CA
5600	C062B562 μ 2X5CA
6800	C062B682 μ 2X5CA
8200	C062B822 μ 2X5CA
10,000	C062B103 μ 2X5CA
12,000	C062B123 μ 2X5CA
15,000	C062B153 μ 2X5CA
18,000	C062B183 μ 2X5CA
22,000	C062B223 μ 2X5CA
27,000	C062B273 μ 2X5CA
33,000	C062B333 μ 2X5CA
39,000	C062B393 μ 2X5CA
47,000	C062B473 μ 2X5CA
56,000	C062B563 μ 2X5CA
68,000	C062B683 μ 2X5CA
100 VOLT - BX - STYLE C062	
82,000	C062B823 μ 1X5CA
100,000	C062B104 μ 1X5CA
120,000	C062B124 μ 1X5CA
150,000	C062B154 μ 1X5CA
180,000	C062B184 μ 1X5CA
220,000	C062B224 μ 1X5CA

(1) Complete KEMET part number by inserting capacitance tolerance, as applicable as shown in ordering information on page 12. **BP CAPACITANCE TOLERANCE:** $\pm 1\%$, $\pm 2\%$, $\pm 5\%$, $\pm 10\%$, $\pm 20\%$ ($\pm 0.5\text{pF}$ & $\pm 0.25\text{pF}$ tolerances available 1.0 thru 9.1pF only) **TEMPERATURE CHARACTERISTIC "G" BX CAPACITANCE TOLERANCE:** $\pm 5\%$, $\pm 10\%$, $\pm 20\%$ **TEMPERATURE CHARACTERISTIC "X"** (2) Capacitance values shown above are standard. Other capacitance values are available upon request.

RATINGS & PART NUMBER REFERENCE

CAPACITANCE pF	KEMET PART NUMBER
50 VOLT - BX - STYLE C062	
270,000	C062B274(1)5X5CA
330,000	C062B334(1)5X5CA
390,000	C062B394(1)5X5CA
470,000	C062B474(1)5X5CA
560,000	C062B564(1)5X5CA
680,000	C062B684(1)5X5CA
820,000	C062B824(1)5X5CA
1,000,000	C062B105(1)5X5CA
200 VOLT - BP- STYLE C512	
2000	C512B202(1)2G5CA
2200	C512B222(1)2G5CA
2400	C512B242(1)2G5CA
2700	C512B272(1)2G5CA
3000	C512B302(1)2G5CA
3300	C512B332(1)2G5CA
3600	C512B362(1)2G5CA
3900	C512B392(1)2G5CA
4300	C512B432(1)2G5CA
4700	C512B472(1)2G5CA
5600	C512B562(1)2G5CA
6800	C512B682(1)2G5CA
8200	C512B822(1)2G5CA
10,000	C512B103(1)2G5CA
12,000	C512B123(1)2G5CA
15,000	C512B153(1)2G5CA
18,000	C512B183(1)2G5CA
22,000	C512B223(1)2G5CA
27,000	C512B273(1)2G5CA
33,000	C512B333(1)2G5CA
100 VOLT - BP- STYLE C512	
39,000	C512B393(1)1G5CA
47,000	C512B473(1)2G5CA
56,000	C512B563(1)1G5CA
68,000	C512B683(1)1G5CA
82,000	C512B823(1)1G5CA
100,000	C512B104(1)1G5CA
50 VOLT - BP- STYLE C512	
120,000	C512B124(1)5G5CA
150,000	C512B154(1)5G5CA

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BX - STYLE C512	
39,000	C512B393(1)2X5CA
47,000	C512B473(1)2X5CA
56,000	C512B563(1)2X5CA
68,000	C512B683(1)2X5CA
82,000	C512B823(1)2X5CA
100,000	C512B104(1)2X5CA
120,000	C512B124(1)2X5CA
150,000	C512B154(1)2X5CA
180,000	C512B184(1)2X5CA
220,000	C512B224(1)2X5CA
270,000	C512B274(1)2X5CA
330,000	C512B334(1)2X5CA
390,000	C512B394(1)2X5CA
100 VOLT - BX - STYLE C512	
470,000	C512B474(1)1X5CA
560,000	C512B564(1)1X5CA
680,000	C512B684(1)1X5CA
820,000	C512B824(1)1X5CA
1,000,000	C512B105(1)1X5CA
50 VOLT - BX - STYLE C512	
1,200,000	C512B125(1)5X5CA
1,500,000	C512B155(1)5X5CA
2,000,000	C512B205(1)5X5CA
2,200,000	C512B225(1)5X5CA
3,300,000	C512B335(1)5X5CA


(1) Complete KEMET part number by inserting capacitance tolerance, as applicable as shown in ordering information on page 12.

BP CAPACITANCE TOLERANCE: $\pm 1\%$, $\pm 2\%$, $\pm 5\%$, $\pm 10\%$, $\pm 20\%$ ($\pm 0.5\text{pF}$ & $\pm 0.25\text{pF}$ tolerances available 1.0 thru 9.1pF only) TEMPERATURE CHARACTERISTIC "G"

BX CAPACITANCE TOLERANCE: $\pm 5\%$, $\pm 10\%$, $\pm 20\%$ TEMPERATURE CHARACTERISTIC "X"

(2) Capacitance values shown above are standard. Other capacitance values are available upon request.

CAPACITOR OUTLINE DRAWINGS



* Add .38mm (.015") to the positive width and thickness tolerance dimensions and .64mm (.025") to the positive length tolerance dimension for Solderguard I.

DIMENSIONS — MILLIMETERS (INCHES)

Size Code	L Length	W Width	T Thickness Max.
0805	2.03 (.080) $\pm$ 0.38 (.015)	1.27 (.050) $\pm$ 0.38 (.015)	1.4 (.055)
1005	2.56 (.100) $\pm$ 0.38 (.015)	1.27 (.050) $\pm$ 0.38 (.015)	1.5 (.059)
1206	3.07 (.120) $\pm$ 0.38 (.015)	1.52 (.060) $\pm$ 0.38 (.015)	1.6 (.065)
1210	3.07 (.120) $\pm$ 0.38 (.015)	2.56 (.100) $\pm$ 0.38 (.015)	1.6 (.065)
1805	4.57 (.180) $\pm$ 0.38 (.015)	1.27 (.050) $\pm$ 0.38 (.015)	1.4 (.055)
1808	4.57 (.180) $\pm$ 0.38 (.015)	2.03 (.080) $\pm$ 0.38 (.015)	1.6 (.065)
1812	4.57 (.180) $\pm$ 0.38 (.015)	3.18 (.125) $\pm$ 0.38 (.015)	2.03 (.080)
1825	4.57 (.180) $\pm$ 0.38 (.015)	6.35 (.250) $\pm$ 0.38 (.015)	2.03 (.080)
2225	5.59 (.220) $\pm$ 0.38 (.015)	6.35 (.250) $\pm$ 0.38 (.015)	2.03 (.080)

ORDERING INFORMATION

The diagram shows a 5-digit capacitor code: **C 0805 A 103 K 5 X A C**. Each digit is connected by a line to its corresponding definition:

- C**: CERAMIC
- 0805**: SIZE CODE (See table above)
- A**: SPECIFICATION (A — KEMET GR900 (CHIPS))
- 103**: CAPACITANCE CODE (Expressed in Picofarads (pF). First two digit-significant figures. Third digit-number of zeros. (Use 9 for 1.0 thru 9.9 pF. Example: 2.2 pF — 229).)
- K**: CAPACITANCE TOLERANCE (M — ±20%, K — ±10%, J — ±5%, G — ±2% (G(BP) Temperature Characteristic Only), F — ±1% (G(BP) Temperature Characteristic Only), *D — ±0.5 pF (G(BP) Temperature Characteristic Only), *C — ±0.25 pF (G(BP) Temperature Characteristic Only). *These tolerances available only for 1.0 through 10 pF capacitors.)
- 5**: VOLTAGE (1—100, 2—200, 5—50)
- X**: END METALLIZATION (C—Tin-Coated, Final (SolderGuard II), H—Soder-Coated, Final (SolderGuard I))
- A**: FAILURE RATE LEVEL (%/1,000 HOURS) (A—Standard—Not applicable)
- C**: TEMPERATURE CHARACTERISTIC (Designated by Capacitance Change over Temperature Range. G—BP (±30 PPM/°C), X—BX (±15%, +15%, -25% with bias.))

RATINGS AND PART NUMBER REFERENCE STYLE C0805

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
1.0	C0805A109(1)2GA(2)
1.1	C0805A119(1)2GA(2)
1.2	C0805A129(1)2GA(2)
1.5	C0805A159(1)2GA(2)
1.6	C0805A169(1)2GA(2)
1.8	C0805A189(1)2GA(2)
2.0	C0805A209(1)2GA(2)
2.2	C0805A229(1)2GA(2)
2.4	C0805A249(1)2GA(2)
2.7	C0805A279(1)2GA(2)
3.0	C0805A309(1)2GA(2)
3.3	C0805A339(1)2GA(2)
3.6	C0805A369(1)2GA(2)
3.9	C0805A399(1)2GA(2)
4.3	C0805A439(1)2GA(2)
4.7	C0805A479(1)2GA(2)
5.1	C0805A519(1)2GA(2)
5.6	C0805A569(1)2GA(2)
6.2	C0805A629(1)2GA(2)
6.8	C0805A689(1)2GA(2)
7.5	C0805A759(1)2GA(2)
8.2	C0805A829(1)2GA(2)
9.1	C0805A919(1)2GA(2)
10.0	C0805A100(1)2GA(2)
11.0	C0805A110(1)2GA(2)
12.0	C0805A120(1)2GA(2)
13.0	C0805A130(1)2GA(2)
15.0	C0805A150(1)2GA(2)
16.0	C0805A160(1)2GA(2)
18.0	C0805A180(1)2GA(2)
20.0	C0805A200(1)2GA(2)
22.0	C0805A220(1)2GA(2)
24.0	C0805A240(1)2GA(2)
27.0	C0805A270(1)2GA(2)
30.0	C0805A300(1)2GA(2)
33.0	C0805A330(1)2GA(2)
36.0	C0805A360(1)2GA(2)
39.0	C0805A390(1)2GA(2)
43.0	C0805A430(1)2GA(2)
47.0	C0805A470(1)2GA(2)
51.0	C0805A510(1)2GA(2)
56.0	C0805A560(1)2GA(2)
62.0	C0805A620(1)2GA(2)
75.0	C0805A750(1)2GA(2)
82.0	C0805A820(1)2GA(2)
91.0	C0805A910(1)2GA(2)
100	C0805A101(1)2GA(2)
110	C0805A111(1)2GA(2)
120	C0805A121(1)2GA(2)
130	C0805A131(1)2GA(2)
150	C0805A151(1)2GA(2)
160	C0805A161(1)2GA(2)
180	C0805A181(1)2GA(2)
200	C0805A201(1)2GA(2)
220	C0805A221(1)2GA(2)
100 VOLT - BP	
240	C0805A241(1)1GA(2)
270	C0805A271(1)1GA(2)
300	C0805A301(1)1GA(2)
330	C0805A331(1)1GA(2)
360	C0805A361(1)1GA(2)
390	C0805A391(1)1GA(2)
430	C0805A431(1)1GA(2)
470	C0805A471(1)1GA(2)
50 VOLT - BP	
510	C0805A511(1)5GA(2)
560	C0805A561(1)5GA(2)

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BX	
180	C0805A181(1)2XA(2)
220	C0805A221(1)2XA(2)
270	C0805A271(1)2XA(2)
330	C0805A331(1)2XA(2)
390	C0805A391(1)2XA(2)
470	C0805A471(1)2XA(2)
560	C0805A561(1)2XA(2)
680	C0805A681(1)2XA(2)
820	C0805A821(1)2XA(2)
100 VOLT - BX	
1000	C0805A102(1)1XA(2)
1200	C0805A122(1)1XA(2)
1500	C0805A152(1)1XA(2)
1800	C0805A182(1)1XA(2)
2200	C0805A222(1)1XA(2)
2700	C0805A272(1)1XA(2)
3300	C0805A332(1)1XA(2)
3900	C0805A392(1)1XA(2)
4700	C0805A472(1)1XA(2)
50 VOLT - BX	
5600	C0805A562(1)5XA(2)
6800	C0805A682(1)5XA(2)
8200	C0805A822(1)5XA(2)
10,000	C0805A103(1)5XA(2)

(1) Complete KEMET part number by inserting capacitance tolerance, as applicable as shown in ordering information on page 16.

BP CAPACITANCE TOLERANCE: ±1%, ±2%, ±5%, ±10%, ±20% (±0.5pF & ±0.25pF tolerances available 1.0 thru 10pF only) TEMPERATURE CHARACTERISTIC "G"

BX CAPACITANCE TOLERANCE: ±5%, ±10%, ±20% TEMPERATURE CHARACTERISTIC "X"

(2) Complete part number by inserting end Metallization, as applicable as shown in ordering information on page 16.

C—Tin-Coated, Final (SolderGuard II)

H—Solder-Coated, Final (SolderGuard I)

RATINGS AND PART NUMBER REFERENCE

STYLE C1005

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
1.0	C1005A109(1)2GA(2)
1.1	C1005A119(1)2GA(2)
1.2	C1005A129(1)2GA(2)
1.5	C1005A159(1)2GA(2)
1.6	C1005A169(1)2GA(2)
1.8	C1005A189(1)2GA(2)
2.0	C1005A209(1)2GA(2)
2.2	C1005A229(1)2GA(2)
2.4	C1005A249(1)2GA(2)
2.7	C1005A279(1)2GA(2)
3.0	C1005A309(1)2GA(2)
3.3	C1005A339(1)2GA(2)
3.6	C1005A369(1)2GA(2)
3.9	C1005A399(1)2GA(2)
4.3	C1005A439(1)2GA(2)
4.7	C1005A479(1)2GA(2)
5.1	C1005A519(1)2GA(2)
5.6	C1005A569(1)2GA(2)
6.8	C1005A689(1)2GA(2)
7.5	C1005A759(1)2GA(2)
8.2	C1005A829(1)2GA(2)
9.1	C1005A919(1)2GA(2)
10.0	C1005A100(1)2GA(2)
11.0	C1005A110(1)2GA(2)
12.0	C1005A120(1)2GA(2)
13.0	C1005A130(1)2GA(2)
15.0	C1005A150(1)2GA(2)
16.0	C1005A160(1)2GA(2)
18.0	C1005A180(1)2GA(2)
20.0	C1005A200(1)2GA(2)
22.0	C1005A220(1)2GA(2)
24.0	C1005A240(1)2GA(2)
27.0	C1005A270(1)2GA(2)
30.0	C1005A300(1)2GA(2)
33.0	C1005A330(1)2GA(2)
36.0	C1005A360(1)2GA(2)
39.0	C1005A390(1)2GA(2)
43.0	C1005A430(1)2GA(2)
47.0	C1005A470(1)2GA(2)
51.0	C1005A510(1)2GA(2)
56.0	C1005A560(1)2GA(2)
62.0	C1005A620(1)2GA(2)
75.0	C1005A750(1)2GA(2)
82.0	C1005A820(1)2GA(2)
91.0	C1005A910(1)2GA(2)
100	C1005A101(1)2GA(2)
110	C1005A111(1)2GA(2)
120	C1005A121(1)2GA(2)
130	C1005A131(1)2GA(2)
150	C1005A151(1)2GA(2)
160	C1005A161(1)2GA(2)

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
180	C1005A181(1)2GA(2)
200	C1005A201(1)2GA(2)
220	C1005A221(1)2GA(2)
240	C1005A241(1)2GA(2)
270	C1005A271(1)2GA(2)
300	C1005A301(1)2GA(2)
330	C1005A331(1)2GA(2)
360	C1005A361(1)2GA(2)
390	C1005A391(1)2GA(2)
430	C1005A431(1)2GA(2)
470	C1005A471(1)2GA(2)
100 VOLT - BP	
510	C1005A511(1)1GA(2)
560	C1005A561(1)1GA(2)
620	C1005A621(1)1GA(2)
680	C1005A681(1)1GA(2)
750	C1005A751(1)1GA(2)
820	C1005A821(1)1GA(2)
50 VOLT - BP	
910	C1005A911(1)5GA(2)
1000	C1005A102(1)5GA(2)
1100	C1005A112(1)5GA(2)
1200	C1005A122(1)5GA(2)
200 VOLT - BX	
330	C1005A331(1)2XA(2)
390	C1005A391(1)2XA(2)
470	C1005A471(1)2XA(2)
560	C1005A561(1)2XA(2)
680	C1005A681(1)2XA(2)
820	C1005A821(1)2XA(2)
1000	C1005A102(1)2XA(2)
1200	C1005A122(1)2XA(2)
1500	C1005A152(1)2XA(2)
1800	C1005A182(1)2XA(2)
100 VOLT - BX	
2200	C1005A222(1)1XA(2)
2700	C1005A272(1)1XA(2)
3300	C1005A332(1)1XA(2)
3900	C1005A392(1)1XA(2)
4700	C1005A472(1)1XA(2)
5600	C1005A562(1)1XA(2)
6800	C1005A682(1)1XA(2)
8200	C1005A822(1)1XA(2)
10,000	C1005A103(1)1XA(2)
50 VOLT - BX	
12,000	C1005A123(1)5XA(2)
15,000	C1005A153(1)5XA(2)
18,000	C1005A183(1)5XA(2)
22,000	C1005A223(1)5XA(2)

RATINGS AND PART NUMBER REFERENCE

STYLE C1206

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
10.0	C1206A100(1)2GA(2)
11.0	C1206A110(1)2GA(2)
12.0	C1206A120(1)2GA(2)
13.0	C1206A130(1)2GA(2)
15.0	C1206A150(1)2GA(2)
16.0	C1206A160(1)2GA(2)
18.0	C1206A180(1)2GA(2)
20.0	C1206A200(1)2GA(2)
22.0	C1206A220(1)2GA(2)
24.0	C1206A240(1)2GA(2)

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
27.0	C1206A270(1)2GA(2)
30.0	C1206A300(1)2GA(2)
33.0	C1206A330(1)2GA(2)
36.0	C1206A360(1)2GA(2)
39.0	C1206A390(1)2GA(2)
43.0	C1206A430(1)2GA(2)
47.0	C1206A470(1)2GA(2)
51.0	C1206A510(1)2GA(2)
56.0	C1206A560(1)2GA(2)
62.0	C1206A620(1)2GA(2)

(1) Complete KEMET part number by inserting capacitance tolerance, as applicable as shown in ordering information on page 16.
BP CAPACITANCE TOLERANCE: ±1%, ±2%, ±5%, ±10%, ±20% (±0.5pF & ±0.25pF tolerances available 1.0 thru 10pF only) **TEMPERATURE CHARACTERISTIC "G"**
BX CAPACITANCE TOLERANCE: ±5%, ±10%, ±20% **TEMPERATURE CHARACTERISTIC "X"**
 (2) Complete part number by inserting end Metallization, as applicable as shown in ordering information on page 16.
 C—Tin-Coated, Final (SolderGuard II)
 H—Solder-Coated, Final (SolderGuard I)

RATINGS AND PART NUMBER REFERENCE STYLE C1206 (continued)

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
68.0	C1206A680(1)2GA(2)
75.0	C1206A750(1)2GA(2)
82.0	C1206A820(1)2GA(2)
91.0	C1206A910(1)2GA(2)
100	C1206A101(1)2GA(2)
110	C1206A111(1)2GA(2)
120	C1206A121(1)2GA(2)
130	C1206A131(1)2GA(2)
150	C1206A151(1)2GA(2)
160	C1206A161(1)2GA(2)
180	C1206A181(1)2GA(2)
200	C1206A201(1)2GA(2)
220	C1206A221(1)2GA(2)
240	C1206A241(1)2GA(2)
270	C1206A271(1)2GA(2)
300	C1206A301(1)2GA(2)
330	C1206A331(1)2GA(2)
360	C1206A361(1)2GA(2)
390	C1206A391(1)2GA(2)
430	C1206A431(1)2GA(2)
470	C1206A471(1)2GA(2)
100 VOLT - BP	
510	C1206A511(1)1GA(2)
560	C1206A561(1)1GA(2)
620	C1206A621(1)1GA(2)
680	C1206A681(1)1GA(2)
750	C1206A751(1)1GA(2)
820	C1206A821(1)1GA(2)
910	C1206A911(1)1GA(2)
1000	C1206A102(1)1GA(2)
1100	C1206A112(1)1GA(2)
1200	C1206A122(1)1GA(2)
1300	C1206A132(1)1GA(2)
1500	C1206A152(1)1GA(2)
1600	C1206A162(1)1GA(2)

CAPACITANCE pF	KEMET PART NUMBER
50 VOLT - BP	
1800	C1206A182(1)5GA(2)
2000	C1206A202(1)5GA(2)
200 VOLT - BX	
470	C1206A471(1)2XA(2)
560	C1206A561(1)2XA(2)
680	C1206A681(1)2XA(2)
820	C1206A821(1)2XA(2)
1000	C1206A102(1)2XA(2)
1200	C1206A122(1)2XA(2)
1500	C1206A152(1)2XA(2)
1800	C1206A182(1)2XA(2)
2200	C1206A222(1)2XA(2)
2700	C1206A272(1)2XA(2)
3300	C1206A332(1)2XA(2)
3900	C1206A392(1)2XA(2)
4700	C1206A472(1)2XA(2)
100 VOLT - BX	
5600	C1206A562(1)1XA(2)
6800	C1206A682(1)1XA(2)
8200	C1206A822(1)1XA(2)
10,000	C1206A103(1)1XA(2)
12,000	C1206A123(1)1XA(2)
15,000	C1206A153(1)1XA(2)
50 VOLT - BX	
18,000	C1206A183(1)5XA(2)
22,000	C1206A223(1)5XA(2)
27,000	C1206A273(1)5XA(2)
33,000	C1206A333(1)5XA(2)
39,000	C1206A393(1)5XA(2)
47,000	C1206A473(1)5XA(2)

RATINGS AND PART NUMBER REFERENCE STYLE C1210

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
10.0	C1210A100(1)2GA(2)
11.0	C1210A110(1)2GA(2)
12.0	C1210A120(1)2GA(2)
13.0	C1210A130(1)2GA(2)
15.0	C1210A150(1)2GA(2)
16.0	C1210A160(1)2GA(2)
18.0	C1210A180(1)2GA(2)
20.0	C1210A200(1)2GA(2)
22.0	C1210A220(1)2GA(2)
24.0	C1210A240(1)2GA(2)
27.0	C1210A270(1)2GA(2)
30.0	C1210A300(1)2GA(2)
33.0	C1210A330(1)2GA(2)
36.0	C1210A360(1)2GA(2)
39.0	C1210A390(1)2GA(2)
43.0	C1210A430(1)2GA(2)
47.0	C1210A470(1)2GA(2)
51.0	C1210A510(1)2GA(2)
56.0	C1210A560(1)2GA(2)
62.0	C1210A620(1)2GA(2)
68.0	C1210A680(1)2GA(2)
75.0	C1210A750(1)2GA(2)
82.0	C1210A820(1)2GA(2)
91.0	C1210A910(1)2GA(2)
100	C1210A101(1)2GA(2)
110	C1210A111(1)2GA(2)
120	C1210A121(1)2GA(2)

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
130	C1210A131(1)2GA(2)
150	C1210A151(1)2GA(2)
160	C1210A161(1)2GA(2)
180	C1210A181(1)2GA(2)
200	C1210A201(1)2GA(2)
220	C1210A221(1)2GA(2)
240	C1210A241(1)2GA(2)
270	C1210A271(1)2GA(2)
300	C1210A301(1)2GA(2)
330	C1210A331(1)2GA(2)
360	C1210A361(1)2GA(2)
390	C1210A391(1)2GA(2)
430	C1210A431(1)2GA(2)
470	C1210A471(1)2GA(2)
510	C1210A511(1)2GA(2)
560	C1210A561(1)2GA(2)
620	C1210A621(1)2GA(2)
680	C1210A681(1)2GA(2)
750	C1210A751(1)2GA(2)
820	C1210A821(1)2GA(2)
910	C1210A911(1)2GA(2)
1000	C1210A102(1)2GA(2)

(1) Complete KEMET part number by inserting capacitance tolerance, as applicable as shown in ordering information on page 16.
BP CAPACITANCE TOLERANCE: ±1%, ±2%, ±5%, ±10%, ±20% (±0.5pF & ±0.25pF tolerances available 1.0 thru 10pF only) **TEMPERATURE CHARACTERISTIC "G"**
BX CAPACITANCE TOLERANCE: ±5%, ±10%, ±20% **TEMPERATURE CHARACTERISTIC "X"**
 (2) Complete part number by inserting end Metallization, as applicable as shown in ordering information on page 16.
 C—Tin-Coated, Final (SolderGuard II)
 H—Solder-Coated, Final (SolderGuard I)

RATINGS AND PART NUMBER REFERENCE

STYLE C1210 (continued)

CAPACITANCE pF	KEMET PART NUMBER
100 VOLT - BP	
1100	C1210A112(1)1GA(2)
1200	C1210A122(1)1GA(2)
1300	C1210A132(1)1GA(2)
1500	C1210A152(1)1GA(2)
1600	C1210A162(1)1GA(2)
1800	C1210A182(1)1GA(2)
2000	C1210A202(1)1GA(2)
2200	C1210A222(1)1GA(2)
2400	C1210A242(1)1GA(2)
2700	C1210A272(1)1GA(2)
3000	C1210A302(1)1GA(2)
3300	C1210A332(1)1GA(2)
50 VOLT - BP	
3600	C1210A362(1)5GA(2)
3900	C1210A392(1)5GA(2)
200 VOLT - BX	
470	C1210A471(1)2XA(2)
560	C1210A561(1)2XA(2)
680	C1210A681(1)2XA(2)
820	C1210A821(1)2XA(2)
1000	C1210A102(1)2XA(2)
1200	C1210A122(1)2XA(2)
1500	C1210A152(1)2XA(2)
1800	C1210A182(1)2XA(2)

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BX	
2200	C1210A222(1)2XA(2)
2700	C1210A272(1)2XA(2)
3300	C1210A332(1)2XA(2)
3900	C1210A392(1)2XA(2)
4700	C1210A472(1)2XA(2)
5600	C1210A562(1)2XA(2)
6800	C1210A682(1)2XA(2)
8200	C1210A822(1)2XA(2)
10,000	C1210A103(1)2XA(2)
100 VOLT - BX	
12,000	C1210A123(1)1XA(2)
15,000	C1210A153(1)1XA(2)
18,000	C1210A183(1)1XA(2)
22,000	C1210A223(1)1XA(2)
27,000	C1210A273(1)1XA(2)
33,000	C1210A333(1)1XA(2)
50 VOLT - BX	
39,000	C1210A393(1)5XA(2)
47,000	C1210A473(1)5XA(2)
56,000	C1210A563(1)5XA(2)
68,000	C1210A683(1)5XA(2)
82,000	C1210A823(1)5XA(2)
100,000	C1210A104(1)5XA(2)

RATINGS AND PART NUMBER REFERENCE

STYLE C1805

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
220	C1805A221(1)2GA(2)
240	C1805A241(1)2GA(2)
270	C1805A271(1)2GA(2)
300	C1805A301(1)2GA(2)
330	C1805A331(1)2GA(2)
360	C1805A361(1)2GA(2)
390	C1805A391(1)2GA(2)
430	C1805A431(1)2GA(2)
470	C1805A471(1)2GA(2)
100 VOLT - BP	
510	C1805A511(1)1GA(2)
560	C1805A561(1)1GA(2)
620	C1805A621(1)1GA(2)
680	C1805A681(1)1GA(2)
750	C1805A751(1)1GA(2)
820	C1805A821(1)1GA(2)
910	C1805A911(1)1GA(2)
1000	C1805A102(1)1GA(2)
1100	C1805A112(1)1GA(2)
1200	C1805A122(1)1GA(2)
1300	C1805A132(1)1GA(2)
1500	C1805A152(1)1GA(2)
50 VOLT - BP	
1600	C1805A162(1)5GA(2)
1800	C1805A182(1)5GA(2)
2000	C1805A202(1)5GA(2)
2200	C1805A222(1)5GA(2)

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BX	
1200	C1805A122(1)2XA(2)
1500	C1805A152(1)2XA(2)
1800	C1805A182(1)2XA(2)
2200	C1805A222(1)2XA(2)
2700	C1805A272(1)2XA(2)
3300	C1805A332(1)2XA(2)
3900	C1805A392(1)2XA(2)
100 VOLT - BX	
4700	C1805A472(1)1XA(2)
5600	C1805A562(1)1XA(2)
6800	C1805A682(1)1XA(2)
8200	C1805A822(1)1XA(2)
10,000	C1805A103(1)1XA(2)
12,000	C1805A123(1)1XA(2)
15,000	C1805A153(1)1XA(2)
50 VOLT - BX	
18,000	C1805A183(1)5XA(2)
22,000	C1805A223(1)5XA(2)
27,000	C1805A273(1)5XA(2)
33,000	C1805A333(1)5XA(2)
39,000	C1805A393(1)5XA(2)
47,000	C1805A473(1)5XA(2)

(1) Complete KEMET part number by inserting capacitance tolerance, as applicable as shown in ordering information on page 16.

BP CAPACITANCE TOLERANCE: $\pm 1\%$, $\pm 2\%$, $\pm 5\%$, $\pm 10\%$, $\pm 20\%$ ($\pm 0.5\text{pF}$ & $\pm 0.25\text{pF}$ tolerances available 1.0 thru 10pF only) TEMPERATURE CHARACTERISTIC "G"

BX CAPACITANCE TOLERANCE: $\pm 5\%$, $\pm 10\%$, $\pm 20\%$ TEMPERATURE CHARACTERISTIC "X"

(2) Complete part number by inserting end Metallization, as applicable as shown in ordering information on page 16.

C—Tin-Coated, Final (SolderGuard II) H—Solder-Coated, Final (SolderGuard I)

RATINGS AND PART NUMBER REFERENCE
STYLE C1808

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
330	C1808A331(1)2GA(2)
360	C1808A361(1)2GA(2)
390	C1808A391(1)2GA(2)
430	C1808A431(1)2GA(2)
470	C1808A471(1)2GA(2)
510	C1808A511(1)2GA(2)
560	C1808A561(1)2GA(2)
620	C1808A621(1)2GA(2)
680	C1808A681(1)2GA(2)
750	C1808A751(1)2GA(2)
820	C1808A821(1)2GA(2)
910	C1808A911(1)2GA(2)
1000	C1808A102(1)2GA(2)
1100	C1808A112(1)2GA(2)
1200	C1808A122(1)2GA(2)
1300	C1808A132(1)2GA(2)
1500	C1808A152(1)2GA(2)
100 VOLT - BP	
1600	C1808A162(1)1GA(2)
1800	C1808A182(1)1GA(2)
2000	C1808A202(1)1GA(2)
2200	C1808A222(1)1GA(2)
2400	C1808A242(1)1GA(2)
2700	C1808A272(1)1GA(2)
3000	C1808A302(1)1GA(2)
3300	C1808A332(1)1GA(2)
3600	C1808A362(1)1GA(2)
3900	C1808A392(1)1GA(2)
4300	C1808A432(1)1GA(2)
4700	C1808A472(1)1GA(2)

CAPACITANCE pF	KEMET PART NUMBER
50 VOLT - BP	
5100	C1808A512(1)5GA(2)
5600	C1808A562(1)5GA(2)
200 VOLT - BX	
2200	C1808A222(1)2XA(2)
2700	C1808A272(1)2XA(2)
3300	C1808A332(1)2XA(2)
3900	C1808A392(1)2XA(2)
4700	C1808A472(1)2XA(2)
5600	C1808A562(1)2XA(2)
6800	C1808A682(1)2XA(2)
8200	C1808A822(1)2XA(2)
10,000	C1808A103(1)2XA(2)
100 VOLT - BX	
12,000	C1808A123(1)1XA(2)
15,000	C1808A153(1)1XA(2)
18,000	C1808A183(1)1XA(2)
22,000	C1808A223(1)1XA(2)
27,000	C1808A273(1)1XA(2)
33,000	C1808A333(1)1XA(2)
50 VOLT - BX	
39,000	C1808A393(1)5XA(2)
47,000	C1808A473(1)5XA(2)
56,000	C1808A563(1)5XA(2)
68,000	C1808A683(1)5XA(2)
82,000	C1808A823(1)5XA(2)
100,000	C1808A104(1)5XA(2)

RATINGS AND PART NUMBER REFERENCE
STYLE C1812

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
330	C1812A331(1)2GA(2)
360	C1812A361(1)2GA(2)
390	C1812A391(1)2GA(2)
430	C1812A431(1)2GA(2)
470	C1812A471(1)2GA(2)
510	C1812A511(1)2GA(2)
560	C1812A561(1)2GA(2)
620	C1812A621(1)2GA(2)
680	C1812A681(1)2GA(2)
750	C1812A751(1)2GA(2)
820	C1812A821(1)2GA(2)
910	C1812A911(1)2GA(2)
1000	C1812A102(1)2GA(2)
1100	C1812A112(1)2GA(2)
1200	C1812A122(1)2GA(2)
1300	C1812A132(1)2GA(2)
1500	C1812A152(1)2GA(2)
1600	C1812A162(1)2GA(2)
1800	C1812A182(1)2GA(2)
2000	C1812A202(1)2GA(2)
2200	C1812A222(1)2GA(2)
2400	C1812A242(1)2GA(2)
2700	C1812A272(1)2GA(2)
100 VOLT - BP	
3000	C1812A302(1)1GA(2)
3300	C1812A332(1)1GA(2)
3600	C1812A362(1)1GA(2)
3900	C1812A392(1)1GA(2)
4300	C1812A432(1)1GA(2)
4700	C1812A472(1)1GA(2)
5100	C1812A512(1)1GA(2)

CAPACITANCE pF	KEMET PART NUMBER
100 VOLT - BP	
5600	C1812A562(1)1GA(2)
6200	C1812A622(1)1GA(2)
6800	C1812A682(1)1GA(2)
50 VOLT - BP	
7500	C1812A752(1)5GA(2)
8200	C1812A822(1)5GA(2)
9100	C1812A912(1)5GA(2)
10,000	C1812A103(1)5GA(2)
200 VOLT - BX	
6800	C1812A682(1)2XA(2)
8200	C1812A822(1)2XA(2)
10,000	C1812A103(1)2XA(2)
12,000	C1812A123(1)2XA(2)
15,000	C1812A153(1)2XA(2)
18,000	C1812A183(1)2XA(2)
100 VOLT - BX	
22,000	C1812A223(1)1XA(2)
27,000	C1812A273(1)1XA(2)
33,000	C1812A333(1)1XA(2)
39,000	C1812A393(1)1XA(2)
47,000	C1812A473(1)1XA(2)
56,000	C1812A563(1)1XA(2)
68,000	C1812A683(1)1XA(2)
50 VOLT - BX	
82,000	C1812A823(1)5XA(2)
100,000	C1812A104(1)5XA(2)
120,000	C1812A124(1)5XA(2)
150,000	C1812A154(1)5XA(2)
180,000	C1812A184(1)5XA(2)

(1) Complete KEMET part number by inserting capacitance tolerance, as applicable as shown in ordering information on page 16. **BP CAPACITANCE TOLERANCE:** ±1%, ±2%, ±5%, ±10%, ±20% (±0.5pF & ±0.25pF tolerances available 1.0 thru 10pF only) **TEMPERATURE CHARACTERISTIC "G" BX CAPACITANCE TOLERANCE:** ±5%, ±10%, ±20% **TEMPERATURE CHARACTERISTIC "X"** (2) Complete part number by inserting end Metallization, as applicable as shown in ordering information on page 16.

C—Tin-Coated, Final (SolderGuard II) H—Solder-Coated, Final (SolderGuard I)

RATINGS AND PART NUMBER REFERENCE STYLE C1825

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
2700	C1825A272(1)2GA(2)
3000	C1825A302(1)2GA(2)
3300	C1825A332(1)2GA(2)
3600	C1825A362(1)2GA(2)
3900	C1825A392(1)2GA(2)
4300	C1825A432(1)2GA(2)
4700	C1825A472(1)2GA(2)
5100	C1825A512(1)2GA(2)
5600	C1825A562(1)2GA(2)
100 VOLT - BP	
6200	C1825A622(1)1GA(2)
6800	C1825A682(1)1GA(2)
7500	C1825A752(1)1GA(2)
8200	C1825A822(1)1GA(2)
9100	C1825A912(1)1GA(2)
10,000	C1825A103(1)1GA(2)
11,000	C1825A113(1)1GA(2)
12,000	C1825A123(1)1GA(2)
13,000	C1825A133(1)1GA(2)
15,000	C1825A153(1)1GA(2)
16,000	C1825A163(1)1GA(2)
18,000	C1825A183(1)1GA(2)
50 VOLT - BP	
20,000	C1825A203(1)5GA(2)
22,000	C1825A223(1)5GA(2)

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BX	
10,000	C1825A103(1)2XA(2)
12,000	C1825A123(1)2XA(2)
15,000	C1825A153(1)2XA(2)
18,000	C1825A183(1)2XA(2)
22,000	C1825A223(1)2XA(2)
33,000	C1825A333(1)2XA(2)
39,000	C1825A393(1)2XA(2)
47,000	C1825A473(1)2XA(2)
100 VOLT - BX	
56,000	C1825A563(1)1XA(2)
68,000	C1825A683(1)1XA(2)
82,000	C1825A823(1)1XA(2)
100,000	C1825A104(1)1XA(2)
120,000	C1825A124(1)1XA(2)
150,000	C1825A154(1)1XA(2)
50 VOLT - BX	
180,000	C1825A184(1)5XA(2)
220,000	C1825A224(1)5XA(2)
270,000	C1825A274(1)5XA(2)
330,000	C1825A334(1)5XA(2)
390,000	C1825A394(1)5XA(2)
470,000	C1825A474(1)5XA(2)

RATINGS AND PART NUMBER REFERENCE STYLE C2225

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BP	
2700	C2225A272(1)2GA(2)
3000	C2225A302(1)2GA(2)
3300	C2225A332(1)2GA(2)
3600	C2225A362(1)2GA(2)
3900	C2225A392(1)2GA(2)
4300	C2225A432(1)2GA(2)
4700	C2225A472(1)2GA(2)
5100	C2225A512(1)2GA(2)
5600	C2225A562(1)2GA(2)
6200	C2225A622(1)2GA(2)
6800	C2225A682(1)2GA(2)
7500	C2225A752(1)2GA(2)
8200	C2225A822(1)2GA(2)
100 VOLT - BP	
9100	C2225A912(1)1GA(2)
10,000	C2225A103(1)1GA(2)
11,000	C2225A113(1)1GA(2)
12,000	C2225A123(1)1GA(2)
13,000	C2225A133(1)1GA(2)
15,000	C2225A153(1)1GA(2)
16,000	C2225A163(1)1GA(2)
18,000	C2225A183(1)1GA(2)
20,000	C2225A203(1)1GA(2)
22,000	C2225A223(1)1GA(2)
50 VOLT - BP	
24,000	C2225A243(1)5GA(2)
27,000	C2225A273(1)5GA(2)

CAPACITANCE pF	KEMET PART NUMBER
200 VOLT - BX	
18,000	C2225A183(1)2XA(2)
22,000	C2225A223(1)2XA(2)
27,000	C2225A273(1)2XA(2)
33,000	C2225A333(1)2XA(2)
39,000	C2225A393(1)2XA(2)
47,000	C2225A473(1)2XA(2)
100 VOLT - BX	
56,000	C2225A563(1)1XA(2)
68,000	C2225A683(1)1XA(2)
82,000	C2225A823(1)1XA(2)
100,000	C2225A104(1)1XA(2)
120,000	C2225A124(1)1XA(2)
150,000	C2225A154(1)1XA(2)
180,000	C2225A184(1)1XA(2)
50 VOLT - BX	
220,000	C2225A224(1)5XA(2)
270,000	C2225A274(1)5XA(2)
330,000	C2225A334(1)5XA(2)
390,000	C2225A394(1)5XA(2)
470,000	C2225A474(1)5XA(2)
560,000	C2225A564(1)5XA(2)
680,000	C2225A684(1)5XA(2)
820,000	C2225A824(1)5XA(2)
1,000,000	C2225A105(1)5XA(2)

(1) Complete KEMET part number by inserting capacitance tolerance, as applicable as shown in ordering information on page 16. **BP CAPACITANCE TOLERANCE:** ±1%, ±2%, ±5%, ±10%, ±20% (±0.5pF & ±0.25pF tolerances available 1.0 thru 10pF only) **TEMPERATURE CHARACTERISTIC "G" BX CAPACITANCE TOLERANCE:** ±5%, ±10%, ±20% **TEMPERATURE CHARACTERISTIC "X"**

(2) Complete part number by inserting end Metallization, as applicable as shown in ordering information on page 16.

C—Tin-Coated, Final (SolderGuard II)

H—Solder-Coated, Final (SolderGuard I)

KEMET® Capacitors

KEMET Electronics Corporation

WORLD SALES HEADQUARTERS • Post Office Box 5928 • Greenville, South Carolina 29606 • USA

Tel: (864) 963-6300 • FAX: (864) 963-6521

KEMET ELECTRONICS CORPORATION

Three Civic Plaza, Suite 240
Newport Beach, California 92660
Western Region U. S. A.
Phone: (714) 640-9320
FAX: (714) 720-9807

KEMET ELECTRONICS CORPORATION

Schaumburg Corporate Center, Suite 110
1515 Woodfield Road
Schaumburg, Illinois 60173
Central Region U. S. A.
Phone: (847) 517-1030
FAX: (847) 517-1037

KEMET ELECTRONICS CORPORATION

Piedmont Center East, Suite 410, B-137
37 Villa Road
Greenville, South Carolina 29615
Southeastern Region U. S. A.
Phone: (864) 242-5789
FAX: (864) 242-5795

KEMET ELECTRONICS CORPORATION

Park West East Tract
1603 LBJ Freeway, Suite 830
Dallas, Texas 75234
West Central Region U. S. A.
Phone: (972) 241-7501
FAX: (972) 241-5604

KEMET ELECTRONICS CORPORATION

301 Edgewater Place, Suite 208
Wakefield, MA 01880
New England Region U. S. A.
Phone: (617) 245-4646
FAX: (617) 245-1595

KEMET ELECTRONICS CORPORATION

2350 Mission College Blvd., Suite 390
Santa Clara, California 95054
Northwestern Region U. S. A.
Phone: (408) 986-0424
FAX: (408) 986-1442

KEMET ELECTRONICS (Canada) LTD.

105-7145 W. Credit Ave., Bldg. 2
Mississauga, Ontario L5N 6J7
Phone: (905) 542-7930
FAX: (905) 542-7949

KEMET ELECTRONICS (Canada) LTD.

66 Rue Dubois, Suite 212
St-Eustache, Quebec J7P 4W9
Phone: (514) 472-6677
FAX: (514) 472-7899

KEMET ELECTRONICS S.A.

15 Chemin des Mines
P.O.B. 76, CH 1211 Geneva, 20
Switzerland
Phone: 41-22-738-4244
Telex: 845-412901 KESA CH
FAX: 41-22-738-3918

KEMET ELECTRONICS GMBH

Hans-Stiessberger-Strasse 2A
Postfach 1380
D 85540 Haar/Munich
Germany
Phone: 49-89-45-64-200
FAX: 49-89-46-04-117

KEMET ELECTRONICS S.A.R.L.

2, Rue Nicolas Ledoux
Silic 254
94568 Rungis-Cedex
France
Phone: 33-1-45-12-53-20
FAX: 33-1-46-87-40-87

KEMET ELECTRONICS LTD.

Waterfront House, 55/61 South St.
Bishop's Stortford
Hertfordshire CM23 3AL
United Kingdom
Phone: 44-1279-757-343
FAX: 44-1279-757-188

KEMET ELECTRONICS LTD.

Brickhill East, Cratloe Co.
Clare, Ireland
Phone: 353-61-357-229
FAX: 353-61-357-455

KEMET ELECTRONICS

Via Gaetano Ermoli, 22
ScF, INT. 11
00155, Rome, Italy
Phone: 39-6-232-3-1718
FAX: 39-6-232-3-3081

KEMET ELECTRONICS ASIA LTD.

4A Chuan Hing Industrial Bldg.
14 Wang Tai Road
Kowloon Bay, Hong Kong
Phone: 852-2305-1168
FAX: 852-2759-0345

KEMET ELECTRONICS S.A.

Sector Oficios 26-2-B
Tres Cantos - 28760 Madrid, Spain
Phone: 34-1-804-43-03
FAX: 34-1-804-44-77

KEMET ELECTRONICS ASIA LTD.

Suite 1512,15/F, Lucky Tower B
3 Dong San Huan Bei Road
Chao Yang District
Beijing 100027, China
Phone: 86-10-6462-0173
FAX: 86-10-6461-5707

KEMET ELECTRONICS MARKETING (S) PTE LTD

8-2-04 Sunny Point Kompleks
Jalan Batu Uban
11700 Gelugor
Palau Penang, Malaysia
Phone: 60-4-65-952-00
FAX: 60-4-65-952-20

KEMET ELECTRONICS MARKETING (S) PTE LTD

24 ANG MO KIO St. 65
Ground Floor (West Wing)
Singapore 569061
Phone: 65-484-2220
FAX: 65-484-1110

KEMET ELECTRONICS CORPORATION., Taiwan Branch

3-4 F., No. 148, Section 4
Chung-Hsiao E. Rd.
Taipei, Taiwan ROC
Phone: 886-2-752-8585
FAX: 886-2-721-3129

UNICOM INTERNATIONAL CORPORATION

Room 702, Shinhwa Bldg.
34-1 Mapo-Dong
Mapo-Gu
Seoul, Korea 121-050
Phone: 82-2-712-5821
FAX: 82-2-712-5823

CRUSADER ELECTRONIC COMPONENTS PTY. LTD.-

3/92 Bryant Street
P. O. Box 226
Padstow NSW 2211
Australia
Phone: 61-2-792-3922
Telex: 790-123993 CRUSAD
FAX: 61-2-792-1446

MULTITECH ELECTRONICS CORPORATION (PTY) LTD

P.O. Box 23351
Claremont 7735
Republic of South Africa
Phone: 27-21-64-4103
FAX: 27-21-64-1360

ELECTRONIC BUILDING ELEMENTS (PTY) LTD

178 Erasmus Street
Meyerspark, Pretoria, 0184
Republic of South Africa
Phone: 27-12-803-7680
FAX: 27-11-803-8294

ELECTRONIC ENTERPRISES (HEAD OFFICE)

Post Bag No. 6367
216, Regal Industrial Estate
Archarya Donde Marg.
Sewri, Bombay 400 015
India
Phone: 91-22-413-7096
FAX: 91-22-413-3341

LANDSEAS ISRAEL LTD.

3 Yehonathan Nethanyahu St.
P.O.B. 676 OR Yehuda 60 256
Israel
Phone: 972-3-5333033
FAX: 972-3-5333052

HITECH ELECTRONICA INDUSTRIAL COMMERCIAL LTDA.

Rua Branco De Moraes 489
CH Santo Antonio
04718-0010SP - Sao Paulo,
Brazil
Phone: 55-11-882-4000
FAX: 55-11-882-4100

ELKO S. R. L.

AV Belgrano 1661
1093 Buenos Aires
Argentina
Phone: 54-1-46-1101
Telex: 390-17561
FAX: 54-1-325-8819

CIBER ELECTRONICA S.A. de C.V.

Prolongacion Arbol No. 33 (2080)
Col. Chapalita Sur
Guadalajara, Jal 45000
Mexico
Phone: 52-36-47-52-17
FAX: 52-31-21-33-31

NOTICE:

Place "011" in front of the above Phone and FAX Numbers of Europe and Asia, when dialing from a United States exchange.
NOTE . . . KEMET reserves the right to modify minor details of internal and external construction at any time in the interest of product improvement. KEMET does not assume any responsibility for infringement that might result from the use of KEMET Capacitors in potential circuit designs. "KEMET" is a registered trademark of KEMET Electronics Corporation