

Technical drawing of a shaft. The diameter is specified as $.111 \pm .003$ DIA. The length is specified as $.250 \pm .008$. The drawing shows a cross-section of the shaft with a central hole and a keyway on the right side.

- ① COPPER PER ASTM-B-152 OR ASTM-B16
② TIN PL PER MIL-T-10727

UNLESS OTHERWISE SPECIFIED DIMENSIONS IN INCHES. TOLERANCES ON: DIMENSIONS ± <u> </u> ANGLES ± <u> </u>	CONTRACT NO. DR <u>4-4-84</u> CHK <u>4/6/84</u> APP <u>4/6/84</u> APP <u>4/6/84</u>	AMP AMP INCORPORATED Harrisburg, Pa. 17105		
	MATERIAL 	NAME FERRULE		
FINISH 	DESGN APPD OTHER APPD	SIZE A	FSCM NO 00779	DRAWING NO 1-332056-0
		SCALE NTS		SHEET