

S8 Bayonet/Screw Base Lamps



Features:


- With Clear Cover
- Drop in replacement
- Instant ON / OFF
- Shock and vibration resistant
- Ultra-energy-efficient replacement for maximum 15 W halogen auto lamps
- 40,000 hours average lifetime : Less maintenance
- No mercury
- Waterproof
- BA15s, BAY15d, BA15d, E12, E14 bases available
- No UV, IR
- 10 to 30 V dc for use where current is not constant

Applications:

- Tail light
- Instrument light
- Dome light
- Under hood light

BA15S Bayonet Base S8 Clear Cover LED Lamp

Base: BA15S; (1156) Single Contact 15 mm Diameter Bayonet Base



D (mm)	C (mm)
Ø25.5	51.5


BA15S (1156) Single Contact 15 mm Bayonet Base Replaces : 1156 1073, 1095, 1141, 1156, 1156A, 1195, 12088, 1295, 1295NA, 199, 2396, 3497, 631, 7506, 93, 97, 97A, 97NA

Specification Table

CCT / Colour	Voltage	LED Quantity	Watts (Typical)	Lumens (Typical)	Part Number
Warm White 2,800 to 3,200 K	10 to 30 V dc	16	0.7	60	MCS815S16NS30DWW
Neutral White 4,250 to 4,750 K	10 to 30 V dc	16	0.7	63	MCS815S16NS30DNW
Cool White 6,000 to 7,000 K	10 to 30 V dc	16	0.7	68	MCS815S16NS30DCW

BA15D Bayonet Base S8 Clear Cover LED Lamp

Base: BA15D; (1142) Dual Contact 15 mm Diameter Bayonet Base



D (mm)	C (mm)
Ø25.5	51.5

BA15D – (1142) Dual Contact 15 mm diameter bayonet base, symmetric locking pins. Two contacts for positive and ground connections. Replaces : 68, 90, 94, 1004, 1076, and 1142 bulbs


S8 Bayonet/Screw Base Lamps

Specification Table

CCT / Colour	Voltage	LED Quantity	Watts (Typical)	Lumens (Typical)	Part Number
Warm White 2,800 to 3,200 K	10 to 30 V dc	16	0.7	60	MCS815D16NS30DWW
Neutral White 4,250 to 4,750 K	10 to 30 V dc	16	0.7	63	MCS815D16NS30DNW
Cool White 6,000 to 7,000 K	10 to 30 V dc	16	0.7	68	MCS815D16NS30DCW

BAY15D Bayonet Base S8 Clear Cover LED Lamp

Base: BAY15D (1157)- Double Contact, Offset Pins 15 mm Diameter Indexed Base*



D (mm)	C (mm)
Ø25.5	51.5


BAY15D (1157) - (double contact, offset pins) 15 mm Diameter Indexed Base Replaces : 1016, 1034, 1157, 1157A, 1176, 1178A, 1196, 2057, 2057A, 2357, 2357A, 2397, 3496, 7225, 7528, 94, 992

Specification Table

CCT / Colour	Voltage	LED Quantity	Watts (Typical)	Lumens (Typical)	Part Number
Warm White 2,800 to 3,200 K	10 to 30 V dc	16	0.7	60	MCS8Y15D16NS30DWW
Neutral White 4,250 to 4,750 K	10 to 30 V dc	16	0.7	63	MCS8Y15D16NS30DNW
Cool White 6,000 to 7,000 K	10 to 30 V dc	16	0.7	68	MCS8Y15D16NS30DCW

* Indexed base (offset pins) has pins that are not symmetrical. They are offset

E14 Base S8 Clear Cover LED Lamp



Dimensions : Millimetres


S8 Bayonet/Screw Base Lamps



Specification Table

CCT / Colour	Voltage	LED Quantity	CRI	Watts (Typical)	Lumens (Typical)	Part Number
Warm White 2,800 to 3,200 K	10 to 30 V dc	16	≥80	0.7	60	MCS8E1416NS30DWW
Neutral White 4,250 to 4,750 K	10 to 30 V dc	16	≥80	0.7	63	MCS8E1416NS30DNW
Cool White 6,000 to 7,000 K	10 to 30 V dc	16	≥80	0.7	68	MCS8E1416NS30DCW
Warm White 2,800 to 3,200 K	230 V ac	16	≥80	1	60	MCS8E1416NSHWW
Neutral White 4,250 to 4,750 K	230 V ac	16	≥80	1	63	MCS8E1416NSHNW
Cool White 6,000 to 7,000 K	230 V ac	16	≥80	1	68	MCS8E1416NSHCW

E12 Base S8 Clear Cover LED Lamp



Dimensions : Millimetres

Specification Table

CCT / Colour	Voltage	LED Quantity	CRI	Watts (Typical)	Lumens (Typical)	Part Number
Warm White 2,800 to 3,200 K	10 to 30 V dc	16	≥80	0.7	60	MCS8E1216NS30DWW
Neutral White 4,250 to 4,750 K	10 to 30 V dc	16	≥80	0.7	63	MCS8E1216NS30DNW
Cool White 6,000 to 7,000 K	10 to 30 V dc	16	≥80	0.7	68	MCS8E1216NS30DCW
Warm White 2,800 to 3,200 K	110 to 120 V ac	16	≥80	1	60	MCS8E1216NSLWW
Neutral White 4,250 to 4,750 K	110 to 120 V ac	16	≥80	1	63	MCS8E1216NSLNW
Cool White 6,000 to 7,000 K	110 to 120 V ac	16	≥80	1	68	MCS8E1216NSLCW

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.