




1470-19 (3/11)

Pro/ENGINEER DRAWING

GENERAL TOLERANCES ± 0.3

WIRE RANGE :
1,0-2,5 mm²

INSULATION RANGE :
3,0-4,1mm DIA.

DIRECTION OFF TOP OF REEL

Terminal "U" down.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm$

1 PLC $\pm$

2 PLC $\pm$

3 PLC $\pm$

4 PLC $\pm$

ANGLES $\pm 1^\circ$

FINISH

MATERIAL

SEE TABLE

DWN
J.V.LIEMPT.

CHK
A.BIJNEN.

APVD
L.V.SOEST.

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

21MAR1992

TE Connectivity

NAME
.250 SRS FASTIN-ON RECEPTACLE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-160446

RESTRICTED TO
-

SCALE
1:1

SHEET
1

OF
1

REV
H2

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		H2	REVISED PER ECO-11-005294	21MAR2011	RK	HMR

NOTES:

- 1 FOR USE ON MINIATURE APPLICATORS (LEFT-RIGHT FEED) AND STANDARD APPLICATORS (RIGHT-LEFT FEED).
- 2 FOR USE ON MINIATURE APPLICATORS (AMP-O-MATOR APPLICATION). (LEFT-RIGHT FEED).
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

SECTION A-A

SECTION B-B

OBSOLETE 3	1	PRE-TINPLATED	PH.BRONZE	6-160446-8
	1	PRE-TINPLATED	BRASS	6-160446-7
	1 2	TINPLATED	PH.BRONZE	6-160446-6
	1 2	SILVERPLATED	PH.BRONZE	5-160446-8
	1 2	SILVERPLATED	BRASS	5-160446-6
	1	TINPLATED	BRASS	5-160446-5
	1	UNPLATED	BRASS	5-160446-4
	1	TINPLATED	PH.BRONZE	5-160446-2
	1	UNPLATED	PH.BRONZE	5-160446-1
NOTES		FINISH	MATERIAL	PART NUMBER

.250 SRS FASTIN-ON RECEPTACLE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-160446	-

SCALE	SHEET	OF	REV
1:1	1	1	H2