


Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION



9520 Multi-Conductor - 300V Power-Limited Tray Cable

For more Information
please call

1-800-Belden1



General Description:

22 AWG pairs stranded (7x30) tinned copper conductors, twisted pairs, PVC insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
9	22	7x30	TC - Tinned Copper

Total Number of Conductors: 18

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
F-R PVC - Flame Retardant Polyvinyl Chloride	.062

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	7x30	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
F-R PVC - Flame Retardant Polyvinyl Chloride	.053

Outer Jacket Ripcord:

Yes

Overall Cable

Overall Nominal Diameter:

0.482 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red and Numbered
2	Black & Red and Numbered
3	Black & Red and Numbered
4	Black & Red and Numbered
5	Black & Red and Numbered
6	Black & Red and Numbered
7	Black & Red and Numbered
8	Black & Red and Numbered
9	Black & Red and Numbered

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

UL Temperature Rating: 105°C

Bulk Cable Weight: 112 lbs/1000 ft.

Max. Recommended Pulling Tension: 172 lbs.

Min. Bend Radius/Minor Axis: 4.800 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMG, ITC-ER, PLTC-ER

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

9520 Multi-Conductor - 300V Power-Limited Tray Cable

CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4 Loading
C(UL) Flame Test:	FT4
IEEE Flame Test:	1202

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes
Sunlight Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (μ H/ft)
.21

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
26

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
45

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
15

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
15

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.4 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9520 0601000	1,000 FT	127.000 LB	CHROME	C	9 PR #22 PVC FS PVC
9520 060500	500 FT	61.000 LB	CHROME	C	9 PR #22 PVC FS PVC

Notes:

C = CRATE REEL PUT-UP.

9520 Multi-Conductor - 300V Power-Limited Tray Cable

Revision Number: 2 Revision Date: 10-21-2014

© 2014 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9520 060500](#)