

**Part Number: 67819-6030**

1.27mm Pitch Board-to-Board Edge Card Connector, Vertical, Solder Tail and Peg Length 2.20mm, Gold (Au) Flash, 120 Circuits

Image not available

<b>Status:</b>	<b>OBsolete</b>
<b>Replacement:</b>	Contact Molex
<b>Series:</b>	<a href="#">67819</a>
<b>Category:</b>	Edge Card Connectors

Series image - Reference only

**Mates With Part(s):**  
32-bit PCI card**Product Environmental Compliance**[EU RoHS](#): ELV and RoHS Compliant[China RoHS](#): [REACH SVHC](#):[Low-Halogen Status](#): Not Reviewed**Part Detail****General**

<b>Status</b>	<b>Obsolete</b>
Category	Edge Card Connectors
Series	<a href="#">67819</a>
Component Type	Edgecard to PCB
Product Name	Edge Card

**Physical**

(p)ower-(s)ignal Configuration	120s - 0p
Circuits (Loaded)	120
Circuits (maximum)	120
Durability (mating cycles max)	50
Entry Angle	Vertical (Top Entry)
Keying to Mating Part	Yes
PC Tail Length	2.20mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.27mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +105°C

**Electrical**

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Voltage - Maximum	500V

**Solder Process Data**

Lead-free Process Capability	Wave Capable (TH only)
------------------------------	------------------------

**Material Info****Reference - Drawing Numbers**

Product Specification	PS-89177, RPS-89177-004
-----------------------	-------------------------

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application****Tooling**[Check our list of old tooling that used to be available for this part](#)

