

## **SERIES 63K**


## High Resolution, Ball Bearing, 4-Pin

## FEATURES


- 25, 32, 50, 64, 100, 128 and 256 Cycles per Revolution Available
- Sealed Version Available
- Rugged Construction
- Cable or Pin Version
- 300 Million Life Cycles
- 5,000 RPM Shaft Rotation



## **DIMENSIONS** In inches (and millimeters)



## CIRCUITRY AND WAVEFORM: Standard Quadrature 2-Bit Code



## SPECIFICATIONS

## Electrical Ratings

**Operating Voltage:**  $5.0 \pm .25$  Vdc**Supply Current:** 30 mA maximum at 5 Vdc

## Logic Output Characteristics:

**Output Type:** Open collector with integrated Schmitt Trigger and 10 kΩ pull-up resistor**Maximum Sink Current:** 16 mA at .40 volts**Power Consumption:** 150 mW maximum**Optical Rise Time:** 500 nS typical**Optical Fall Time:** 14 nS typical

## Mechanical Ratings

**Mechanical Life:** 300 million revolutions**Time Life:** Guaranteed for 10 years of continuous operation (calculated from emitter degradation data)**Mounting Torque:** 20 in-lbs maximum**Terminal Strength:** 5 lbs terminal pull-out force minimum**Solderability:** 95% free of pin holes and voids**Operating Torque:** 0.5 in-oz maximum (no detents) for unsealed versions**Externally Applied Shaft Force:** Axial: 15 lbs maximum; Radial: 15 lbs maximum

## Environmental Ratings

**Operating Temperature Range:** -40°C to 85°C**Storage Temperature Range:** -55°C to 100°C**Relative Humidity:** 90-95% at 40°C for 96 hours**Vibration Resistance:** Harmonic motion with amplitude of 15g, within a varied 10 to 2000 Hz frequency for 12 hours per MIL-STD-202, Method 204**Shock Resistance:** Test 1: 100g for 6 mS, half-sine wave with velocity change of 12.3 ft/s. Test 2: 100g for 6 mS, sawtooth wave with velocity change of 9.7 ft/s.


## Materials and Finishes

**Bushing:** 6262-T9 aluminum alloy**Housing:** Hiloy 610B**Code Rotor and Aperture:** Chemically etched stainless steel/electroformed nickel**Printed Circuit Board:** NEMA Grade FR-4. Five microinches minimum gold over 100 microinches minimum nickel over copper**Optical Barrier:** Polyphenylene sulfide, 94 V-0**Backplate:** Polyester**Header:** Phosphor bronze, 200 microinches tin over 50 microinches nickel (pin version only)**Infrared Emitter:** Gallium aluminum arsenide**Photo IC:** Planar silicon**Retaining Ring:** Stainless steel**Cable:** 26 AWG, stranded/tinned wire, PVC coated on .100 (2.54) centers (cable version only)**Connector:** Glass-filled PCT, UL94V-0

## Bearing Subassembly

**Bearing:** NSK ABEC 5 (stainless steel)**Preload Collar:** 303 (stainless steel)**Spacer:** 303 (stainless steel)**Bellville Spring:** spring steel (stainless steel)

## ORDERING INFORMATION



## Series

Style: K = Standard, 4-pin, high resolution

KS = Sealed, 4-pin, high resolution

Cycles: per channel per revolution = 25, 32, 50, 64, 100, 128, 256

63KS256-020

## Termination:

Blank (no dash or numbers): pins as described in drawing.


Cable Termination: 020 = 2.0 inches minimum to 250 = 25 inches maximum. Provided in increments of 1/2 inch. (Example 035 = 3.5", 060 = 6".) Cable is terminated with standard Molex part no. 14-56-3046. Use any standard .100 center 4-pin header to interface with cable. Recommended to be mounted with Molex header part no. 70543-0003 or 70553-0003.

Control knobs available, see page E-39.


Available from your local Grayhill Distributor. For prices and discounts, contact a local Sales Office, an authorized local Distributor or Grayhill.

**SERIES 63R****High Resolution, Ball Bearing,  
5-pin (Polarized Connection)****FEATURES**

- 25, 32, 50, 64, 100, 128 and 256 Cycles per Revolution Available
- Sealed Version Available
- Rugged Construction
- Cable or Pin Versions
- 300 Million Life Cycles
- 5000 RPM Shaft Rotation
- Index Pulse Available


**DIMENSIONS** In Inches (and millimeters)**Top View**

Unless otherwise specified, dimension tolerances are as follows: linear ± .010 (0.25), diameters ± .010 (0.25), angular ± 5°

**Top View**

Unless otherwise specified, dimension tolerances are as follows: linear ± .010 (0.25), diameters ± .010 (0.25), angular ± 5°

## CIRCUITRY AND WAVEFORM: Standard Quadrature 2-Bit Code



## SPECIFICATIONS

## Electrical Ratings

**Operating Voltage:** 5 ±.25 Vdc**Supply Current:** 30 mA maximum at 5 Vdc

## Logic Output Characteristics:

Output Type: Open collector with integrated Schmitt Trigger and 10 kΩ pull-up resistor

Maximum Sink Current: 16 mA at .40 volts

**Power Consumption:** 150 mW maximum**Optical Rise Time:** 500 nS typical**Optical Fall Time:** 14 nS typical

## Mechanical Ratings

**Mechanical Life:** 300 million revolutions**Time Life:** Guaranteed for 10 years of continuous operation (calculated from emitter degradation data)**Mounting Torque:** 20 in-lbs maximum**Terminal Strength:** 5 lbs terminal pull-out force minimum**Solderability:** 95% free of pin holes and voids

## Externally Applied Shaft Force:

Axial: 15 lbs maximum; Radial: 15 lbs maximum

**Operating Torque:** 0.5 in-oz maximum (no detents) for unsealed versions

## Environmental Ratings

**Operating Temperature Range:** -40°C to 85°C**Storage Temperature Range:** -55°C to 100°C**Relative Humidity:** 90-95% at 40°C for 96 hours**Vibration Resistance:** Harmonic motion with amplitude of 15g, within a varied 10 to 2000 Hz frequency for 12 hours per MIL-STD-202, Method 204**Shock Resistance:** Test 1: 100g for 6 mS, half-sine wave with velocity change of 12.3 ft/s. Test 2: 100g for 6 mS, sawtooth wave with velocity change of 9.7 ft/s.

## Materials and Finishes

**Bushing:** 6262-T9 aluminum alloy**Housing:** Hiloy 610B**Shaft:** Stainless steel insert molded into nylon rotor support**Code Rotor and Aperture:** Chemically etched stainless steel/electroformed nickel**Printed Circuit Board:** NEMA Grade FR-4.


Five microinches minimum gold over 100 microinches minimum nickel over copper

**Optical Barrier:** Polyphenylene sulfide, 94 V-0**Backplate:** Polyester**Header:** Phosphor bronze, 200 microinches tin over 50 microinches nickel (pin version only)**Infrared Emitter:** Gallium aluminum arsenide**Photo IC:** Planar silicon**Retaining Ring:** Stainless steel**Cable:** 26 AWG, stranded/tinned wire, PVC coated on .100 (2.54) centers (cable version only)**Connector:** Glass-filled PCT, UL94V-0

## Bearing Subassembly

**Bearing:** NSK ABEC 5 (stainless steel)**Preload Collar:** 303 stainless steel**Spacer:** 303 stainless steel**Bellville Spring:** Spring steel (stainless steel)

## ORDERING INFORMATION



## Series

**Style:** R = Standard, 5-pin, high resolution

RS = Sealed, 5-pin, high resolution

**Cycles:** per channel per revolution = 25, 32, 50, 64, 100, 128, 256

## Termination:

Blank (no dash or numbers): pins as described in drawing.

Cable Termination: 020 = 2.0 inches minimum to 250 = 25 inches maximum

Provided in increments of 1/2 inch. (Example 035 = 3.5", 060 = 6".)

Cable is terminated with standard Molex part no. 14-56-3056.

Use any standard .100 center 5-pin header to interface with cable.

Control knobs available, see page E-39.

Available from your local Grayhill Distributor. For prices and discounts, contact a local Sales Office, an authorized local Distributor or Grayhill.