

NTE548 Silicon High Voltage Rectifier for Industrial/Microwave Oven

Features:

- Low Cost
- Low Leakage
- Isolated Case
- Surge Overload Rating: 50A Peak
- Low Forward Voltage Drop
- Mounting position: Any

Maximum Ratings and Electrical Characteristics:

(Ratings at $T_A = +25^\circ\text{C}$ unless otherwise specified. Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%)

Maximum Recurrent Peak Reverse Voltage, V_{RRM}	12kV
Maximum RMS Voltage, V_{RMS}	8.4kV
Maximum DC Blocking Voltage, V_{DC}	12kV
Maximum Average Forward Rectified Current ($T_A = 50^\circ\text{C}$), I_O	750mA
Peak Forward Surge Current, I_{FSM} (8.3ms single half sine-wave superimposed on rated load)	50A
Maximum Instantaneous Forward Voltage ($I_F = 350\text{mA}$), V_F	14V
Maximum DC Reverse Current ($V_{RRM} = 12\text{kV}$, $T_A = +25^\circ\text{C}$), I_R	5 μA
Operating Junction Temperature Range, T_J	-20° to $+135^\circ\text{C}$
Storage Temperature Range, T_{stg}	-20° to $+135^\circ\text{C}$

