





PART NO.
20021111



SQ 0.41 TYP.
Ø0.3 A B C



RECOMMENDED PCB LAYOUT

SCALE 5.000

NOTES:

- 1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94-V0 BLACK.
TERMINAL: COPPER ALLOY
- 2.THE HOUSING WILL WITHSTAND EXPOSURE TO 260~C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER OR VAPOR PHASE REFLOW OVEN.
- 3.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 4.PRODUCT SPEC: GS-12-629
- 5.PACKAGE SPEC: GS-14-1420

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MINITEK127®			
ltr				ecn no		dr		date		tolerances unless otherwise specified		title	
E				ELX-N-23548		TIM		03/21/16		angles		linear	
F				ELX-N-25883		TONY		01/11/17		.0±.30		mm	
G				ELX-N-27768		TONY		08/18/17		0°±2'		.000±.10	
										scale 1:1			
										dwg no		sheet 1 of 2	
										Amphenol FCI		size	
										20021111		A3	
										type		Product Customer Drawing	
sheet index				revision sheet		G 1		G 2					

PART NO.	PDS.	DIM"x"	DIM"x"
20021111-XXX92XXLF	2 X 46	58.42	57.15
20021111-XXX94XXLF	2 X 47	59.69	58.42
20021111-XXX96XXLF	2 X 48	60.96	59.69
20021111-XXX98XXLF	2 X 49	62.23	60.96
20021111-XXXA0XXLF	2 X 50	63.50	62.23

20021111 - X X X XX X X LF

—LEAD FREE

—PLATING OPTIONAL

1: GOLD FLASH AT CONTACT, 1.27 μ m MIN. MATTE TIN AT TAIL

2: GOLD FLASH AT CONTACT, GOLD FLASH AT TAIL

4: 0.25um Au MIN. AT CONTACT, 1.27um MIN.MATTE TIN AT TAIL

5: 0.25um Au MIN. AT CONTACT, GOLD FLASH AT TAIL

6: 0.38um GXT MIN. AT CONTACT, 1.27um MIN.MATTE TI

7: 0.38um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

8: 0.76um GXT MIN. AT CONTACT, 1.27um MIN. MATTE TI

9: 0.76um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

—PACKING STYLE

—PACKING STYLE
T. TUBE

Q: TAPE

Q: TAPE & REEL WITHOUT CAP
—PIN NO. SEE TABLE

-FIN NO. SEE TABLE
 MATING LENGTHS

—MATING LENGTH(DIM'A')

0: 3.05MM

—TAIL LENGTH(DIM'B')


0: 2.30MM (FOR 1.6MM PCB)

1: 1.60MM (FOR 1.0MM PCB)

2: 2.70MM (FOR 2.0MM PCB)

—RESERVE CODE

—RESERVE CDD
0: STANDARD

mat'l. code					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MINITEK127®						
litr	ecn	no	dr	date	tolerances unless otherwise specified					title							
					angles		linear		mm 		UNSHROUDED HDR VT TH						
					0°±2°				scale 1:1								
					dr ZK HU		09/28/12				dwg no		sheet2 of 2		size		
					engr ZK HU		09/28/12				20021111		A3				
					chr BIAN RICK		09/28/12										
					appd BIAN RICK		09/28/12										
sheet index		revision sheet		G	G												
				1	2												