


© 1967 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP
PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.



FOR .102 TO .214 WIRE INSULATION DIA.
TONGUE MATERIAL THK. = .040 $\pm$.002

REVISIONS

ZONE	LTR	DESCRIPTION	DATE	APPROVED
	B	REDRAWN & REV. P-6077 SK	7-30-69	FCY
	C	REVISED PC-5579 WM	10-8-70	me
	D	REVISED PC-5578 TC	2-23-77	L.D.
	E	REV/0610-0094-98	2-4-99	ME/JS
	E1	REV PER ECR 05-013140	10/20/05	KE/TM

1	WIRE TERMINAL	50846	BODY: COPPER (ASTM B152) NICKEL PLATE (QQ-N-290) .0003 AVG EXT. THK.	
			SLEEVE: COPPER (ASTM B152) NICKEL PL (QQ-N-290).00003 AVG. EXT. THK.	
			INSULATION: TEFLON (ASTM D3295) COLOR: BLACK	
QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS $\pm$.008 ANGLES $\pm$ 5°		CONTRACT NO. 11	AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
MATERIAL SEE TABLE	DR. Stone Kautz	7-29-69	NAME WIRE TERMINAL	
	CHK F.L. Jones	7-30-69	PIDG™ STRATO-THERM - RING TONGUE	
	APPD J. W. Abel	8-6-69	WIRE SIZE: 12-10	
	REL J.M. Ensmus	8-6-69	SIZE B CODE IDENT NO. 00779 NUMBER 50846	
	DSGN APPD		SCALE NTS SHEET 10F1	
OTHER APPD				