




FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE



mat'l. code SEE NOTE 3					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC																
ltr		ecn no		dr		date		tolerances unless otherwise specified					title														
J		V90523		HTB		3/1/99		angles		linear		.XX±.01/.3		INCH/MM		4 ROW R/A HEADER											
K		V00262		JWS		1/26/00						.XXX±.005/.13				SOLDER TO BOARD, 0 G.P.											
L		V05-0740		DAI		10/7/05		0'±2'				.XXXX±.0020/.051		scale 1:1													
M		V05-1040		HTB		11/14/05		dr		D.SHEAFFER		6/5/91				dwg no					sheet 1 of 3		size				
N		M06-0283		MHT		7/27/06		enrg		S.CLARK		6/5/91				50122					A3						
								chr		S.CLARK		6/5/91															
								appd		S.CLARK		6/5/91				type					Product		Customer		Drawing		
sheet index		revision sheet		N		N		N																			


form: A3





FCIconnect.com

Copyright FCI

PRODUCT NO.
SEE TABLE



SECTION U-U



SECTION X-X


mat'l. code SEE NOTE 3		surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM scale 1:1	product family HPC
ltr	ecm	no	dr	date	title
N					4 ROW R/A HEADER SOLDER TO BOARD, 0 G.P.
					dwg no
					sheet 2 of 3 size
					50122 A3
					type Product Customer Drawing
sheet	revision				
index	sheet				

form: A3


PRODUCT NUMBER	NUMBER OF POSITIONS SEE NOTE 2	TAIL LENGTH REF.	TERMINAL PLATING
50122 -1YYYY	YYY	.180/4.57	30μ"/.76μ GOLD
50122 -1YYYJ	YYY	.120/3.05	30μ"/.76μ GOLD
50122 -3YYYY	YYY	.180/4.57	50μ"/1.27μ GOLD
50122 -3YYYJ	YYY	.120/3.05	50μ"/1.27μ GOLD
50122 -5YYYY	YYY	.180/4.57	30μ"/.76μ GXT
50122 -5YYYYLF	YYY	.180/4.57	30μ"/.76μ GXT
50122 -5YYYJ	YYY	.120/3.05	30μ"/.76μ GXT
50122 -5YYYJLF	YYY	.120/3.05	30μ"/.76μ GXT

NOTES:

1. PRODUCT NUMBERING CODE:



PRODUCT NUMBERING CODE FOR SELECT LOAD PART NUMBERS:



- THIS PRODUCT IS CONFIGURED IN SIZES OF 6 THRU 100 COLUMNS IN INCREMENTS OF ONE.
i.e.: 6,7,8,9,.....98,99,100.
- HOUSING MATERIAL: GLASS AND MINERAL FILLED HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER UL94V-0. COLOR: BLACK.
PIN MATERIAL: PHOS. BRONZE
- MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE PER BUS-12-108.
- LENGTH FORMULAS:
DIM "A" = .100/2.54 x NO. OF COLUMNS + .75/19.1
DIM "B" = .100/2.54 x NO. OF COLUMNS + .450/11.43
DIM "C" = .100/2.54 x NO. OF COLUMNS - .100/2.54

- THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

mat'l. code SEE NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecr	no	dr	date	tolerances unless otherwise specified		title
N					angles linear .XX±.01/.3		4 ROW R/A HEADER
					0'±2' .XXX±.005/.13		SOLDER TO BOARD, 0 G.P.
					XXXX±.0020/.051		scale 1:1
				dr	D.SHEAFFER 6/5/91		dwg no
				enr	S.CLARK 6/5/91		sheet 3 of 3 size
				chr	S.CLARK 6/5/91		50122 A3
				appd	S.CLARK 6/5/91		type Product Customer Drawing
sheet index	revision sheet						

form: A3