

Features


- High-speed: $t_{PD} = 1.8\text{ns}$ typical
- Broad operating range: $V_{CC} = 1.8\text{V} - 3.6\text{V}$
- Power down high-impedance inputs/outputs
- High output drive: $\pm 24\text{mA}$ at $3\text{V } V_{CC}$
- Package: 5-pin space saving SOT23 and SC70

Description


The PI74ST1G126 is a buffer with 3-state output that operates over the 1.8V to $3.6\text{V } V_{CC}$ operating range.

Pericom's PI74ST series of products are produced using the Company's advanced submicron technology.

Pinout



Block Diagram



Pin Description

Pin Names	Description
A_{IN}	Input
OE	Input
Y_{OUT}	Output

Function Table

Inputs		Output
OE	A_{IN}	Y_{OUT}
H	L	L
H	H	H
L	X	Z

Notes:

H = HIGH Logic Level
 L = LOW Logic Level
 X = Don't Care
 Z = HIGH Impedance State

Recommended Operating Conditions⁽¹⁾

Parameter	Condition	Min.	Max.	Units
Supply Voltage (V_{CC})		1.8	3.6	V
Input Voltage (V_{IN})		0	5.5	
Output Voltage (V_{OUT})		0	V_{CC}	
Operating Temperature		-40	85	°C
Input Rise and Fall Time (t_r, t_f)	$V_{CC} = 1.8\text{V}, 2.5\text{V} \pm 0.2\text{V}$	0	20	ns/V
	$V_{CC} = 3.3\text{V}, \pm 0.3\text{V}$	0	10	

Note:

1. Unused inputs must be held HIGH or LOW. They may not float.

Absolute Maximum Ratings

Supply Voltage (V_{CC})	–0.5V to +4V
DC Input Voltage (V_{IN})	–0.5V to +6V
DC Output Voltage (V_{OUT})	–0.5V to +6V
DC Input Diode Current (I_{IK})	–50mA to 20mA
DC Output Diode Current (I_{OK})	–50mA to 20mA
DC Output Current (I_{OUT})	±50mA
DC V_{CC} /GND Current (I_{CC}/I_{GND})	±50mA
Storage Temperature (T_{STG})	–65°C to +150°C
Junction Lead Temperature (IOS)	200°C
Power Dissipation SOT23	200mW
SC70	150mW

Note:

Absolute maximum ratings are DC values beyond which the device may be damaged or have its useful life impaired. The datasheet specifications should be met, without exception, to ensure that the system design is reliable over its power supply, temperature, and output/input loading variables. Pericom does not recommend operation outside datasheet specifications.

DC Electrical Characteristics (Over supply voltage and operating temperature ranges, unless otherwise specified)

Symbol	Parameter	V_{CC} (V)	Conditions		$T_A = +25^\circ\text{C}$			$T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$		Units
					Min.	Typ.	Max.	Min.	Max.	
V_{IH}	HIGH Level Input Voltage	1.8 2.3-3.6			$0.75V_{CC}$ $0.70V_{CC}$			$0.75V_{CC}$ $0.70V_{CC}$		V
V_{IL}	LOW Level Input Voltage	1.8 2.3-3.6					$0.25V_{CC}$ $0.30V_{CC}$		$0.25V_{CC}$ $0.30V_{CC}$	
V_{OH}	HIGH Level Output Voltage	1.8	$V_{IN} = V_{IH}$	$I_{OH} = -100\mu\text{A}$	1.7	1.79		1.7		
		2.3			2.2	2.29		2.2		
		3.0			2.9	2.99		2.9		
		2.3		$I_{OH} = -8\text{mA}$	1.9	2.13		1.9		
V_{OL}	LOW Level Output Voltage	3.0		$I_{OH} = -16\text{mA}$	2.4	2.71		2.4		
		3.0		$I_{OH} = -24\text{mA}$	2.3	2.55		2.3		
		1.8	$V_{IN} = V_{IL}$	$I_{OL} = 100\mu\text{A}$		0.01	0.1		0.1	
		2.3				0.01	0.1		0.1	
		3.0				0.00	0.1		0.1	
I_{IN}	Input Leakage Current	2.3		$I_{OL} = 8\text{mA}$		0.10	0.3		0.3	μA
		3.0		$I_{OL} = 16\text{mA}$		0.18	0.4		0.4	
		3.0		$I_{OL} = 24\text{mA}$		0.28	0.55		0.55	
I_{OFF}	Power Off Leakage Current	0.0	V_{IN} or $V_{OUT} = 5.5\text{V}$		–1		1	–1	1	
I_{CC}	Quiescent Supply Current	1.8-3.6	$V_{IN} = 5.5\text{V}$, GND				2.0		20	
I_{OZ}	3-State Output Leakage	1.8-3.6	$V_{IN} = V_{IH}$ or V_{IL} $V_O = V_{CC}$ or GND				±1		±10	

AC Electrical Characteristics

Symbol	Parameter	V _{CC} (V)	Conditions	T _A = +25°C			T _A = -40°C to +85°C		Units	Fig. No.
				Min.	Typ.	Max.	Min.	Max.		
t _{PLH} , t _{PHL}	Propagation Delay	1.8 2.5 ±0.2 3.3 ±0.3	C _L = 15pF, R _L = 1MΩ S ₁ = Open	2.0 0.8 0.5	2.7 1.7 1.1	3.6 2.3 1.6	2.0 0.8 0.5	4.0 2.6 1.8	ns	1 3
t _{PLH} , t _{PHL}	Propagation Delay	3.3 ±0.3	C _L = 50pF, R _L = 500Ω, S ₁ = Open	1.5	2.7	3.6	1.5	4.0		1 3
t _{pZL} t _{pZH}	Output Enable Time	1.8 2.5 ±0.2 3.3 ±0.3	C _L = 50pF, R _D = 500Ω R _U = 500Ω, S ₁ = GND for t _{pZH} S ₁ = V _{IN} for t _{pZL} V _{IN} = 2xV _{CC}	2.0 1.5 1.5	5.9 4.0 3.0	7.8 5.4 4.1	2.0 1.5 1.5	8.6 6.0 4.5		1 3
t _{PLZ} t _{PHZ}	Output Disable Time	1.8 2.5 ±0.2 3.3 ±0.3	C _L = 50pF, R _D = 500Ω R _U = 500Ω, S ₁ = GND for t _{PHZ} S ₁ = V _{IN} for t _{PLZ} , V _{IN} = 2xV _{CC}	2.0 1.0 1.0	5.4 4.0 3.2	6.4 4.8 3.8	2.0 1.0 1.0	7.1 5.3 4.2		1 3
C _{IN} C _{OUT}	Input Capacitance Output Capacitance	V _{IN} = 0 V _{OUT} = 0			4 8				pF	
C _{PD}	Power Dissipation Capacitance	3.3	Note 3		17					2

Notes:

3. C_{PD} is defined as the value of the internal equivalent capacitance which is derived from dynamic operating current consumption (I_{CCD}) at no output loading and operating at 50% duty cycle (see Figure 2). C_{PD} is related to I_{CCD} dynamic operating current by the expression: I_{CCD} = (C_{PD})(V_{CC})(f_{IN}) + (I_{CC} static).

AC Loading and Waveforms




Figure 1. AC Test Circuit




Figure 2. I_{CCD} Test Circuit





Figure 3. AC Waveforms



Technical drawing of a rectangular component with dimensions in inches and millimeters. The drawing includes a top view, a side view, and a detail view of a fillet.

Top View Dimensions:

- Top edge: .075 [1.90] BSC
- Right edge: .059 [1.50] / .068 [1.75]
- Bottom edge: .102 [2.60] / .118 [3.00]
- Left edge: .037 [0.95] BSC
- Bottom edge (inner): .014 [0.35] / .019 [0.50]

Side View Dimensions:

- Top edge: .110 [2.80] / .118 [3.00]
- Right edge: .057 [1.45] MAX.
- Bottom edge: .000 [0.00] / .005 [0.15]

Detail View Dimensions:

- Top edge: .004 [0.10] / .023 [0.60]
- Angle: 0° - 10°

Legend:

- X.XX DENOTES DIMENSIONS IN MILLIMETERS

Technical drawing of a 5-pin D-subminiature connector housing. The drawing includes a top view, a side view, and a cross-sectional view (View A). Dimensions are provided in millimeters, with some values in brackets indicating maximum values.

Top View Dimensions:

- Overall width: $.079$ $[2.00]$ BSC
- Pin 5 to Pin 4 spacing: $.051$ $[1.30]$ BSC
- Pin 5 to Pin 4 spacing (center-to-center): $.083$ $[2.10]$ BSC
- Pin 5 to Pin 4 spacing (center-to-center): $.049$ $[1.25]$ BSC
- Pin 1 to Pin 2 spacing: $.026$ $[0.65]$ BSC
- Pin 2 to Pin 3 spacing: $.006$ $[0.15]$ $[0.30]$
- Pin 1 to Pin 2 spacing (center-to-center): $.011$ $[0.15]$ $[0.30]$

Side View Dimensions:

- Overall height: $.083$ $[2.10]$ BSC
- Pin 5 to Pin 4 spacing (center-to-center): $.049$ $[1.25]$ BSC
- Pin 1 to Pin 2 spacing (center-to-center): $.011$ $[0.15]$ $[0.30]$

View A Dimensions:

- Overall width: $.079$ $[2.00]$ BSC
- Pin 5 to Pin 4 spacing (center-to-center): $.049$ $[1.25]$ BSC
- Pin 1 to Pin 2 spacing (center-to-center): $.011$ $[0.15]$ $[0.30]$
- Pin 5 to Pin 4 spacing (center-to-center): $.083$ $[2.10]$ BSC
- Pin 1 to Pin 2 spacing (center-to-center): $.011$ $[0.15]$ $[0.30]$
- Pin 5 to Pin 4 spacing (center-to-center): $.049$ $[1.25]$ BSC
- Pin 1 to Pin 2 spacing (center-to-center): $.011$ $[0.15]$ $[0.30]$
- Pin 5 to Pin 4 spacing (center-to-center): $.083$ $[2.10]$ BSC
- Pin 1 to Pin 2 spacing (center-to-center): $.011$ $[0.15]$ $[0.30]$

Notes:

- Controlling dimensions in millimeters
- Ref: JEDEC MO-203AA

Part	Pin-Package	Top Markting	Operating Range
PI74ST1G126TX	5-Pin - SOT23	L7E	−40°C to 85°C
PI74ST1G126CX	5-Pin - SC70	L7E	−40°C to 85°C