




(1.27 mm) .050"

CFT, CFS SERIES

COMPACT FLASH TERMINALS & SOCKETS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?CFT or www.samtec.com?CFS

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material (CFT):

Phosphor Bronze

Contact Material (CFS):

BeCu

Plating:

Sn or Au over
50µ" (1.27 µm) Ni

Operating Temp Range:

CFT = -55 °C to +105 °C Tin

CFT = -55 °C to +125 °C Gold

CFS = -55 °C to +125 °C

Insertion Depth (CFS):

(3.05 mm) .120" min

Insertion Force (CFS):

(Single contact only)

3.3 oz (0.92 N) avg.

Withdrawal Force (CFS):

(Single contact only)

2.5 oz (0.70 N) avg.

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

CFT = (0.15 mm) .006" max


CFS = 0.10 mm) .004" max

RoHS Compliant:

Yes

APPLICATIONS

Reflowed solder
forced into lock notch



RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

**TIGER
EYE**
CONTACT

Note:
Some lengths, styles and options are non-standard, non-returnable.

CFT - 125 - LEAD STYLE - PLATING OPTION - D - RA - CARD LENGTH - SL

Mates with:
CFS

Specify
LEAD
STYLE
from chart

-L

= 10µ" (0.25 µm) Gold on post,
Matte Tin on tail

-S


= 30µ" (0.76 µm) Gold on post,
Matte Tin on tail

-01

= (25.40 mm) 1.00"
Card Length

-02


= (50.80 mm) 2.00"
Card Length



LEAD STYLE	Y
-01	(6.35) .250
-02	(8.89) .350

POSITION NUMBER	C (POST)
(3.50) .138	(3.50) .138
(5.00) .197	(5.00) .197
(4.25) .167	(4.25) .167

-RA OPTION



CFS - 1 - NO. PINS PER ROW - CARD THICKNESS - PLATING OPTION - D

Mates with:
CFS

25

-01

= (0.80 mm) .031" thick board

-02


= (1.60 mm) .062" thick board

-L

= 10µ" (0.25 µm) Gold on contact,
Matte Tin on tail

-S

= 30µ" (0.76 µm) Gold on contact,
Matte Tin on tail



CARD THICKNESS	A	B	C
-01	(1.02) .040	(1.79) .070	(3.12) .123
-02	(1.70) .067	(2.46) .097	(2.77) .109

WWW.SAMTEC.COM

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.