


## High Ohmic (up to 10 M $\Omega$ )/High Voltage (up to 3.5 kV) Metal Film Leaded Resistors



A homogenous film of metal alloy is deposited on a high grade ceramic body. After a helical groove has been cut in the resistive layer, tinned electrolytic copper wires are welded to the end-caps. The resistors are coated with a blue, non-flammable lacquer, which provides electrical, mechanical, and climatic protection.

### FEATURES

- Technology: Metal film
- High pulse loading (up to 10 kV) capability
- Small size (0207/0411)
- Compatible with lead (Pb)-free and lead containing soldering processes
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS**  
COMPLIANT

### APPLICATIONS

- Power supplies
- Electronic ballast
- White goods
- Television

| TECHNICAL SPECIFICATIONS               |       |                       |                        |                       |                        |
|----------------------------------------|-------|-----------------------|------------------------|-----------------------|------------------------|
| DESCRIPTION                            | UNIT  | HVR25                 |                        | HVR37                 |                        |
| Resistance Range                       | Ω     | 100K to 10M           |                        | 100K to 10M           |                        |
| Resistance Tolerance                   | %     | ± 5;<br>E24 series    | ± 1;<br>E24/E96 series | ± 5;<br>E24 series    | ± 1;<br>E24/E96 series |
| Temperature Coefficient                | ppm/K | ± 200                 |                        |                       |                        |
| Climatic Category<br>(LCT/UCT/days)    |       | 55/155/56             |                        |                       |                        |
| Rated Dissipation, $P_{70}$            | W     | 0.25                  |                        | 0.5                   |                        |
| Maximum Permissible Voltage $U_{\max}$ |       |                       |                        |                       |                        |
| DC                                     | V     | 1600                  |                        | 3500                  |                        |
| RMS                                    |       | 1150                  |                        | 2500                  |                        |
| Basic Specification                    |       | IEC 60115-1           |                        |                       |                        |
| Stability After:                       |       |                       |                        |                       |                        |
| Load (1000 h, $P_{70}$ )               |       | ± (5 % $R$ + 0.1 Ω)   | ± (1.5 % $R$ + 0.1 Ω)  | ± (5 % $R$ + 0.1 Ω)   | ± (1.5 % $R$ + 0.1 Ω)  |
| Long Term Damp Heat Test (56 days)     |       | ± (1.5 % $R$ + 0.1 Ω) | ± (1.5 % $R$ + 0.1 Ω)  | ± (1.5 % $R$ + 0.1 Ω) | ± (1.5 % $R$ + 0.1 Ω)  |
| Soldering (10 s, 260 °C)               |       | ± (1 % $R$ + 0.1 Ω)   | ± (1 % $R$ + 0.1 Ω)    | ± (1 % $R$ + 0.1 Ω)   | ± (1 % $R$ + 0.1 Ω)    |

**PART NUMBER AND PRODUCT DESCRIPTION <sup>(1)</sup>**

Part Number: HVR2500001503JA100

|   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| H | V | R | 2 | 5 | 0 | 0 | 0 | 0 | 1 | 5 | 0 | 3 | J | A | 1 | 0 | 0 |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|

| MODEL/SIZE         | VARIANT     | TCR/MATERIAL | VALUE                                                                                                                     | TOLERANCE              | PACKAGING <sup>(2)</sup> | SPECIAL                         |
|--------------------|-------------|--------------|---------------------------------------------------------------------------------------------------------------------------|------------------------|--------------------------|---------------------------------|
| HVR2500<br>HVR3700 | 0 = Neutral | 0 = Standard | 3 digit value<br>1 digit multiplier<br>MULTIPLIER<br>3 = *10 <sup>3</sup><br>4 = *10 <sup>4</sup><br>5 = *10 <sup>5</sup> | F = ± 1 %<br>J = ± 5 % | A1<br>A5<br>R5<br>N4     | Up to 2 digits<br>00 = Standard |

Product Description: HVR25 5 % A1 150K


|                |                |                          |                                 |
|----------------|----------------|--------------------------|---------------------------------|
| HVR25          | 5 %            | A1                       | 150K                            |
| Model          | TOLERANCE      | PACKAGING <sup>(2)</sup> | RESISTANCE VALUE                |
| HVR25<br>HVR37 | ± 1 %<br>± 5 % | A1<br>A5<br>R5<br>N4     | 150K = 150 kΩ<br>4M64 = 4.64 MΩ |

**Notes**


- (1) The PART NUMBER is shown to facilitate the introduction of the unified part numbering system  
(2) Please refer to table PACKAGING, see next page

**PACKAGING**

| MODEL | TAPING       | AMMO PACK |      | REEL   |      |
|-------|--------------|-----------|------|--------|------|
|       |              | PIECES    | CODE | PIECES | CODE |
| HVR25 | Axial, 52 mm | 5000      | A5   | 5000   | R5   |
|       |              | 1000      | A1   |        |      |
|       | Radial       | 4000      | N4   |        |      |
| HVR37 | Axial, 52 mm | 1000      | A1   | 5000   | R5   |

**DIMENSIONS**

**DIMENSIONS - Resistor types, mass and relevant physical dimensions**

| TYPE  | L <sub>1</sub> max.<br>(mm) | L <sub>2</sub> max.<br>(mm) | D <sub>max</sub> .<br>(mm) | Ø d<br>(mm) | A<br>(mm)  | MASS<br>(mg) |
|-------|-----------------------------|-----------------------------|----------------------------|-------------|------------|--------------|
| HVR25 | 6.5                         | 7.5                         | 2.5                        | 0.58 ± 0.05 | 52.5 ± 1.5 | 220          |
| HVR37 | 10                          | 12                          | 4                          | 0.70 ± 0.03 | 52.5 ± 1.5 | 500          |

**PRODUCTS WITH RADIAL LEADS (HVR25)**


| DIMENSIONS - Radial taping |                                                 |       |           |      |
|----------------------------|-------------------------------------------------|-------|-----------|------|
| SYMBOL                     | PARAMETER                                       | VALUE | TOLERANCE | UNIT |
| P                          | Pitch of components                             | 12.7  | $\pm 1.0$ | mm   |
| P <sub>0</sub>             | Feed-hole pitch                                 | 12.7  | $\pm 0.2$ | mm   |
| P <sub>1</sub>             | Feed-hole centre to lead at topside at the tape | 3.85  | $\pm 0.5$ | mm   |
| P <sub>2</sub>             | Feed-hole center to body center                 | 6.35  | $\pm 1.0$ | mm   |
| F                          | Lead-to-lead distance                           | 4.8   | +0.7/-0   | mm   |
| W                          | Tape width                                      | 18.0  | $\pm 0.5$ | mm   |
| W <sub>0</sub>             | Minimum hold down tape width                    | 5.5   | -         | mm   |
| H <sub>1</sub>             | Component height                                | 29    | Max.      | mm   |
| H <sub>0</sub>             | Lead wire clinch height                         | 16.5  | 0.5       | mm   |
| H                          | Height of component from tape center            | 19.5  | $\pm 1$   | mm   |
| D <sub>0</sub>             | Feed-hole diameter                              | 4.0   | $\pm 0.2$ | mm   |
| L                          | Maximum length of snapped lead                  | 11.0  | -         | mm   |
| L <sub>1</sub>             | Minimum lead wire (tape portion) shortest lead  | 2.5   | -         | mm   |


**Note**

- Please refer document number 28721 "Packaging" for more detail

**MARKING**

The nominal resistance and tolerance are marked on the resistor using four or five colored bands in accordance with IEC 60062, marking codes for resistors and capacitors. Standard values of nominal resistance are taken from the E24 and E24/E96 series for resistors with a tolerance of  $\pm 5\%$  or  $\pm 1\%$  respectively. The values of the E24/E96 series are in accordance with IEC 60063. Yellow and grey are used instead of gold and silver because metal particles in the lacquer could affect high-voltage properties.

## FUNCTIONAL PERFORMANCE




### Derating - Standard Operation

Maximum dissipation ( $P_{max}$ ) in percentage of rated power as a function of ambient temperature ( $T_{amb}$ )


## PULSE LOADING CAPABILITY

### Note

- Maximum allowed peak pulse voltage in accordance with IEC 60065, 14.1.a; 50 discharges from a 1 nF capacitor charged to  $U_{max}$ ; 12 discharges/min



**HVR25**  
 $\Delta R = \pm (4.0 \% R + 0.1 \Omega)$



**HVR37**  
 For 5 % tolerance  $\Delta R = \pm (4.0 \% R + 0.1 \Omega)$   
 For 1 % tolerance  $\Delta R = \pm (2.0 \% R + 0.1 \Omega)$

**TESTS AND REQUIREMENTS**

Essentially all tests are carried out in accordance with IEC 60115-1, category 55/155/56 (rated temperature range - 55 °C to + 155 °C; damp heat, long term, 56 days) and along the lines of IEC 60068-2-xx test method. The tests are carried out under standard atmospheric conditions according to IEC 60068-1, 5.3 unless otherwise specified. In some instances deviations from IEC recommendations were necessary for our method of specifying.

| PERFORMANCE              |                                        |                                           |                                                                                                                                                                                                         |                                                              |                    |
|--------------------------|----------------------------------------|-------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------|--------------------|
| IEC<br>60115-1<br>CLAUSE | IEC<br>60068-2-xx<br>TEST<br>METHOD    | TEST                                      | PROCEDURE                                                                                                                                                                                               | REQUIREMENTS<br>PERMISSIBLE CHANGE ( $\Delta R$ )            |                    |
|                          |                                        |                                           |                                                                                                                                                                                                         | HVR25                                                        | HVR37              |
| 4.8                      | -                                      | Temperature coefficient                   | Between -55 °C and +155 °C                                                                                                                                                                              | $\pm 200$ ppm/K                                              |                    |
| 4.25.1                   | -                                      | Endurance at 70 °C                        | 1000 h;<br>loaded with $P_{70}$ or $U_{max}$ ;<br>1.5 h ON; 0.5 h OFF<br><br>for 5 % tolerance<br>for 1 % tolerance                                                                                     | $\pm (5 \% R + 0.1 \Omega)$<br>$\pm (1.5 \% R + 0.1 \Omega)$ |                    |
| 4.24                     | 78 (Cab)                               | Damp heat, steady state                   | 56 days; 40 °C;<br>90 % to 95 % RH<br>loaded with 0.01 $P_{70}$<br><br>for 5 % tolerance<br>for 1 % tolerance                                                                                           | $\pm (5 \% R + 0.1 \Omega)$<br>$\pm (1.5 \% R + 0.1 \Omega)$ |                    |
| 4.23                     | 2 (Ba)<br>30 (Db)<br>1 (Aa)<br>30 (Db) | Climatic sequence                         | 16 h, 155 °C<br><br>24 h; 25 °C to 55 °C<br>90 % to 100 % RH; 1 cycle<br><br>2 h, -55 °C<br><br>5 days; 25 °C to 55 °C<br>90 to 100 % RH                                                                | $\pm (1.5 \% R + 0.1 \Omega)$                                |                    |
| 4.23.2                   |                                        | Dry heat                                  |                                                                                                                                                                                                         |                                                              |                    |
| 4.23.3                   |                                        | Damp heat, cyclic                         |                                                                                                                                                                                                         |                                                              |                    |
| 4.23.4                   |                                        | Cold                                      |                                                                                                                                                                                                         |                                                              |                    |
| 4.23.6                   |                                        | Damp heat, (accelerated) remaining cycles |                                                                                                                                                                                                         |                                                              |                    |
| 4.19                     | 14 (Na)                                | Rapid change of temperature               | 30 min at LCT;<br>30 min at UCT;<br>LCT = -55 °C;<br>UCT = 155 °C;<br>5 cycles                                                                                                                          | No visual damage<br>$\pm (1 \% R + 0.1 \Omega)$              |                    |
| 4.13                     | -                                      | Short time overload                       | Room temperature;<br>dissipation 6.25 x $P_{70}$<br>(voltage not more than 2 x limiting voltage,<br>10 000 $V_{max}$ .);<br>10 cycles 5 s ON and 45 s OFF<br><br>for 5 % tolerance<br>for 1 % tolerance | $\pm (2 \% R + 0.1 \Omega)$<br>$\pm (1 \% R + 0.1 \Omega)$   |                    |
| 4.12                     | -                                      | Noise                                     | IEC 60195                                                                                                                                                                                               | Max. 5 $\mu V/V$                                             | Max. 2.5 $\mu V/V$ |
| 4.16                     | 21 (Ua1)<br>21 (Ub)<br>21 (Uc)         | Robustness of terminations:               | Load 10 N; 10 s<br><br>Load 5 N; 4 x 90°<br><br>3 x 360° in opposite direction                                                                                                                          | No damage<br>$\pm (1 \% R + 0.1 \Omega)$                     |                    |
| 4.16.2                   |                                        | Tensile all samples                       |                                                                                                                                                                                                         |                                                              |                    |
| 4.16.3                   |                                        | Bending half number of samples            |                                                                                                                                                                                                         |                                                              |                    |
| 4.16.4                   |                                        | Torsion other half of samples             |                                                                                                                                                                                                         |                                                              |                    |
| 4.22                     | 6 (Fc)                                 | Vibration                                 | Frequency 10 Hz to 500 Hz;<br>displacement 1.5 mm or acceleration 10 g;<br>3 directions;<br>total 6 h (3 x 2 h)                                                                                         | $\pm (1.0 \% R + 0.1 \Omega)$                                |                    |



| <b>PERFORMANCE</b>       |                                     |                                 |                                                                                              |                                                              |       |
|--------------------------|-------------------------------------|---------------------------------|----------------------------------------------------------------------------------------------|--------------------------------------------------------------|-------|
| IEC<br>60115-1<br>CLAUSE | IEC<br>60068-2-xx<br>TEST<br>METHOD | TEST                            | PROCEDURE                                                                                    | REQUIREMENTS<br>PERMISSIBLE CHANGE ( $\Delta R$ )            |       |
|                          |                                     |                                 |                                                                                              | HVR25                                                        | HVR37 |
| 4.17                     | 20 (Ta)                             | Solderability<br>(after ageing) | 2 s; 235 °C: Solder bath method;<br>SnPb40<br>3 s; 245 °C: Solder bath method;<br>SnAg3Cu0.5 | Good tinning<br>( $\geq 95$ % covered);<br>no visible damage |       |
| 4.18                     | 20 (Tb)                             | Resistance to<br>soldering heat | Thermal shock: 10 s; 260 °C;<br>3 mm from body                                               | $\pm (1 \% R + 0.1 \Omega)$                                  |       |
| 4.29                     | 45 (XA)                             | Component solvent<br>resistance | Isopropyl alcohol                                                                            | No visible damage                                            |       |
| 4.6.11                   | -                                   | Insulation resistance           | $U = 500 V_{DC}$<br>during 1 min,<br>V-block method                                          | $R_{ins}$ min. 104 M $\Omega$                                |       |
| 4.7                      | -                                   | Voltage proof on<br>insulation  | $U_{RMS} = 700 V$<br>during 1 min,<br>V-block method                                         | No flashover or breakdown                                    |       |

**12NC INFORMATION FOR HISTORICAL CODING REFERENCE ONLY**

- The resistors have a 12 digit ordering code starting with 2306
- The next 4 or 5 digits indicate the resistor type and packaging
- For 5 % tolerance the last 3 digits indicate the resistance value:
  - The first 2 digits indicate the resistance value
  - The last digit indicates the resistance decade in accordance with table
- For 1 % tolerance the last 4 digits indicate the resistance value:
  - The first 3 digits indicate the resistance value
  - The last digit indicates the resistance decade in accordance with table

**Last Digit of 12NC Indicating Resistance Decade**

| RESISTANCE<br>DECADE (5 %)       | RESISTANCE<br>DECADE (1 %)       | LAST DIGIT |
|----------------------------------|----------------------------------|------------|
| 100 k $\Omega$ to 910 k $\Omega$ | 100 k $\Omega$ to 976 k $\Omega$ | 4          |
| 1 M $\Omega$ to 9.1 M $\Omega$   | 1 M $\Omega$ to 9.76 M $\Omega$  | 5          |
| = 10 M $\Omega$                  | = 10 M $\Omega$                  | 6          |

**12NC Example**

HVR25, 150 k $\Omega$ ,  $\pm 5$  %, ammpack 1000 pieces is  
**2306 241 13154**

| <b>12NC - resistor type and packaging</b> |            |           |                       |            |            |                      |
|-------------------------------------------|------------|-----------|-----------------------|------------|------------|----------------------|
| DESCRIPTION                               |            |           | 2306 ... ..           |            |            |                      |
|                                           |            |           | BANDOLIER IN AMMOPACK |            |            | BANDOLIER<br>ON REEL |
| TYPE                                      | TAPE WIDTH | TOLERANCE | RADIAL TAPED          | 1000 UNITS | 5000 UNITS | 5000 UNITS           |
|                                           |            |           | 4000 UNITS            |            |            |                      |
| HVR25                                     | 52.5       | $\pm 5$ % | 241 36...             | 241 13...  | 241 53...  | 241 23...            |
|                                           |            | $\pm 1$ % | 241 0....             | 241 8....  | 241 7....  | 241 6....            |
| HVR37                                     | 52.5       | $\pm 5$ % | -                     | 242 13...  | -          | 242 23...            |
|                                           |            | $\pm 1$ % | -                     | 242 8....  | -          | 242 6....            |



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**