

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

105027-8001

Status:


Active

Overview:

microSD Memory Card Connector

Description:

1.10mm, 0.75mm, 0.70mm Pitch microSD Card Header with Detect Switch (VDD), Height 1.70mm, Lead-Free



Series

image - Reference only

Documents:

3D Model

Drawing (PDF)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Memory Card Sockets
Series	105027
Comments	Ground Pin located between Pin 4 and 5
Component Type	I/O Header (Card)
Overview	microSD Memory Card Connector
Product Name	microSD Card, TransFlash
Style	Guide and Holder
Type	N/A
UPC	884982118096

Physical

Card Detection Switch	Yes
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	10,000
Ejector Button	No
Ejector Button Side	N/A
Entry Angle	Horizontal
Keying to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	0.721/g
PCB Locator	No
PCB Mounting Side	Normal
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.09mm
Pitch - Termination Interface	1.09mm
Plating min - Mating	0.762µm
Plating min - Termination	0.051µm
Ports	1
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	5V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	2
Lead-free Process Capability	Reflow Capable (SMT only)

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

105027Series

Mates With

Standard SIM Card

Use With

microSD Card

Max. Cycles at Max. Process Temperature	2
Process Temperature max. C	255

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-105027-801
---------------	---------------

This document was generated on 01/19/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION