





RECOMMENDED P.C. BOARD LAYOUT



NOTES:

- PIN PUSHOUT FORCE: 4 LBS. MINIMUM (IN EITHER DIRECTION)
- FOR ILLUSTRATION PURPOSES, 20 (DUAL 10) CIRCUIT SIZE IS SHOWN.
- PINS MUST MEET MOLEX SOLDERABILITY SPECIFICATION ES-152, EXCEPT VOIDS ARE PERMISSIBLE AT BANDOLIER PIN FAYING SURFACE (APPROX. .025 LONG X .006 WIDE REF.- 2 LOCATIONS).
- MEASURE POINT FOR PLATING THICKNESS.
- THIS PART CONFORMS TO MOLEX PRODUCT SPECIFICATION PS-8624.
- PACKAGING INFORMATION: (UNLESS OTHERWISE NOTED IN TABLES) PER PACKAGING DRAWING NO. PK-70873-0353 BULK PACKAGED IN BAGS

MATERIAL:

WAFER - GLASS FILLED POLYESTER; UL94V-0; COLOR: BLACK
PIN - PHOSPHOR BRONZE

PLATING:

- TIN - .000150 MINIMUM TIN PLATE OVER .000050 MINIMUM NICKEL PLATE.
- 15 GOLD - .000015 MINIMUM GOLD PLATE IN SELECT AREA, .000075 MINIMUM TIN PLATE IN SELECT AREA, OVER .000050 MINIMUM NICKEL PLATE OVERALL.
- 30 GOLD - .000030 MINIMUM GOLD PLATE IN SELECT AREA, .000075 MINIMUM TIN PLATE IN SELECT AREA, OVER .000050 MINIMUM NICKEL PLATE OVERALL.
- D30 GOLD - .000030 MINIMUM GOLD PLATE IN SELECT AREAS OVER .000050 MINIMUM NICKEL PLATE OVERALL.
- 5 GOLD - .000005 MINIMUM GOLD FLASH IN SELECT AREA, .000075 MINIMUM TIN PLATE IN SELECT AREA, OVER .000050 MINIMUM NICKEL PLATE OVERALL.

*THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC". CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD.

CKT. SIZE	DIMENSION A		DIMENSION B	
	(MM)	INCH	(MM)	INCH
4	(2.54)	.100	(4.83)	.190
6	(5.08)	.200	(7.37)	.290
8	(7.62)	.300	(9.91)	.390
10	(10.16)	.400	(12.45)	.490
12	(12.70)	.500	(14.99)	.590
14	(15.24)	.600	(17.53)	.690
16	(17.78)	.700	(20.07)	.790
18	(20.32)	.800	(22.61)	.890
20	(22.86)	.900	(25.15)	.990
22	(25.40)	1.000	(27.69)	1.090
24	(27.94)	1.100	(30.23)	1.190
26	(30.48)	1.200	(32.77)	1.290
28	(33.02)	1.300	(35.31)	1.390
30	(35.56)	1.400	(37.85)	1.490
32	(38.10)	1.500	(40.39)	1.590
34	(40.64)	1.600	(42.93)	1.690
36	(43.18)	1.700	(45.47)	1.790
38	(45.72)	1.800	(48.01)	1.890
40	(48.26)	1.900	(50.55)	1.990
42	(50.80)	2.000	(53.09)	2.090
44	(53.34)	2.100	(55.63)	2.190
46	(55.88)	2.200	(58.17)	2.290
48	(58.42)	2.300	(60.71)	2.390
50	(60.96)	2.400	(63.25)	2.490
52	(63.50)	2.500	(65.79)	2.590
54	(66.04)	2.600	(68.33)	2.690
56	(68.58)	2.700	(70.87)	2.790
58	(71.12)	2.800	(73.41)	2.890
60	(73.66)	2.900	(75.95)	2.990
62	(76.20)	3.000	(78.49)	3.090
64	(78.74)	3.100	(81.03)	3.190
66	(81.28)	3.200	(83.57)	3.290
68	(83.82)	3.300	(86.11)	3.390
70	(86.36)	3.400	(88.65)	3.490
72	(88.90)	3.500	(91.19)	3.590
74	(91.44)	3.600	(93.73)	3.690
76	(93.98)	3.700	(96.27)	3.790
78	(96.52)	3.800	(98.81)	3.890
80	(99.06)	3.900	(101.35)	3.990

DIMENSIONS SHOWN (METRIC) INCH		UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°	
INCH		METRIC	
3 PLACE ± .005			
2 PLACE ± .01 ± 0.13			
1 PLACE ± 0.25			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			
DRWG. BY: EIK	CHK'D. BY: AAB		
APPROV. BY: WAZ	SCALE: 4 : 1		
FILE NAME: 58624X1		SHEET NO. 1 OF 7	
DATE: 11/30/88		DATE: 11/30/88	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.			

7	P	
6	P	
5	P	
4	P	
3	P	
2	P	
1	P	

REVISIONS

REV.	DATE	DESCRIPTION
1	03/07/88	ADDED EDP NOS. PER ECR # U30114 MGB
2	05/17/93	RELEASED PER ECR # U30114 MGB
3	05/17/93	RELEASED PER ECR # U30114 MGB
4	05/17/93	RELEASED PER ECR # U30114 MGB
5	05/17/93	RELEASED PER ECR # U30114 MGB
6	05/17/93	RELEASED PER ECR # U30114 MGB
7	05/17/93	RELEASED PER ECR # U30114 MGB

I3		I2		I1		I0		9		8		7		6		8624		4		3		2		1	
ENGINEERING NUMBER A-8624		RELEASE FOR MANUFACTURE						C ± (0.38) .015		E ± (0.25) .010		F ± (0.25) .010		PLATING PER NOTES SHEET 1		CONNECTOR END PLATING		H MEAS.		P.C. BOARD END PLATING		K MEAS.		FOR PACKAGING INFORMATION, SEE NOTE 6, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)	
TYPE																TYPE				TYPE					
-0001/-0040		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240		TIN		TIN		(2.54) .100		TIN		(1.27) .050			
-0041/-0080		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240		15 GOLD		GOLD		(2.54) .100		TIN		(1.27) .050			
-0081/-0120		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240		30 GOLD		GOLD		(2.54) .100		TIN		(1.27) .050			
-0121/-0160		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240		TIN		TIN		(2.54) .100		TIN		(1.27) .050		PK-70873-0090 (TUBE)	
-0161/-0200		R.F.M.						(4.45) .175		(12.83) .505		(6.10) .240		TIN		TIN		(2.54) .100		TIN		(1.27) .050			
-0201/-0240		R.F.M.						(4.45) .175		(12.83) .505		(6.10) .240		15 GOLD		GOLD		(2.54) .100		TIN		(1.27) .050			
-0241/-0280		R.F.M.						(4.45) .175		(12.83) .505		(6.10) .240		30 GOLD		GOLD		(2.54) .100		TIN		(1.27) .050			
CKTS	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	CKTS
02	N.A.	A-8624-0001	N.A.	A-8624-0041	N.A.	A-8624-0081	N.A.	A-8624-0121	N.A.	A-8624-0161	N.A.	A-8624-0201	N.A.	A-8624-0241	N.A.	A-8624-0281	N.A.	A-8624-0321	N.A.	A-8624-0361	N.A.	A-8624-0401	N.A.	A-8624-0441	02
04	10-88-1041	A-8624-0002	10-89-1041	A-8624-0042	10-89-2041	A-8624-0082		A-8624-0122	10-88-1042	A-8624-0162	10-89-1042	A-8624-0202	10-89-2042	A-8624-0242	04										
06	10-88-1061	A-8624-0003	10-89-1061	A-8624-0043	10-89-2061	A-8624-0083	10-89-3064	A-8624-0123	10-88-1062	A-8624-0163	10-89-1062	A-8624-0203	10-89-2062	A-8624-0243	06										
08	10-88-1081	A-8624-0004	10-89-1081	A-8624-0044	10-89-2081	A-8624-0084		A-8624-0124	10-88-1082	A-8624-0164	10-89-1082	A-8624-0204	10-89-2082	A-8624-0244	08										
10	10-88-1101	A-8624-0005	10-89-1101	A-8624-0045	10-89-2101	A-8624-0085	10-89-3104	A-8624-0125	10-88-1102	A-8624-0165	10-89-1102	A-8624-0205	10-89-2102	A-8624-0245	10										
12	10-88-1121	A-8624-0006	10-89-1121	A-8624-0046	10-89-2121	A-8624-0086		A-8624-0126	10-88-1122	A-8624-0166	10-89-1122	A-8624-0206	10-89-2122	A-8624-0246	12										
14	10-88-1141	A-8624-0007	10-89-1141	A-8624-0047	10-89-2141	A-8624-0087		A-8624-0127	10-88-1142	A-8624-0167	10-89-1142	A-8624-0207	10-89-2142	A-8624-0247	14										
16	10-88-1161	A-8624-0008	10-89-1161	A-8624-0048	10-89-2161	A-8624-0088		A-8624-0128	10-88-1162	A-8624-0168	10-89-1162	A-8624-0208	10-89-2162	A-8624-0248	16										
18	10-88-1181	A-8624-0009	10-89-1181	A-8624-0049	10-89-2181	A-8624-0089		A-8624-0129	10-88-1182	A-8624-0169	10-89-1182	A-8624-0209	10-89-2182	A-8624-0249	18										
20	10-88-1201	A-8624-0010	10-89-1201	A-8624-0050	10-89-2201	A-8624-0090		A-8624-0130	10-88-1202	A-8624-0170	10-89-1202	A-8624-0210	10-89-2202	A-8624-0250	20										
22	10-88-1221	A-8624-0011	10-89-1221	A-8624-0051	10-89-2221	A-8624-0091		A-8624-0131	10-88-1222	A-8624-0171	10-89-1222	A-8624-0211	10-89-2222	A-8624-0251	22										
24	10-88-1241	A-8624-0012	10-89-1241	A-8624-0052	10-89-2241	A-8624-0092		A-8624-0132	10-88-1242	A-8624-0172	10-89-1242	A-8624-0212	10-89-2242	A-8624-0252	24										
26	10-88-1261	A-8624-0013	10-89-1261	A-8624-0053	10-89-2261	A-8624-0093		A-8624-0133	10-88-1262	A-8624-0173	10-89-1262	A-8624-0213	10-89-2262	A-8624-0253	26										
28	10-88-1281	A-8624-0014	10-89-1281	A-8624-0054	10-89-2281	A-8624-0094		A-8624-0134	10-88-1282	A-8624-0174	10-89-1282	A-8624-0214	10-89-2282	A-8624-0254	28										
30	10-88-1301	A-8624-0015	10-89-1301	A-8624-0055	10-89-2301	A-8624-0095		A-8624-0135	10-88-1302	A-8624-0175	10-89-1302	A-8624-0215	10-89-2302	A-8624-0255	30										
32	10-88-1321	A-8624-0016	10-89-1321	A-8624-0056	10-89-2321	A-8624-0096		A-8624-0136	10-88-1322	A-8624-0176	10-89-1322	A-8624-0216	10-89-2322	A-8624-0256	32										
34	10-88-1341	A-8624-0017	10-89-1341	A-8624-0057	10-89-2341	A-8624-0097		A-8624-0137	10-88-1342	A-8624-0177	10-89-1342	A-8624-0217	10-89-2342	A-8624-0257	34										
36	10-88-1361	A-8624-0018	10-89-1361	A-8624-0058	10-89-2361	A-8624-0098		A-8624-0138	10-88-1362	A-8624-0178	10-89-1362	A-8624-0218	10-89-2362	A-8624-0258	36										
38	10-88-1381	A-8624-0019	10-89-1381	A-8624-0059	10-89-2381	A-8624-0099		A-8624-0139	10-88-1382	A-8624-0179	10-89-1382	A-8624-0219	10-89-2382	A-8624-0259	38										
40	10-88-1401	A-8624-0020	10-89-1401	A-8624-0060	10-89-2401	A-8624-0100		A-8624-0140	10-88-1402	A-8624-0180	10-89-1402	A-8624-0220	10-89-2402	A-8624-0260	40										
42	10-88-1421	A-8624-0021	10-89-1421	A-8624-0061	10-89-2421	A-8624-0101		A-8624-0141	10-88-1422	A-8624-0181	10-89-1422	A-8624-0221	10-89-2422	A-8624-0261	42										
44	10-88-1441	A-8624-0022	10-89-1441	A-8624-0062	10-89-2441	A-8624-0102		A-8624-0142	10-88-1442	A-8624-0182	10-89-1442	A-8624-0222	10-89-2442	A-8624-0262	44										
46	10-88-1461	A-8624-0023	10-89-1461	A-8624-0063	10-89-2461	A-8624-0103		A-8624-0143	10-88-1462	A-8624-0183	10-89-1462	A-8624-0223	10-89-2462	A-8624-0263	46										
48	10-88-1481	A-8624-0024	10-89-1481	A-8624-0064	10-89-2481	A-8624-0104		A-8624-0144	10-88-1482	A-8624-0184	10-89-1482	A-8624-0224	10-89-2482	A-8624-0264	48										
50	10-88-1501	A-8624-0025	10-89-1501	A-8624-0065	10-89-2501	A-8624-0105		A-8624-0145	10-88-1502	A-8624-0185	10-89-1502	A-8624-0225	10-89-2502	A-8624-0265	50										
52	10-88-1521	A-8624-0026	10-89-1521	A-8624-0066	10-89-2521	A-8624-0106		A-8624-0146	10-88-1522	A-8624-0186	10-89-1522	A-8624-0226	10-89-2522	A-8624-0266	52										
54	10-88-1541	A-8624-0027	10-89-1541	A-8624-0067	10-89-2541	A-8624-0107		A-8624-0147	10-88-1542	A-8624-0187	10-89-1542	A-8624-0227	10-89-2542	A-8624-0267	54										
56	10-88-1561	A-8624-0028	10-89-1561	A-8624-0068	10-89-2561	A-8624-0108		A-8624-0148	10-88-1562	A-8624-0188	10-89-1562	A-8624-0228	10-89-2562	A-8624-0268	56										
58	10-88-1581	A-8624-0029	10-89-1581	A-8624-0069	10-89-2581	A-8624-0109		A-8624-0149	10-88-1582	A-8624-0189	10-89-1582	A-8624-0229	10-89-2582	A-8624-0269	58										
60	10-88-1601	A-8624-0030	10-89-1601	A-8624-0070	10-89-2601	A-8624-0110		A-8624-0150	10-88-1602	A-8624-0190	10-89-1602	A-8624-0230	10-89-2602	A-8624-0270	60										
62	10-88-1621	A-8624-0031	10-89-1621	A-8624-0071	10-89-2621	A-8624-0111		A-8624-0151	10-88-1622	A-8624-0191	10-89-1622	A-8624-0231	10-89-2622	A-8624-0271	62										
64	10-88-1641	A-8624-0032	10-89-1641	A-8624-0072	10-89-2641	A-8624-0112		A-8624-0152	10-88-1642	A-8624-0192	10-89-1642	A-8624-0232	10-89-2642	A-8624-0272	64										
66	10-88-1661	A-8624-0033	10-89-1661	A-8624-0073	10-89-2661	A-8624-0113		A-8624-0153	10-88-1662	A-8624-0193	10-89-1662	A-8624-0233	10-89-2662	A-8624-0273	66										
68	10-88-1681	A-8624-0034	10-89-1681	A-8624-0074	10-89-2681	A-8624-0114		A-8624-0154	10-88-1682	A-8624-0194	10-89-1682	A-8624-0234	10-89-2682	A-8624-0274	68										
70	10-88-1701	A-8624-0035	10-89-1701	A-8624-0075	10-89-2701	A-8624-0115		A-8624-0155	10-88-1702	A-8624-0195	10-89-1702	A-8624-0235	10-89-2702	A-8624-0275	70										
72	10-88-1721	A-8624-0036	10-89-1721	A-8624-0076	10-89-2721	A-8624-0116		A-8624-0156	10-88-1722	A-8624-0196	10-89-1722	A-8624-0236	10-89-2722	A-8624-0276	72										
74	10-88-1741	A-8624-0037	10-89-1741	A-8624-0077	10-89-2741	A-8624-0117		A-8624-0157	10-88-1742	A-8624-0197	10-89-1742	A-8624-0237	10-89-2742	A-8624-0277	74										
76	10-88-1761	A-8624-0038	10-89-1761	A-8624-0078	10-89-2761	A-8624-0118		A-8624-0158	10-88-1762	A-8624-0198	10-89-1762	A-8624-0238	10-89-2762	A-8624-0278	76										
78	10-88-1781	A-8624-0039	10-89-1781	A-8624-0079	10-89-2781	A-8624-0119		A-8624-0159	10-88-1782	A-8624-0199	10-89-1782	A-8624-0239	10-89-2782	A-8624-0279	78										
80	10-88-1801	A-8624-0040	10-89-1801	A-8624-0080	10-89-2801	A-8624-0120		A-8624-0160	10-88-1802	A-8624-0200	10-89-1802	A-8624-0240	10-89-2802	A-8624-0280	80										
															L1	SEE SHEET 1	DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°		▽ = 0 ▼ = 0		REVISE ONLY ON CAD SYSTEM				
															H	SEE SHEET 1	INCH METRIC		TITLE		SALES ASSY-DUAL ROW WAFER W/BREAK-OFF OPTION 0.025 SQ. PINS/.100 GRID				
															F	SEE SHEET 1	9 PLACE ± ±		SHEET NO. 2		DATE 08/15/88				
															C	SEE SHEET 1	2 PLACE ± ±		PART NO. SEE CHART		DRWG. NO. SDA-8624-0001-				