

Wiha BitFlip Sets - Insulated & Standard

“Available Fall 2008”

NEW
From Wiha

Each insulated tool individually tested to 10,000 volts and certified to 1000 Volt ac or 1500 Volt dc

Insulation according to IEC/EN 60900, ASTM F-1505-01, DIN 7437, NFPA70E

BitFlip
Insulated

“8 In 1 Bit Sets”

Blade CVM tool steel, hardened

BitFlip standard SoftFinish® handle, multi-component, cushion grip, easy access & 8 bit storage

BitFlip Insulated

1000volt



BitFlip Standard


380 16 Slotted/Phillips/Square BitFlip Insulated
[SHOP](#)

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

↓ 	Slotted Sizes: 4.5, 6.5mm	
⊕	Phillips Sizes: 0, 1, 2, 3	lbs.
□	Square Sizes: 1, 2	.45

BitFlip Insulated

1000volt


380 26 Slotted/Phillips/Square BitFlip Standard
[SHOP](#)

with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

↓ 	Slotted Sizes: 4.5, 6.5mm	
⊕	Phillips Sizes: 0, 1, 2, 3	lbs.
□	Square Sizes: 1, 2	.44

BitFlip Standard


380 17 Slotted/Phillips/TORX® BitFlip Insulated
[SHOP](#)

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

↓ 	Slotted Sizes: 4.5, 6.5mm	
⊕	Phillips Sizes: 1, 2	lbs.
⊗	TORX® Sizes: T10, T15, T20, T25	.45

BitFlip Insulated

1000volt


380 27 Slotted/Phillips/TORX® BitFlip Standard
[SHOP](#)

with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

↓ 	Slotted Sizes: 4.5, 6.5mm	
⊕	Phillips Sizes: 1, 2	lbs.
⊗	TORX® Sizes: T10, T15, T20, T25	.44

BitFlip Standard


380 18 Slotted/Phillips BitFlip Insulated
[SHOP](#)

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

↓ 	Slotted Sizes: 4.5, 5.5, 6.5, 8.0mm	lbs.
⊕	Phillips Sizes: 0, 1, 2, 3	.45

BitFlip Insulated

1000volt


380 28 TORX® BitFlip Standard
[SHOP](#)

with Wiha cushion grip handle and insulated shaft.

Set includes the following 1/4" bits:

⊗	TORX® Sizes: T8, T10, T15, T20, T25, T27, T30, T40	lbs.
		.44

[PREVIOUS](#)
[NEXT](#)