

F

E

D

C

B

A

F

E







D

C

B

A

10987654321




注記 NOTES

- 使用材料 MATERIAL
ハウジング : 液晶ポリマー(LCP)、ナチュラル(白色系)、ガラス充填、UL94V-0
奇数端子 : 磷青銅、ニッケル下地、金メッキ
偶数端子 : 磷青銅、ニッケル下地、金メッキ
HOUSING : LIQUID CRYSTAL POLYMER(LCP), NATURAL(WHITE)
GLASS FILLED, UL94V-0
ODD TERMINAL : PHOSPHOR BRONZE, Gold OVER Nickel PLATING
EVEN TERMINAL : PHOSPHOR BRONZE, Gold OVER Nickel PLATING
- めっき仕様 PLATING
ターミナル TERMINAL
接点部 : 金メッキ 0.1μm以上
テール部 : 金メッキ
下地 : ニッケルメッキ 1.0μm以上
CONTACT AREA : GOLD PLATING 0.1μm MINIMUM
TAIL AREA : GOLD PLATING
UNDER PLATING : NICKEL PLATING 1.0μm MINIMUM
- 端子のコプラナリティーは 0.1 以下とする。
COPLANARITY OF SOLDER TAILS: 0.1MAX.
- ELV 及び RoHS 適合品
ELV AND RoHS COMPLIANT
- 一般公差 : ±0.3
GENERAL TOLERANCE: ±0.3

6.0	4.8	5.4	6.6	504281-1900	19
5.4	4.2	4.8	6.0	504281-1700	17
4.2	3.0	3.6	4.8	504281-1300	13
3.6	2.4	3.0	4.2	504281-1100	11
D	C	B	A	EMBOSSED PACKAGE オーダー番号 ORDER NO.	極数 CIRCUIT

RELEASED EC NO: J2014-0037 DRWN:SKUR05E CHKD:H I J I M A APPR:YNOGAWA REV 0	DESCRIPTION REV 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 15:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		10 UNDER		+0.2		TITLE 0.3 FPC CONN. NON-ZIF TYPE HGT=1.0MM molex			
		10 OVER 30 UNDER		±0.25					
		30 OVER		±0.3					
		ANGULAR ±1 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-504281-001		1 OF 2	
		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					



98765432




SEE SHEET 1 OF 2 EC NO: J2014-0037 DRWN:SKUROSE CHKD:H IJIMA APPR:YNOGAWA	2014/04/28 2014/04/28 2014/05/07	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 15:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
			10 UNDER		+0.2	DRAWN BY NNISHI	DATE 2012/07/17	TITLE 0.3 FPC CONN. NON-ZIF TYPE HGT=1.0MM		
			10 OVER 30 UNDER		±0.25	CHECKED BY H IJIMA	DATE 2012/07/17			
			30 OVER		±0.3	APPROVED BY YNOGAWA	DATE 2014/05/07	molex		
			ANGULAR ±1 °		MATERIAL NO.		DOCUMENT NO.			SHEET NO.
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 1		SD-504281-001			2 OF 2
0		A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

注記 NOTES

- 製品詳細寸法については図面SD-504281-001を参照下さい。
CONNECTOR DETAILED DIMENSIONS, REFER TO SD-504281-001.
- 梱包数量: 5000個/リール
NUMBER OF CONNECTORS : 5000PCS / REEL
- リードテープ長さ
LEAD TAPE LENGTH



- キャリアテープ(CARRIER TAPE) : ポリスチレン(POLYSTYRENE)
トップテープ(TOP TAPE) : PET, PE, PEF
リール(REEL) : ポリスチレン(POLYSTYRENE) <リサイクル材を含む>
POLYSTYRENE(PS) <RECYCLE MATERIAL CONTAINED>
- トップテープの剥離強度については、IEC60286-3に準拠
TOP TAPE PEEL FORCE IS DEFINED BY IEC60286-3



RELEASED EC NO: J2014-0037 DRWN:SKUROSE CHKD:HIJIMA APPR:YNOGAWA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY SKUROSE	DATE 2013/05/20	TITLE 0.3 FPC CONN NON-ZIF TYPE HGT=1.0MM				
		10 OVER 30 UNDER	± 0.25	CHECKED BY HIJIMA	DATE 2013/05/20					
		30 OVER	± 0.3	APPROVED BY YNOGAWA	DATE 2014/05/07	molex				
		ANGULAR ±1 °		MATERIAL NO. SEE CHART						
	0	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

10

9

8

7

6

5

4

3

2

1

F

E

D

C

B

A

F



E

D

C

B

A



7.5	17.4	6.6	504281-1900	19
		6.0	504281-1700	17
		4.8	504281-1300	13
		4.2	504281-1100	11
C	B	A	EMBOSSED TAPE PACKAGE オーダー番号 ORDER NO.	種 数 Ckt.

SEE SHEET 1 OF 2 EC NO.: J2014-0037 DRWN:SKUROSE 2014/04/28 CHKD:H I I J I M A 2014/04/28 APPR:YNOGAWA 2014/05/07	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
				MM ONLY		5:1	METRIC			
		10 UNDER	± 0.2	DRAWN BY	DATE	TITLE 0.3 FPC CONN NON-ZIF TYPE HGT=1.0MM molex				
		10 OVER 30 UNDER	± 0.25	CHECKED BY	DATE					
		30 OVER	± 0.3	APPROVED BY	DATE					
	ANGULAR ±1 °		MATERIAL NO.		DOCUMENT NO.					SHEET NO.
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 1		SD-504281-002					2 OF 2
0	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

9

8

7

6

5

4

3

2