

SMD
 VERSION 9

MENTOR
 INNOVATIONS FOR THE FUTURE

Tastkappe

Push button cap

Allgemeine Hinweise und Technische Daten

[Allgemeine Hinweise: klicken Sie hier](#)

Material:

Gehäuse: PBT UL94 weiß

Streuscheibe: PC UL94 diffus

Betriebstemperatur: -40°C ... +85°C

Klima: GPF DIN 40040

Diese Tastkappen können mit verschiedenen Kurzhubtastern kombiniert werden (siehe Layoutvorschlag). Die Tastkappen werden als Standard in zwei verschiedenen Größen und Höhen angeboten. Sondergrößen sind auf Anfrage möglich.



General Remarks and Technical Data

[General Remarks: click here](#)

Material:


Housing: PBT UL94 white

Diffuser disk: PC UL94 diffuse


Operating temperature: -40°C ... +85°C

Climate: GPF DIN 40040

These push button caps can be combined with various push button switches (see layout suggestion). The push button caps are available standardly in two different sizes and heights. Special sizes are available on request.




2271.1003





Taster/push button 1: MENTOR [1254.1007]

Taster/push button 2: OMRON B3FS-1052

Taster/push button 3: RAFI RACON 8



Layoutvorschlag · Layout Suggestion



Einbaubeispiel · Mounting Example

A x A	B	C	D	E	F	G	H	Taster push button	Art.-Nr.
19 x 19	8,9	22,86	9,2	21	-	9,4	9,7	1 + 2	2271.1003
19 x 19	8,9	22,86	9,2	21	11,4	-	9,7	3	2271.1004
19 x 19	11,7	22,86	12	21	-	9,4	12,5	1 + 2	2271.1006
19 x 19	11,7	22,86	12	21	11,4	-	12,5	3	2271.1007
15 x 15	8,9	19,05	9,2	16	-	8,4	9,7	1 + 2	2271.1009
15 x 15	8,9	19,05	9,2	16	9,4	-	9,7	3	2271.1010
15 x 15	11,7	19,05	12	16	-	8,4	12,5	1 + 2	2271.1011
15 x 15	11,7	19,05	12	16	9,4	-	12,5	3	2271.1012

Magerdruck keine Lagerware · Bestellmenge und Preise auf Anfrage
Light printing non-stock item · Quantity and prices on request



[Seite ausdrucken](#)



[Print page](#)