Quad RS-485/RS-422 Line Drivers

- RS-485 or RS-422 Applications
- Quad Differential Line Drivers
- Tri-state Output Control
- 40ns Typical Driver Propagation Delays
- 5ns Skew
- -7V to +12V Common Mode Output Range
- 100µA Supply Current
- Single +5V Supply Operation
- Pin Compatible with SN75172, SN75174, LTC486 and LTC487

DESCRIPTION

The **SP486** and **SP487** are low-power quad differential line drivers meeting RS-485 and RS-422 standards. The SP486 features a common driver enable control; the SP487 provides independent driver enable controls for each pair of drivers. Both feature tri-state outputs and a wide common-mode output range. SP486 and SP487 are available in a 16-pin SOIC package.



ABSOLUTE MAXIMUM RATINGS

These are stress ratings only and functional operation of the device at these ratings or any other above those indicated in the operation sections of the specifications below is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability.

V_{CC}.....+7V
Input Voltages
Logic.....-0.5V to (Vcc + 0.5V)
Drivers.....-0.5V to (Vcc + 0.5V)
Driver Output Voltage.....+/-14V
Input Currents
Logic.....+/-25mA
Driver.....+/-25mA
Storage Temperature.....-65˚C to +150˚C
Power Dissipation
Plastic DIP.....375mW
(derate 7mW/ºC above +70ºC)
Small Outline.....375mW
(derate 7mW/ºC above +70ºC)

ELECTRICAL CHARACTERISTICS

V_{CC} = +5.0V +/-5%; typicals at 25°C; $T_{MIN} \le T_{AMB} \le T_{MAX}$ unless otherwise noted.

PARAMETERS	MIN.	TYP.	MAX.	UNITS	CONDITIONS
DC CHARACTERISTICS					
DIGITAL INPUTS					DI, EN, $\overline{EN}$, EN_1/EN_2, EN_3/EN_4
Voltage V_{IL}			0.8	Volts	
Voltage V_{IH}	2.0			Volts	
Input Current			+/-2	µA	V_{IN} = 0V to V_{CC}
DRIVER OUTPUTS					
Differential Voltage			5	Volts	I_O = 0; unloaded
Differential Voltage	2			Volts	R_L = 50Ω (RS-422); Figure 1
Differential Voltage	1.5	2	5	Volts	R_L = 27Ω (RS-485); Figure 1
Change in Output Magnitude for Complementary Output state			0.2	Volts	R_L = 27Ω or 50Ω; Figure 1
Common Mode Output Voltage		2.3	3	Volts	R_L = 27Ω or 50Ω; Figure 1
Change in Common Mode Output Magnitude for Complementary Output state			0.2	Volts	R_L = 27Ω or 50Ω; Figure 1
Driver Short Circuit Current V_{OH}			+/-250	mA	$-7V \le V_O \le +10V$
Driver Short Circuit Current V_{OL}			+/-250	mA	$-7V \le V_O \le +10V$
High Impedance Output Current		+/-2	+/-200	µA	V_O = -7V to +10V
POWER REQUIREMENTS					
Supply Voltage	4.75		5.25	Volts	
Supply Current		0.5	10	µA	No load, output enabled
Supply Current		0.1	10	µA	No load, output disabled

ELECTRICAL CHARACTERISTICS

V_{CC} = +5.0V +/-5%; typicals at 25°C; $T_{MIN} \le T_{AMB} \le T_{MAX}$ unless otherwise noted.

PARAMETERS	MIN.	TYP.	MAX.	UNITS	CONDITIONS
ENVIRONMENTAL AND MECHANICAL					
Operating Temperature, _C	0		+70	°C	
Operating Temperature, _E	-40		+85	°C	
Storage Temperature	-65		+150	°C	
Package -_T	16-pin SOIC				
AC CHARACTERISTICS					
Maximum Data Rate	10			Mbps	
Propagation Delay, t_{PLH}	20	40	60	ns	R_{DIFF} = 54 ohms, C_{L1}= C_{L2} = 100pF; Figure 2
Propagation Delay, t_{PHL}	20	40	60	ns	R_{DIFF} = 54 ohms, C_{L1}= C_{L2} = 100pF; Figure 2
Differential Driver Skew		5	15	ns	R_{DIFF} = 54 ohms, C_{L1}= C_{L2} = 100pF; Figure 2
Driver Rise Time (t_R)		20		ns	10% to 90%
Driver Fall Time (t_F)		20		ns	90% to 10%
Driver Enable to output High		60	110	ns	C_L = 100pF, Figures 3 and 5 (S2 closed)
Driver Enable to output Low		60	115	ns	C_L = 100pF, Figures 3 and 5 (S1 closed)
Driver Disable from output High		60	130	ns	C_L = 15pF, Figures 3 and 5 (S2 closed)
Driver Disable from output Low		60	130	ns	C_L = 15pF, Figures 3 and 5 (S1 closed)

SP486



Pin Function SP486

Pin 1 - DI_1 - Driver 1 Input - If driver 1 output is enabled, a logic 0 on DI_1 forces driver output DO_1A low and DO_1B high. A logic 1 on DI_1 with driver 1 output enabled forces driver DO_1A high and DO_1B low.

Pin 2 - DO_1A - Driver 1 output A.

Pin 3 - DO_1B - Driver 1 output B.

Pin 4 - EN - Driver Output Enable; Please refer to SP486 truth table (1).

Pin 5 - DO_2B - Driver 2 output B.

Pin 6 - DO_2A - Driver 2 output A.

Pin 7 - DI_2 - Driver 2 Input - If driver 2 output is enabled, a logic 0 on DI_2 forces driver output DO_2A low and DO_2B high. A logic 1 on DI_2 with driver 2 output enabled forces driver DO_2A high and DO_2B low.

Pin 8 - GND - Ground.

Pin 9 - DI_3 - Driver 3 Input - If driver 3 output is enabled, a logic 0 on DI_1 forces driver output DO_3A low and DO_3B high. A logic 1 on DI_3 with driver 3 output enabled forces driver DO_3A high and DO_3B low.

Pin 10 - DO_3A - Driver 3 output A.

Pin 11 - DO_3B - Driver 3 output B.

Pin 12 - $\overline{EN}$ - Driver Output Disable; Please refer to SP486 truth table (1).

Pin 13 - DO_4B - Driver 4 output B.

Pin 14 - DO_4A - Driver 4 output A.

Pin 15 - DI_4 - Driver 4 Input - If driver 4 output is enabled, a logic 0 on DI_4 forces driver output DO_4A low and DO_4B high. A logic 1 on DI_4 with driver 4 output enabled forces driver DO_4A high and DO_4B low.

Pin 16 - Supply Voltage - $+4.75V \leq Vcc \leq +5.25V$.

SP487



Pin Function SP487

Pin 1 - DI_1 - Driver 1 Input - If driver 1 output is enabled, a logic 0 on DI_1 forces driver output DO_1A low and DO_1B high. A logic 1 on DI_1 with driver 1 output enabled forces driver DO_1A high and DO_1B low.

Pin 2 - DO_1A - Driver 1 output A.

Pin 3 - DO_1B - Driver 1 output B.

Pin 4 - EN_1/EN_2 - Driver 1 and 2 Output Enable; Please refer to SP487 truth table (2).

Pin 5 - DO_2B - Driver 2 output B.

Pin 6 - DO_2A - Driver 2 output A.

Pin 7 - DI_2 - Driver 2 Input - If driver 2 output is enabled, a logic 0 on DI_2 forces driver output DO_2A low and DO_2B high. A logic 1 on DI_2 with driver 2 output enabled forces driver DO_2A high and DO_2B low.

Pin 8 - GND - Ground.

Pin 9 - DI_3 - Driver 3 Input - If driver 3 output is enabled, a logic 0 on DI_1 forces driver output DO_3A low and DO_3B high. A logic 1 on DI_3 with driver 3 output enabled forces driver DO_3A high and DO_3B low.

Pin 10 - DO_3A - Driver 3 output A.

Pin 11 - DO_3B - Driver 3 output B.

Pin 12 - EN_3/EN_4 - Driver 3 and 4 Output Enable; Please refer to SP487 truth table (2)..

Pin 13 - DO_4B - Driver 4 output B.

Pin 14 - DO_4A - Driver 4 output A.

Pin 15 - DI_4 - Driver 4 Input - If driver 4 output is enabled, a logic 0 on DI_4 forces driver output DO_4A low and DO_4B high. A logic 1 on DI_4 with driver 4 output enabled forces driver DO_4A high and DO_4B low.

Pin 16 - Supply Voltage - +4.75V ≤ Vcc ≤ +5.25V.



Figure 1. Driver DC Test Load



Figure 2. Driver Timing Test



Figure 3. Driver Timing Test Load



Figure 4. Driver Propagation Delays



Figure 5. Driver Enable/Disable Timing

The **SP486** and **SP487** are low power quad differential line drivers meeting RS-485 and RS-422 standards. The SP486 features active high and active low common driver enable controls; the SP487 provides independent, active high driver enable controls for each pair of drivers. The driver outputs are short-circuit limited to 200mA. Data rates up to 10Mbps are supported. The SP486 and SP487 are available in a 16-pin SOIC package.

INPUT	ENABLES		OUTPUTS	
DI	EN	$\overline{EN}$	OUTA	OUTB
H	H	X	H	L
L	H	X	L	H
H	X	L	H	L
L	X	L	L	H
X	L	H	Hi-Z	Hi-Z

Table 1. SP486 Truth Table

INPUT	ENABLES	OUTPUTS	
DI	EN_1/EN_2 or EN_3/EN_4	OUTA	OUTB
H	H	H	L
L	H	L	H
X	L	Hi-Z	Hi-Z

Table 2. SP487 Truth Table

REVISION HISTORY			
REV.	DISCRIPTION	DATE	APP'D
A	DRAWING ORIGINATION	11/05/05	JL
B	DRAWING FORMAT MODIFICATION	09/13/06	JL
C	CHANGE DRAWING LOGO AND COMPANY NAME	11/21/07	JL



Top View

16 Pin SOICW JEDEC MS-013 Variation AA						
SYMBOLS	DIMENSIONS IN MM (Control Unit)			DIMENSIONS IN INCH (Reference Unit)		
	MIN	NOM	MAX	MIN	NOM	MAX
A	2.35	—	2.65	0.093	—	0.104
A1	0.10	—	0.30	0.004	—	0.012
A2	2.05	—	2.55	0.081	—	0.100
b	0.31	—	0.51	0.012	—	0.020
c	0.20	—	0.33	0.008	—	0.013
E	10.30 BSC			0.406 BSC		
E1	7.50 BSC			0.295 BSC		
e	1.27 BSC			0.050 BSC		
h	0.25	—	0.75	0.010	—	0.030
L	0.40	—	1.27	0.016	—	0.050
L1	1.40 REF			0.055 REF		
L2	0.25 BSC			0.010 BSC		
R	0.07	—	—	0.003	—	—
R1	0.07	—	—	0.003	—	—
θ	0°	—	8°	0°	—	8°
θ1	5°	—	15°	5°	—	15°
θ2	0°	—	—	0°	—	—
D	10.30 BSC			0.405 BSC		
N	16			16		



Side View



Front View

EXAR Powering Connectivity	EXAR CORPORATION		
	16 PIN SOICW PACKAGE OUTLINE		
Packaging Approval:	Drawing No:	16-PIN SOICW	
By: JL / Date: 11/21/07	Revision: C	Sheet: 1 OF 1	

ORDERING INFORMATION

Model	Temperature Range	Package Types
SP486CT-L	0°C to +70°C	16-pin SOIC
SP486CT-L/TR	0°C to +70°C	16-pin SOIC
SP486ET-L	-40°C to +85°C	16-pin SOIC
SP486ET-L/TR	-40°C to +85°C	16-pin SOIC
SP487CT-L	0°C to +70°C	16-pin SOIC
SP487CT-L/TR	0°C to +70°C	16-pin SOIC
SP487ET-L	-40°C to +85°C	16-pin SOIC
SP487ET-L/TR	-40°C to +85°C	16-pin SOIC

Note: /TR = Tape and Reel

REVISION HISTORY

DATE	REVISION	DESCRIPTION
June 2005	--	Legacy Sipex Datasheet
June 2011	1.0.0	Update ordering information per PDN 110510-01 and convert to Exar Format

Notice

EXAR Corporation reserves the right to make changes to any products contained in this publication in order to improve design, performance or reliability. EXAR Corporation assumes no representation that the circuits are free of patent infringement. Charts and schedules contained herein are only for illustration purposes and may vary depending upon a user's specific application. While the information in this publication has been carefully checked; no responsibility, however, is assumed for inaccuracies.

EXAR Corporation does not recommend the use of any of its products in life support applications where the failure or malfunction of the product can reasonably be expected to cause failure of the life support system or to significantly affect its safety or effectiveness. Products are not authorized for use in such applications unless EXAR Corporation receives, in writting, assurances to its satisfaction that: (a) the risk of injury or damage has been minimized ; (b) the user assumes all such risks; (c) potential liability of EXAR Corporation is adequately protected under the circumstances.

Copyright 2011 EXAR Corporation

Datasheet June 2011

For technical support please email Exar's Serial Technical Support group at: serialtechsupport@exar.com

Reproduction, in part or whole, without the prior written consent of EXAR Corporation is prohibited.