

REVISIONS									
LOC	DIST	P	F	ZONE	LTR	DESCRIPTION			DATE
BD	62				K	REV PER 0520-0287-02			01MAY02
									TS/RF

D

C

B


A

D





C

B

A



- 1 PADDLEBOARD HOUSING: LCP, BLACK, UL 94V-0 RATED.
PADDLEBOARD COVER: POLYESTER, BLACK OR GREY, UL 94V-0 RATED.
COVER: ABS, BLACK, UL 94V-0 RATED.
CONTACTS: COPPER ALLOY.
SUBSTRATE: PLASTIC LAMINATE.
- 2 2.54µm[.000100] MIN TIN-LEAD OVER 1.27µm[.000050] MIN NICKEL.
- 3 C1 = 4.7µFD TANTALUM; C3 = 22µFD TANTALUM; C2 COMPRISED OF TWO .1µFD CERAMIC CAPACITORS.
- 4 VOLTAGE REGULATOR TO MEET ALL SCSI SINGLE-ENDED ACTIVE REQUIREMENTS.



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.13 [.005] 3 PLC DEC ± . ANGLES ± -				DR 08-08-94 D.BROCKWAY		869888-1		
MATERIAL				CHK 08-09-94 R.STONE		PART NO		
FINISH				APPD 09-10-94 J.VANDYKE		NAME		
				APPD 09-10-94 J.VANDYKE		AMP Incorporated Harrisburg, PA 17105-3608		
				PRODUCT SPEC		.025¢ IDC ASSEMBLY, ACTIVE TERMINATOR		
				APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO
				WEIGHT		D	00779	C-869888
						SCALE	4:1	SHEET 1 OF 1