

ISO VIEW

TYPE	PART NO.	INSULATION DIA. (mm)	COLOR
MCP 6.3 (A2)	963243-1	1.4 - 2.1	BLUE
	963244-1	2.2 - 3.0	WHITE
	963245-1	3.4 - 3.7	YELLOW
	2188967-3	4.6 - 5.0	GRAY
	100132-1	CAVITY PLUG	BLACK

TYPE	PART NO.	WIRE RANGE (mm ²)	INSULATION DIA. (mm)	FINISH
MCP 6.3 (A2)	1241412-1	0.5 - 1.0	1.4 - 2.1	CuNiSi, Tin
	1241412-3			CuNiSi, Silver
	1241414-1	1.0 - 2.5	2.2 - 3.0	CuNiSi, Tin
	1241414-3			CuNiSi, Silver
	1241416-1	2.5 - 4.0	3.4 - 3.7	CuNiSi, Tin
	1241416-3			CuNiSi, Silver
	1241418-4	5.0	4.6 - 5.0	CuNiSi, Tin

1. GENERAL TOLERANCE : ± 0.3 , $\pm 3.0^\circ$
2. THE MATING CONNECTOR : 1897213-2
3. APPLICABLE RECEPTACLE CONTACT P/N: TABLE 1
4. APPLICABLE WIRE SEAL P/N: TABLE 2

ASS'Y P/N	DESCRIPTION
1897214-1	MCP 2P PLUG ASS'Y

3	SEAL	SILICONE	ORANGE	1
2	SUB PLUG HSG	PA66-GF15	BLACK	1
1	MAIN PLUG HSG	PA66-GF15	BLACK	1
NO	DESCRIPTION	MATERIAL	COLOR	Q'TY




MCP 6.3 2P PLUG ASSY

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
A3	00779	C=1897214	-		
SCALE			SHEET	OF	REV
2:1			1	1	A2

DWN	JM JEON
CHK	JW JUNG
APVD	HG CHO
PRODUCT SPEC	

	NAME
--	------

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
		0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$	
MATERIAL		FINISH	
SEE TABLE			