

100731/730/723/720

JOBBER DRILLS


Straight Shank

Standard Helix

BS 328 DIN 338 ISO 235/1

	Range	Finish
01 000 HSS	1/16"-3/4" 1.55mm-25.00mm	P1 Blue P1 Blue
01 030 HSS	1/64"-3/4" 0.30mm-25.00mm	Bright Bright
01 005 HSS	3/64"-3/4" 1.00mm-20.00mm	TiN TiN

Point Angle 118° General Purpose



Dia	Flute Length	Overall Length	01000	01005
in	mm	mm	01030	Availability
d	L ₂	L ₁		

Dia	Flute Length	Overall Length	01000	01005
in	mm	mm	01030	Availability
d	L ₂	L ₁		

Dia	Flute Length	Overall Length	01000	01005
in	mm	mm	01030	Availability
d	L ₂	L ₁		

*0.30	4	19	•	-		1.80	22	46	•	•		3.95	43	75	•	•
*0.32	4	19	•	-		1.85	22	46	•	•		5/32	43	75	•	•
*0.35	4	19	•	-		1.90	22	46	•	•		4.00	43	75	•	•
*0.38	4	19	•	-		1.95	24	49	•	•		4.05	43	75	•	•
*1/64	5	20	•	-		2.00	24	49	•	•		4.10	43	75	•	•
*0.40	5	20	•	-		2.05	24	49	•	•		4.15	43	75	•	•
*0.42	5	20	•	-		2.10	24	49	•	•		4.20	43	75	•	•
*0.45	5	20	•	-		2.15	27	53	•	•		4.25	43	75	•	•
*0.48	5	20	•	-		2.20	27	53	•	•		4.30	47	80	•	•
*0.50	6	22	•	-		2.25	27	53	•	•		4.35	47	80	•	•
*0.52	6	22	•	-		2.30	27	53	•	•		11/64	47	80	•	•
*0.55	7	24	•	-		2.35	27	53	•	•		4.40	47	80	•	•
*0.58	7	24	•	-		2.40	30	57	•	•		4.45	47	80	•	•
*0.60	7	24	•	-		2.45	30	57	•	•		4.50	47	80	•	•
*0.62	8	26	•	-		2.50	30	57	•	•		4.55	47	80	•	•
*0.65	8	26	•	-		2.55	30	57	•	•		4.60	47	80	•	•
*0.68	9	28	•	-		2.60	30	57	•	•		4.65	47	80	•	•
*0.70	9	28	•	-		2.65	30	57	•	•		4.70	47	80	•	•
*0.72	9	28	•	-		2.70	33	61	•	•		4.75	47	80	•	•
*0.75	9	28	•	-		2.75	33	61	•	•		3/16	52	86	•	•
*0.78	10	30	•	-		2.80	33	61	•	•		4.80	52	86	•	•
*1/32	10	30	•	-		2.85	33	61	•	•		4.85	52	86	•	•
*0.80	10	30	•	-		2.90	33	61	•	•		4.90	52	86	•	•
*0.82	10	30	•	-		2.95	33	61	•	•		4.95	52	86	•	•
*0.85	10	30	•	-		3.00	33	61	•	•		5.00	52	86	•	•
*0.88	11	32	•	-		3.05	36	65	•	•		5.10	52	86	•	•
*0.90	11	32	•	-		3.10	36	65	•	•		5.15	52	86	•	•
*0.92	11	32	•	-		3.15	36	65	•	•		13/64	52	86	•	•
*0.95	11	32	•	-		3.20	36	65	•	•		5.20	52	86	•	•
*0.98	12	34	•	-		3.25	36	65	•	•		5.25	52	86	•	•
*1.00	12	34	•	•		3.30	36	65	•	•		5.30	52	86	•	•
*1.05	12	34	•	•		3.35	36	65	•	•		5.35	57	93	•	•
*1.10	14	36	•	•		3.40	39	70	•	•		5.40	57	93	•	•
*1.15	14	36	•	•		3.45	39	70	•	•		5.45	57	93	•	•
*3/64	16	38	•	•		3.50	39	70	•	•		5.50	57	93	•	•
*1.20	16	38	•	•		3.55	39	70	•	•		7/32	57	93	•	•
*1.25	16	38	•	•		3.60	39	70	•	•		5.60	57	93	•	•
*1.30	16	38	•	•		3.65	39	70	•	•		5.65	57	93	•	•
*1.35	18	40	•	•		3.70	39	70	•	•		5.70	57	93	•	•
*1.40	18	40	•	•		3.75	39	70	•	•		5.75	57	93	•	•
*1.45	18	40	•	•		3.80	43	75	•	•		5.80	57	93	•	•
*1.50	18	40	•	•		3.85	43	75	•	•		5.85	57	93	•	•
*1.55	20	43	•	•		3.90	43	75	•	•		5.90	57	93	•	•
*1/16	20	43	•	•								15/64	57	93	•	•
1.60	20	43	•	•								6.00	57	93	•	•
1.65	20	43	•	•								6.05	63	101	•	•
1.70	20	43	•	•								6.10	63	101	•	•
1.75	22	46	•	•								6.15	63	101	•	•

* Available Bright Finish Only

Standard Helix

Range

Finish

1/16"-3/4"

1.55mm-25.00mm

P1 Blue

P1 Blue

1/64"-3/4"

0.30mm-25.00mm

Bright

Bright
Bright


3/64"-3/4"

1.00mm-20.00mm

TiN

TiN

Point Angle 118° General Purpose

13

Continued on page 14


J O B B E R D R I L L S

Straight Shank

Standard Helix

BS 328 DIN 338 ISO 235/1

	Range	Finish
01 000 HSS	1/16"-3/4" 1.55mm-25.00mm	P1 Blue P1 Blue
01 030 HSS	1/64"-3/4" 0.30mm-25.00mm	Bright Bright
01 005 HSS	3/64"-3/4" 1.00mm-20.00mm	TiN TiN



Point Angle 118° General Purpose

Dia in d	Flute Length mm l ₂	Overall Length mm l ₁	01000 01030 Availability	01005
----------------	---	---	--------------------------------	-------

	13.20	101	151	•	•
	13.25	108	160	•	•
	13.30	108	160	•	•
	13.40	108	160	•	•
17/32		108	160	•	•
	13.50	108	160	•	•
	13.60	108	160	•	•
	13.70	108	160	•	•
	13.75	108	160	•	•
	13.80	108	160	•	•
35/64		108	160	•	•
	13.90	108	160	•	•
	14.00	108	160	•	•
	14.25	114	169	•	•
9/16		114	169	•	•
	14.50	114	169	•	•
37/64		114	169	•	•
	14.75	114	169	•	•
	15.00	114	169	•	•
19/32		120	178	•	•
	15.25	120	178	•	•
39/64		120	178	•	•
	15.50	120	178	•	•
	15.75	120	178	•	•
5/8		120	178	•	•
	16.00	120	178	•	•
41/64		125	184	•	•
	16.50	125	184	•	•
21/32		125	184	•	•
	17.00	125	184	•	•
43/64		130	191	•	•
11/16		130	191	•	•
	17.50	130	191	•	•
	18.00	130	191	•	•
23/32		135	198	•	•
	18.50	135	198	•	•
	19.00	135	198	•	•
3/4		140	205	•	•
	19.50	140	205	•	•
25/32		140	205	•	•
	20.00	140	205	•	•
	21.00	145	213	•	-
	22.00	150	221	•	-
	23.00	155	229	•	-
	24.00	160	236	•	-
	25.00	160	236		