




$\phi.030$
 $\pm.002$
[0.76]


NOTES:

1. SUGGESTED MOUNTING HOLE = $\phi.130$



LEAD FINISH: GOLD PL.	
CASING FINISH: GOLD PL.	
CAPACITANCE	500pF MIN.
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	125°C -- VAC MAX. 125°C 200 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	--
10	--
100	18
1 GHz	37
10 GHz	38

SCHEMATIC



MARKING:

PART: BROWN COLOR DOT
BAG:

SCI-9980-501
DATE CODE
LOT NO.
QTY/BAG (200 MAX.)

00	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED
CN 53067-ENG	CHANGE NOTICE	Fractions $\pm 1/64$
		Dec. .xx $\pm$
		Dec. .xxx $\pm.005$
		Angles $\pm 0^{\circ} 30'$
		CODE IDENT. NO. DLSP2



FAIRVIEW
PENNSYLVANIA

Dwn. KAUFFMAN
Date 2-18-10
Engr. B. DEVINE
Scale NONE

Description
FEEDTHRU FILTER
SCI-9980-501

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[SCI-9980-501](#)