



Revision Date: 2008-12-01
Reason for Revision: REACH Compliance and General Update

SECTION 1: IDENTIFICATION OF THE PRODUCT AND COMPANY

Product Name: HI 7010 Buffer Solution pH 10.01

Application: pH Buffer Solution. ± 0.01 @ 25°C/77°F

Additional Product Codes: HI 7010/1G HI 7010/1L HI 7010L
HI 7010L/C HI 7010M HI 7010/1LB
HI 7010C HI 7010LB HI 7010M-0
HI 7010W HI 7010QC

Company Information (USA):

Hanna Instruments, Inc.
584 Park East Dr, Woonsocket, Rhode Island, USA 02895

Technical Service Contact Information:

1-800-426-6287 (8:30AM - 5:00PM ET)
+1-401-766-4260 (8:30AM - 5:00PM ET)

USA Emergency Contact Information:

1-800-424-9300 (Chemtrec 24Hr. Emergency)

International Emergency Contact Information:

+1-703-527-3887 (Chemtrec 24Hr. Emergency)

E-mail Address:

tech@hannainst.com

SECTION 2: HAZARD IDENTIFICATION

Non-hazardous product as specified in Directives 67/548/EEC and 1999/45/EC.

SECTION 3: COMPOSITION AND COMPONENT INFORMATION

Component: Aqueous Buffer Solution

EC-No.:

CAS-No.:

Hazard:

Phrases:

Content:

SECTION 4: FIRST AID MEASURES

After Inhalation: Remove to fresh air. Call a physician if breathing becomes difficult.

After Skin Contact: Wash effected area with water and soap.

After Eye Contact: Rinse out with plenty of water for at least 15 minutes. If pain persists, summon medical advice.

After Swallowing: Wash out mouth with plenty of water, provided person is conscious. Obtain medical attention if feeling unwell.

General Information: Not available

SECTION 5: FIRE-FIGHTING MEASURES

Suitable Extinguishing Media:

Water Spray, Foam, Dry Powder, Carbon Dioxide

Special Risks:

Non-combustible. Development of hazardous combustion gases or vapors possible in the event of fire.

Special Protective Equipment:

Do not stay in dangerous zone without suitable chemical protection clothing and self-contained breathing apparatus.

Additional Information:

Contain escaping vapors with water.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal Precautions:

None

Environmental Precautions:

None

Additional Notes:

None

SECTION 7: HANDLING AND STORAGE

Handling:

No restrictions

Storage:

Keep container closed and protected from direct sunlight. Store at room temperature (+15°C to +25°C).

SECTION 8: EXPOSURE CONTROL/PERSONAL PROTECTION

Ingredients:

Engineering:

Maintain general industrial hygiene practice.

Personal Protective Equipment:

As appropriate to quantity handled.

Respiratory Protection:

Required when vapors/aerosols are generated.

Protective Gloves:

Rubber or plastic

Eye Protection:

Goggles or face mask

Industrial Hygiene:

Change contaminated clothing. Wash hands after working with substance.

SECTION 9: PHYSICAL/CHEMICAL PROPERTIES

Appearance: Colorless or violet liquid

Odor: Odorless

Density at 20° C: 1.0 g/cm³ at 25°C

Melting Point: NA

Boiling Point: > 100 °C

Solubility: Soluble

pH at 20° C: 10.01 at 25°C

Explosion Limit: NA

Flash Point: NA

Thermal Decomp.: NA

SECTION 10: STABILITY AND REACTIVITY

Conditions to be Avoided:

Heating

Hazardous Polymerization:

Will not occur.

Further Information:

Not available

Hazardous Decomposition Products:

In the event of fire: See section 5.

Substances to be Avoided:

The generally known reaction partners of water

SECTION 11: TOXICOLOGICAL INFORMATION

Quantitative data on the toxicity of this product is not available.

In Case of Inhalation:

In Case of Skin Contact:

In Case of Eye Contact:

In Case of Ingestion:

Further Data: Hazardous properties cannot be excluded, but are relatively unlikely because of the low concentration of the dissolved substances, when the product is handled appropriately. The product should be handled with the usual care when dealing with chemicals.

SECTION 12: ECOLOGICAL INFORMATION

Quantitative data on the ecological effect of this product is not available.

Further Data: No ecological problems are to be expected when the product is handled and used with due care and attention.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal: Can be safely disposed of as an ordinary refuse.

SECTION 14: TRANSPORTATION INFORMATION

Land:

Not subject to transport regulations

Sea:

Not subject to transport regulations

Air:

Not subject to transport regulations

SECTION 15: REGULATORY INFORMATION

Labeling according to EC Directives:

Symbol: Non-hazardous according to Directives 67/548/EEC and 1999/45/EC.

R-phrases:

S-phrases:

Contains:

SECTION 16: OTHER INFORMATION

Text of R-phrases under Section 3

Revision Information

Legend

Revision Date: 2008-12-01

NA: Not Applicable

Supersedes edition of: 2006-05-05

ND: Not Determined

Reason for revision: REACH Compliance and General Update

**THE INFORMATION CONTAINED HEREIN IS BASED ON THE PRESENT STATE OF OUR
KNOWLEDGE. IT CHARACTERIZES THE PRODUCT WITH REGARD TO THE
APPROPRIATE SAFETY PRECAUTIONS. IT DOES NOT REPRESENT A GUARANTEE OF
THE PROPERTIES OF THE PRODUCT.**