

5

4

3

2

1

受控 CONTROLLED DOCUMENT

编号 P/N	CPFIUG885-CUST	版本 Rev	01	日期 Rel'd Date	Apr29,09
-----------	----------------	-----------	----	------------------	----------

DRAWING NO.

CPFIUG885-CUST

REVISIONS

01	OFFICIAL RELEASE					
	03-13-09	Z	Y	T	H	Thomas Chow

Description: BNC Twist-On For RG 6

Part No: CPFIUG885

Application: For RG-6 Cable

Crimp Tool: N/A

Impedance: 50 Ohms

Frequency Range: 0-4 GHz

Material: Body Zinc Nickel plated


Contact Phosphor bronze Gold plated

Insulator Teflon

Nut Zinc Nickel plated

RoHS Compliance: Yes

Technical Detail: Refer to Emerson Document P/N 27-0000



DIM OUTLINE

CUSTOMER COPY

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY GARY.ZHANG	DATE 03-13-09
DECIMALS	mm	CHECKED BY BETTY.YU	DATE 03-13-09
X	± 0.5	APPROVED BY THOMAS	DATE 03-13-09
X.X	± 0.3	U/M	mm
X.XX	± 0.1		
ANGLES	$\pm 0.5^\circ$		

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

		Connectivity Solutions	
TITLE		BNC TWIST-ON FOR RG 6	
SHEET 1 OF 1	DRAWING NO. CPFIUG885-CUST	SIZE A	