


High Tech (LR03)

AAA



Industry Standard Dimensions




Specifications

Classification:	Alkaline
Chemical System:	Zinc-Manganese Dioxide (Zn/MnO ₂) No added mercury or cadmium
Designation:	IEC-LR03
Nominal Voltage:	1.5 volts
Nominal IR:	150 to 300 milliohms (fresh)
Operating Temp:	-18°C to 55°C
Typical Weight:	11.5 grams
Typical Volume:	3.8 cubic centimeters
Jacket:	Plastic Label
Shelf Life:	10 years at 21°C
Terminal:	Flat Contact


Milliamp-Hours Capacity

Continuous discharge to 0.8 volts at 21°C




Industry Standard Testing (21°C):


TAPE PLAYER
10 ohm 1 hr/day



PHOTOFLASH
600 mA 10 sec/min 1 hr/day



Battery Selection Indicator



Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.