

Vitreous Wirewound Resistors with Lugs



FEATURES

- Complete welded construction
- Ceramic core
- High quality vitreous coating
- Available in adjustable = "E" or non inductive design = "Ni"
- Lugs with various termination styles suitable for soldering or bolt connection
- TCR 100. . .180 ppm/K



RoHS
COMPLIANT

STANDARD ELECTRICAL SPECIFICATIONS												
GLOBAL MODEL	HISTORICAL MODEL	TERMINAL	SIZE DIN 41432	POWER RATING $P_{40^{\circ}\text{C}}$ W	LIMITING VOLTAGE V	RESISTANCE RANGE Ω	TOLERANCE $\pm\%$	E-SERIES				
GWS0153	GWS 15	SL	9 x 45	15	250	4R3 - 20K	10	E 12, E 24, DIN 41432				
							5					
						30R - 15K	3					
						220R - 20K	2					
GWS0158	GWS 15 E			10		250	4R3 - 620R	10	E 12, E 24			
GWS015D	GWS 15 Ni							5				
								10				
								5				
GWS0203	GWS 20	SL	-	20	300	3R6 - 30K	10	E 12, E 24				
GWS0204		SS					5					
						-	3					
						180R - 30K	2					
GWS0208	GWS 20 E	SL		15		300	4R3 - 1K0		10	E 12, E 24		
GWS0209		SS							5			
GWS020D	GWS 20 Ni	SL					5R1 - 1K3		10		E 12, E 24, DIN 41432	
GWS020E		SS							5			
GWS0253	GWS 25	SL	13 x 55		25		300	3R6 - 39K	10			E 12, E 24, DIN 41432
GWS0254		SS						30R - 20K	5			
	91R - 39K							3				
								2				
GWS0258	GWS 25 E	SL		18	300	5R1 - 1K3		10	E 12, E 24			
GWS0259		SS						5				
GWS025D	GWS 25 Ni	SL				6R8 - 1K8		10		E 12, E 24, DIN 41432		
GWS025E		SS						5				
GWS0353	GWS 35	SL	-			30	400	5R1 - 47K			10	E 12, E 24
GWS0354		SS						-			5	
	56R - 47K							3				
								2				
GWS0358	GWS 35 E	SL		22	400	6R8 - 1K6		10	E 12, E 24			
GWS0359		SS						5				
GWS035D	GWS 35 Ni	SL				8R2 - 2K4		10		E 12, E 24, DIN 41432		
GWS035E		SS				8R2 - 2K4		5				
GWS0503	GWS 50	SL	16 x 63			40		3R3 - 62K			10	E 12, E 24, DIN 41432
GWS0504		SS									5	
GWS0505		SB									3	
GWS0507		FST									2	



STANDARD ELECTRICAL SPECIFICATIONS									
GLOBAL MODEL	HISTORICAL MODEL	TERMINAL	SIZE DIN 41432	POWER RATING $P_{40^{\circ}\text{C}}$ W	LIMITING VOLTAGE V	RESISTANCE RANGE Ω	TOLERANCE $\pm \%$	E-SERIES	
GWS0508	GWS 50 E	SL	16 x 63	30	400	8R2 - 2K0	10	E 12, E 24	
GWS0509		SS					5		
GWS050A		SB							
GWS050C		FST							
GWS050D	GWS 50 Ni	SL				10R - 3K0	10		5
GWS050E		SS							
GWS050F		SB							
GWS050H		FST							
GWS0753	GWS 75	SL	16 x 100	65	800	7R5 - 130K	10	E 12, E 24, DIN 41432	
GWS0754		SS				5			
GWS0755		SB				15R - 39K	3		
GWS0757		FST				30R - 130K	2		
GWS0758	GWS 75 E	SL		45		18R - 3K9	10	E 12, E 24	
GWS0759		SS					5		
GWS075A		SB							
GWS075C		FST							
GWS075D	GWS 75 Ni	SL				22R - 6K2	10		5
GWS075E		SS							
GWS075F		SB							
GWS075H		FST							
GWS1004	GWS 100	SS		24 x 100	80	600	6R8 - 110K	10	E 12, E 24, DIN 41432
GWS1006		SSB					5		
GWS1005		SB					20R - 51K	3	
GWS1007		FST					75R - 110K	2	
GWS1009	GWS 100 E	SS	60		13R - 5K1		10	E 12, E 24	
GWS100B		SSB					5		
GWS100A		SB							
GWS100C		FST							
GWS100E	GWS 100 Ni	SS			24R - 6K8		10		5
GWS100G		SSB							
GWS100F		SB							
GWS100H		FST							

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	HISTORICAL MODEL	TERMINAL	SIZE DIN 41432	POWER RATING $P_{40\text{ }^{\circ}\text{C}}$ W	LIMITING VOLTAGE V	RESISTANCE RANGE Ω	TOLERANCE $\pm\%$	E-SERIES		
GWS2204	GWS 220	SS	24 x 165	160	1250	13R - 160K	10	E 12, E 24, DIN 41432		
GWS2206		SSB				5				
GWS2205		SB				30R - 100K	3			
GWS2207		FST				56R - 160K	2			
GWS2209	GWS 220 E	SS		120		30R - 10K	10	E 12, E 24		
GWS220B		SSB					5			
GWS220A		SB								
GWS220C		FST								
GWS220E	GWS 220 Ni	SS					51R - 16K		10	5
GWS220G		SSB								
GWS220F		SB								
GWS220H		FST								
GWS3004	GWS 300	SS			300	2500	24R - 300K	10	E 12, E 24, DIN 41432	
GWS3006		SSB					5			
GWS3005		SB					51R - 150K	3		
GWS3007		FST					110R - 300K	2		
GWS3009	GWS 300 E	SS		200	56R - 20K		10	E 12, E 24		
GWS300B		SSB					5			
GWS300A		SB								
GWS300C		FST								
GWS300E	GWS 300 Ni	SS					100R - 30K		10	5
GWS300G		SSB								
GWS300F		SB								
GWS300H		FST								
GWS5004	GWS 500	SS	36 x 330		500	3000	39R - 270K	10	E 12, E 24, DIN 41432	
GWS5006		SSB					5			
GWS5005		SB					100R - 240K	3		
GWS5007		FST					75R - 270K	2		
GWS5009	GWS 500 E	SS	300	100R - 36K	10		E 12, E 24			
GWS500B		SSB			5					
GWS500A		SB								
GWS500C		FST								



STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	HISTORICAL MODEL	TERMINAL	SIZE DIN 41432	POWER RATING $P_{40^{\circ}\text{C}}$ W	LIMITING VOLTAGE V	RESISTANCE RANGE Ω	TOLERANCE $\pm \%$	E-SERIES
GWSN844	GWS 30/100	SS		150	1600	9R1 - 100K	10	E 12, E 24, DIN 41432
GWSN846		SSB					5	
GWSN845		SB				-	3	
GWSN847		FST				27R - 100K	2	
GWSN849	GWS 30/100 E	SS		110		22R - 8K2	10	E 12, E 24
GWSN84B		SSB						
GWSN84A		SB					5	
GWSN84C		FST						
GWSN914	GWS 30/133	SS		200	2300	13R - 160K	10	E 12, E 24, DIN 41432
GWSN916		SSB					5	
GWSN915		SB				-	3	
GWSN917		FST				27R - 160K	2	
GWSN919	GWS 30/133 E	SS		130		36R - 13K	10	E 12, E 24
GWSN91B		SSB						
GWSN91A		SB					5	
GWSN91C		FST						

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: GWS01531009KLX000 (preferred part number format)

G	W	S	0	1	5	3	1	0	0	9	K	L	X	0	0	0
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---




MODEL	TCR/MATERIAL	SPECIAL CHARACTER	VALUE	TOLERANCE	PACKAGING	SPECIAL
GWS	015 = 15 020 = 20 025 = 25 035 = 35 050 = 50 075 = 75 100 = 100 220 = 220 300 = 300 500 = 500 N84 = 30/100 N91 = 30/133	3 = SL 4 = SS 5 = SB 6 = SSB 7 = FST 8 = E SL 9 = E SS A = E SB B = E SSB C = E FST D = NI SL E = NI SS F = NI SB G = NI SSB H = NI FST I = SWI SL J = SWI SS K = SWI SB L = SWI SSB M = SWI FST Z = Value overflow (BV)	3 digit value 1 digit multiplier MULTIPLIER 8 = $\times 10^{-2}$ 9 = $\times 10^{-1}$ 0 = $\times 10^0$ 1 = $\times 10^1$ 2 = $\times 10^2$ 3 = $\times 10^3$	G = $\pm 2.0 \%$ H = $\pm 3.0 \%$ J = $\pm 5.0 \%$ K = $\pm 10.0 \%$	(See Packing table)	The 5 digit BV number will be encoded using a 36 character code. This code contains numbers 0...9 and letters A...Z (36 characters total) and allows to encode at least 46 655 five digit BV numbers. 000 = Standard

Historical Part Number Example: GWS 15 SL 10R 10 % (will continue to be accepted)





GWS 15	SL	10R	10 %
HISTORICAL MODEL	SPECIAL CHARACTER	VALUE	TOLERANCE

PACKAGING TABLE

SAP	DESCRIPTION	TYPE
LX	Loose pack, without quantity	all
ZX	Special pack (with BV #), without quantity Note: LX = B29 on Dale legacy ZX = S51 on Dale legacy	all






DIMENSIONS**SL TERMINALS****ADJUSTABLE LUGS**GWS 15 E
GWS 20 E

from GWS 25 E


**SS TERMINALS****CORE SECTION**

MODEL	DIMENSIONS in millimeters [inches]						
	GWS 15 GWS 15 E GWS 15 Ni	GWS 20 GWS 20 E GWS 20 Ni		GWS 25 GWS 25 E GWS 25 Ni		GWS 35 GWS 35 E GWS 35 Ni	
TERMINAL	SL	SL	SS	SL	SS	SL	SS
DIMENSION							
D	7.5 ± 0.5 [0.295 ± 0.020]	9.5 ± 0.5 [0.374 ± 0.020]		11.8 ± 0.8 [0.465 ± 0.031]		11.8 ± 0.8 [0.465 ± 0.031]	
L	45 ± 1.5 [1.772 ± 0.059]	50 ± 1.5 [1.969 ± 0.059]		55 ± 1.5 [2.165 ± 0.059]		62 ± 2 [2.441 ± 0.079]	
a ± 2 [a ± 0.079]	36 [1.417]	39 [1.535]	40 [1.575]	43 [1.693]	44 [1.732]	50 [1.969]	51 [2.008]
b	4 [0.157]	4 [0.157]	5 [0.197]	4 [0.157]	5 [0.197]	4 [0.157]	5 [0.197]
b ₁	4 [0.157]	4 [0.157]	4 [0.157]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]
c	15.5 [0.610]	18 [0.709]	10.5 [0.413]	19 [0.748]	11.5 [0.453]	19 [0.748]	11.5 [0.453]
d	2.6 [0.102]	3.5 [0.138]	3.5 [0.138]	5.5 [0.217]	5.5 [0.217]	5.5 [0.217]	5.5 [0.217]
e	1.5 [0.059]	2 [0.079]	M3 x 16	2 [0.079]	M3 x 16	2 [0.079]	M3 x 16
e ₁	2.8 [0.110]	2.8 [0.110]	2.8 [0.110]	2.8 [0.110]	2.8 [0.110]	2.8 [0.110]	2.8 [0.110]
k	2.5 [0.098]	3.5 [0.138]	2.5 [0.098]	4 [0.157]	3 [0.118]	4 [0.157]	3 [0.118]
WEIGHT (g)	6	8		13		15	





DIMENSIONS (continued)

SL TERMINALS

FST TERMINALS

SS AND SSB TERMINALS

SB TERMINALS

CORE SECTION

ADJUSTABLE LUGS


from GWS 25 E



MODEL	DIMENSIONS in millimeters [inches]															
	GWS 50 GWS 50 E GWS 50 Ni				GWS 75 GWS 75 E GWS 75 Ni				GWS 100 GWS 100 E GWS 100 Ni				GWS 220 GWS 220 E GWS 220 Ni			
TERMINAL	SL	SS	SB	FST	SL	SS	SB	FST	SL	SSB	SB	FST	SS	SSB	SB	FST
DIMENSION																
D	14.8 ± 0.8 [0.583 ± 0.031]				14.8 ± 0.8 [0.583 ± 0.031]				22.3 ± 1.3				22.3 ± 1.3			
L	62 ± 2 [2.441 ± 0.079]				100 ± 2 [4.100 ± 0.080]				100 ± 2 [4.100 ± 0.080]				165 ± 2 [6.760 ± 0.080]			
a ± 2 [a ± 0.079]	50 [1.969]	51 [2.008]	51 [2.008]	48 [1.890]	86 [3.520]	87 [3.570]	87 [3.570]	84 [3.440]	72 [2.950]				136 [5.570]			
b	4 [0.157]	5 [0.197]	5 [0.197]	6.3 [0.248]	4 [0.157]	5 [0.197]	5 [0.197]	6.3 [0.248]	8 [0.330]	8 [0.330]	8 [0.330]	6.3 [0.620]	8 [0.330]	8 [0.330]	8 [0.330]	6.3 [0.620]
b ₁	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]
c	20.5 [0.807]	13 [0.512]	23 [0.906]	23.5 [0.925]	20.5 [0.807]	13 [0.512]	23 [0.906]	23.5 [0.925]	18.5 [0.760]	18.5 [0.760]	29.5 [1.210]	27 [1.110]	18.5 [0.760]	18.5 [0.760]	29.5 [1.210]	27 [1.110]
d	5.5 [0.217]	5.5 [0.217]	5.5 [0.217]	5.5 [0.217]	5.5 [0.217]	5.5 [0.217]	5.5 [0.217]	5.5 [0.217]	10 [0.410]	10 [0.410]	10 [0.410]	10 [0.410]	10 [0.410]	10 [0.410]	10 [0.410]	10 [0.410]
e	2 [0.079]	M3 x 16			2 [0.079]	M3 x 16			M4 x 20			-	M4 x 20			-
e ₁	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]
k	4 [0.157]	3 [0.118]	3 [0.118]	3 [0.118]	5 [0.197]	4 [0.157]	4 [0.157]	4 [0.157]	10 [0.410]	10 [0.410]	10 [0.410]	10 [0.410]	10.5 [0.430]	10.5 [0.430]	10.5 [0.430]	10.5 [0.430]
WEIGHT (g)	25				40				92				135			

DIMENSIONS (continued)**SS TERMINALS****SSB TERMINALS****SB TERMINALS****FST TERMINALS**

FST A 6.3 mm [0.248]/DIN 46244
(at end terminals only)


CORE SECTION

GWS 15 ... GWS 500








GWS 30/ ...

ADJUSTABLE LUGS

from GWS 25 E



MODEL	DIMENSIONS in millimeters [inches]															
	GWS 300 GWS 300 E GWS 300 Ni				GWS 500 GWS 500 E				GWS 30/100 GWS 30/100 E				GWS 30/133 GWS 30/133 E			
TERMINAL	SS	SSB	SB	FST	SS	SSB	SB	FST	SS	SSB	SB	FST	SS	SSB	SB	FST
DIMENSION																
D	22.3 ± 1.3 [0.878 ± 0.051]				32.5 ± 1.5 [1.330 ± 0.060]				32.5 ± 1.5 [1.330 ± 0.060]				32.5 ± 1.5 [1.330 ± 0.060]			
L	265 ± 4 [2.433 ± 0.157]				330 ± 5 [13.52 ± 0.200]				100 ± 2.5 [4.100 ± 0.100]				133 ± 3 [5.450 ± 0.120]			
a ± 2 [a ± 0.079]	235 [9.252]				280 [11.48]				85 [3.480]				118 [4.840]			
b	8 [0.315]	8 [0.315]	8 [0.315]	6.3 [0.248]	8 [0.315]	8 [0.315]	8 [0.315]	6.3 [0.248]	8 [0.315]	8 [0.315]	8 [0.315]	6.3 [0.248]	8 [0.315]	8 [0.315]	8 [0.315]	6.3 [0.248]
b ₁	5 [0.197]	5 [0.197]	5 [0.197]	5 [0.197]	8 [0.315]	8 [0.315]	8 [0.315]	8 [0.315]	8 [0.315]	8 [0.315]	8 [0.315]	8 [0.315]	8 [0.315]	8 [0.315]	8 [0.315]	8 [0.315]
c	18.5 [0.728]	18.5 [0.728]	29.5 [1.161]	27 [1.063]	23.5 [0.960]	23.5 [0.960]	35 [1.430]	31.5 [1.290]	23.5 [0.960]	23.5 [0.960]	35 [1.430]	31.5 [1.290]	23.5 [0.960]	23.5 [0.960]	35 [1.430]	31.5 [1.290]
d	10 [0.394]	10 [0.394]	10 [0.394]	10 [0.394]	18.5 [0.760]	18.5 [0.760]	18.5 [0.760]	18.5 [0.760]	14 [0.570]	14 [0.570]	14 [0.570]	14 [0.570]	14 [0.570]	14 [0.570]	14 [0.570]	14 [0.570]
e	M4 x 20				M4 x 20				M4 x 20				M4 x 20			
e ₁	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	3.2 [0.126]	4.2 [0.170]	4.2 [0.170]	4.2 [0.170]	4.2 [0.170]	4.2 [0.170]	4.2 [0.170]	4.2 [0.170]	4.2 [0.170]	4.2 [0.170]	4.2 [0.170]	4.2 [0.170]	4.2 [0.170]
k	11 [0.433]	11 [0.433]	11 [0.433]	11 [0.433]	21 [0.860]	21 [0.860]	21 [0.860]	21 [0.860]	3.5 [0.138]	3.5 [0.138]	3.5 [0.138]	3.5 [0.138]	3.5 [0.138]	3.5 [0.138]	3.5 [0.138]	3.5 [0.138]
WEIGHT (g)	238				425				183				265			





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.