


Features :

- Constant voltage design
- Universal AC input / Full range
- Fully encapsulated with IP67 level
- Withstand 300VAC surge input for 5 seconds
- Protections: Short circuit / Overload / Over voltage
- Fully isolated plastic case
- Cooling by free air convection
- UL1310 Class 2 power unit, pass LPS
- 100% full load burn-in test
- Low cost, high reliability
- Suitable for LED lighting and moving sign applications (Note.7)
- 2 years warranty


LPS IP67  (for 48V only)  **US** (except for 5V,48V) 
SPECIFICATION

MODEL		LPV-60-5	LPV-60-12	LPV-60-15	LPV-60-24	LPV-60-36	LPV-60-48
OUTPUT	DC VOLTAGE	5V	12V	15V	24V	36V	48V
	RATED CURRENT	8A	5A	4A	2.5A	1.67A	1.25A
	CURRENT RANGE	0 ~ 8A	0 ~ 5A	0 ~ 4A	0 ~ 2.5A	0 ~ 1.67A	0 ~ 1.25A
	RATED POWER	40W	60W	60W	60W	60W	60W
	RIPPLE & NOISE (max.) Note.2	80mVp-p	120mVp-p	120mVp-p	150mVp-p	150mVp-p	150mVp-p
	VOLTAGE TOLERANCE Note.3	±8.0%	±5.0%				
	LINE REGULATION	±1.0%					
	LOAD REGULATION	±6.0%	±2.0%				
INPUT	SETUP, RISE TIME Note.6	500ms, 20ms / 230VAC	500ms, 20ms / 115VAC at full load(for 5~36V) ; 500ms, 30ms / 230VAC	500ms, 30ms / 115VAC at full load(for 48V)			
	HOLD UP TIME (Typ.)	50ms/230VAC	16ms/115VAC at full load				
	VOLTAGE RANGE Note.4	90 ~ 264VAC	127 ~ 370VDC				
	FREQUENCY RANGE	47 ~ 63Hz					
	EFFICIENCY (Typ.)	76%	83%	83%	86%	86%	86%
	AC CURRENT	1.2A/115VAC 1A/230VAC					
PROTECTION	INRUSH CURRENT(max.)	COLD START 30A/115VAC	60A/230VAC				
	LEAKAGE CURRENT	0.25mA / 240VAC					
	OVER CURRENT	110 ~ 150% rated output power Protection type : Hiccup mode, recovers automatically after fault condition is removed					
ENVIRONMENT	OVER VOLTAGE	5.75 ~ 6.75V	13.8 ~ 16.2V	17.25 ~ 20.25V	27.6 ~ 32.4V	41.4 ~ 48.6V	55.2 ~ 64.8V
		Protection type : Shut down o/p voltage, re-power on to recover					
	WORKING TEMP.	-30 ~ +70°C (Refer to output load derating curve)					
	WORKING HUMIDITY	20 ~ 90% RH non-condensing					
	STORAGE TEMP., HUMIDITY	-40 ~ +80°C, 10 ~ 95% RH					
SAFETY & EMC	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)					
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes					
	SAFETY STANDARDS	UL1310 Class 2(except for LPV-60-5), CAN/CSA C22.2 No. 223-M91(except for LPV-60-5,LPV-60-48), IP67 approved ; design refer to TUV EN60950-1, EN61347-2-13					
	WITHSTAND VOLTAGE	I/P-O/P:3KVAC					
	ISOLATION RESISTANCE	I/P-O/P:>100M Ohms / 500VDC / 25°C / 70% RH					
OTHERS	EMI CONDUCTION & RADIATION	Compliance to EN55022 (CISPR22) Class B					
	HARMONIC CURRENT	Compliance to EN61000-3-2 Class A, EN61000-3-3					
	EMS IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11; ENV50204, EN55024, light industry level, criteria A					
	MTBF	732Khrs min. MIL-HDBK-217F (25°C)					
NOTE	DIMENSION	162.5*42.5*32mm (L*W*H)					
	PACKING	0.4Kg; 32pcs/13.8Kg/0.56CUFT					


1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature.
2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uF & 47uF parallel capacitor.
3. Tolerance : includes set up tolerance, line regulation and load regulation.
4. Derating may be needed under low input voltage. Please check the static characteristics for more details.
5. The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again.
6. Length of set up time is measured at first cold start. Turning ON/OFF the power supply may lead to increase of the set up time.
7. In the European market this product is only suitable for LED lighting applications that don't have to comply with the harmonic current requirements of EN61000-3-2 Class C.

■ Mechanical Specification


Case No. 976A Unit:mm




■ Block Diagram



Derating Curve



■ Static Characteristics



MODEL : LPV-60-5

OUTPUT FUNCTION TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	RIPPLE & NOISE	V1:80 mVp-p (Max)	I/P: 230VAC O/P:FULL LOAD Ta:25℃	V1: 30 mVp-p (Max)	P
2	OUTPUT VOLTAGE TOLERANCE	V1: 8 %~ -8 % (Max)	I/P: 100VAC / 264 VAC O/P:FULL/ MIN LOAD Ta:25℃	V1: 2.5 %~ -2.5 %	P
3	LINE REGULATION	V1: 1 %~ -1 % (Max)	I/P: 100 VAC ~ 264 VAC O/P:FULL LOAD Ta:25℃	V1: 0.02 %~ -0.02 %	P
4	LOAD REGULATION	V1: 6 %~ -6 % (Max)	I/P: 230 VAC O/P:FULL ~MIN LOAD Ta:25℃	V1: 2.5 %~ -2.5 %	P
5	SET UP TIME	230VAC: 500 ms (Max) 115 VAC: 500 ms (Max)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25℃	230VAC/ 157 ms 115VAC/ 314 ms	P
6	RISE TIME	230VAC: 20 ms (Max) 115VAC: 20 ms (Max)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25℃	230VAC/ 7 ms 115VAC/ 8 ms	P
7	HOLD UP TIME	230VAC: 50 ms (TYP) 115VAC: 16 ms (TYP)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25℃	230VAC/ 120 ms 115VAC/ 24 ms	P
8	OVER/UNDERSHOOT TEST	< ±5%	I/P: 230 VAC O/P:FULL LOAD Ta:25℃	TEST: <5 %	P
9	DYNAMIC LOAD	V1: 1000 mVp-p	I/P: 230 VAC O/P:FULL /Min LOAD 90%DUTY/1KHZ Ta:25℃	324 mVp-p	P

INPUT FUNCTION TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	INPUT VOLTAGE RANGE	90VAC~264 VAC	I/P: TESTING O/P: FULL LOAD Ta: 25°C	66 V~264V	P
			I/P: LOW-LINE-3V= 87 V HIGH-LINE+15%=300 V O/P: FULL/MIN LOAD ON: 30 Sec . OFF: 30 Sec 10MIN (AC POWER ON/OFF NO DAMAGE)	TEST: OK	
2	INPUT FREQUENCY RANGE	47HZ ~63 HZ NO DAMAGE OSC	I/P: 100VAC ~ 264 VAC O/P: FULL~MIN LOAD Ta: 25°C	TEST: OK	P
3	EFFICIENCY	76 % (TYP)	I/P: 230 VAC O/P: FULL LOAD Ta: 25°C	77%	P
4	INPUT CURRENT	230V/ 1 A (TYP) 115V/ 1.2 A (TYP)	I/P: 230 VAC I/P: 115 VAC O/P: FULL LOAD Ta: 25°C	I = 0.47 A/ 230 VAC I = 0.81 A/ 115 VAC	P
5	INRUSH CURRENT	230V/ 60 A (TYP) 115V/ 30 A (TYP) COLD START	I/P: 230 VAC I/P: 115 VAC O/P: FULL LOAD Ta: 25°C	I = 58 A/ 230 VAC I = 29 A/ 115 VAC	P
6	LEAKAGE CURRENT	< 0.25 mA / 240 VAC	I/P: 264 VAC O/P: Min LOAD Ta: 25°C	L-FG: 0.01 mA N-FG: 0.01 mA	P

PROTECTION FUNCTION TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	OVER LOAD PROTECTION	110%~ 150 %	I/P: 230 VAC I/P: 115 VAC O/P: TESTING Ta: 25°C	135 %/ 230 VAC 133 %/ 115 VAC Hiccup Mode	P
2	OVER VOLTAGE PROTECTION	CH1: 5.75 V~ 6.75 V	I/P: 230 VAC I/P: 115 VAC O/P: MIN LOAD Ta: 25°C	6.4 V/ 230 VAC 6.4 V/ 115 VAC Shut down Re- power ON	P
3	SHORT PROTECTION	SHORT EVERY OUTPUT 1 HOUR NO DAMAGE	I/P: 264 VAC O/P: FULL LOAD Ta: 25°C	NO DAMAGE Hiccup Mode	P

ENVIRONMENT TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT																																																																											
1	TEMPERATURE RISE TEST	MODEL : LPV-60-24 1. ROOM AMBIENT BURN-IN : 2 HRS I/P: 230VAC O/P: FULL LOAD Ta=30.9 °C 2. HIGH AMBIENT BURN-IN : 8 HRS I/P: 230VAC O/P: FULL LOAD Ta=63.2°C <table><tr><th>NO</th><th>Position</th><th>P/N</th><th>ROOM AMBIENT Ta=30.9 °C</th><th>HIGH AMBIENT Ta=63.2 °C</th></tr><tr><td>1</td><td>U1</td><td>NCP1230</td><td>82.2°C</td><td>104.4°C</td></tr><tr><td>2</td><td>BD1</td><td>4A/600V GLASS D3SB60</td><td>81.1°C</td><td>102.2°C</td></tr><tr><td>3</td><td>LF1</td><td>LF158</td><td>72.5°C</td><td>92.9°C</td></tr><tr><td>4</td><td>C5</td><td>120u/400V 105°C KMG</td><td>86.8°C</td><td>108.5°C</td></tr><tr><td>5</td><td>Q1</td><td>2SK3562 6A/600V</td><td>95.1°C</td><td>118.4°C</td></tr><tr><td>6</td><td>D1</td><td>EGP20J 2A/600V</td><td>88.6°C</td><td>112.8°C</td></tr><tr><td>7</td><td>ZD1</td><td>P6KE180A</td><td>85.3°C</td><td>105.8°C</td></tr><tr><td>8</td><td>D40</td><td>1A/100V 1N4002</td><td>88.2°C</td><td>111.2°C</td></tr><tr><td>9</td><td>C40</td><td>47u/50V UL10Kh YXM</td><td>87.3°C</td><td>110.8°C</td></tr><tr><td>10</td><td>T1</td><td>TF1775</td><td>86.1°C</td><td>109.6°C</td></tr><tr><td>11</td><td>D100</td><td>FMX-12SL 10A/200V</td><td>79.8°C</td><td>102.6°C</td></tr><tr><td>12</td><td>C105</td><td>330u/35V L7Kh YXG</td><td>69.4°C</td><td>92.3°C</td></tr><tr><td>13</td><td>L100</td><td>RB010E</td><td>63.6°C</td><td>87.0°C</td></tr><tr><td>14</td><td>CASE</td><td>UPCASE</td><td>67.4°C</td><td>98.6°C</td></tr></table>			NO	Position	P/N	ROOM AMBIENT Ta=30.9 °C	HIGH AMBIENT Ta=63.2 °C	1	U1	NCP1230	82.2°C	104.4°C	2	BD1	4A/600V GLASS D3SB60	81.1°C	102.2°C	3	LF1	LF158	72.5°C	92.9°C	4	C5	120u/400V 105°C KMG	86.8°C	108.5°C	5	Q1	2SK3562 6A/600V	95.1°C	118.4°C	6	D1	EGP20J 2A/600V	88.6°C	112.8°C	7	ZD1	P6KE180A	85.3°C	105.8°C	8	D40	1A/100V 1N4002	88.2°C	111.2°C	9	C40	47u/50V UL10Kh YXM	87.3°C	110.8°C	10	T1	TF1775	86.1°C	109.6°C	11	D100	FMX-12SL 10A/200V	79.8°C	102.6°C	12	C105	330u/35V L7Kh YXG	69.4°C	92.3°C	13	L100	RB010E	63.6°C	87.0°C	14	CASE	UPCASE	67.4°C	98.6°C	P
NO	Position	P/N	ROOM AMBIENT Ta=30.9 °C	HIGH AMBIENT Ta=63.2 °C																																																																												
1	U1	NCP1230	82.2°C	104.4°C																																																																												
2	BD1	4A/600V GLASS D3SB60	81.1°C	102.2°C																																																																												
3	LF1	LF158	72.5°C	92.9°C																																																																												
4	C5	120u/400V 105°C KMG	86.8°C	108.5°C																																																																												
5	Q1	2SK3562 6A/600V	95.1°C	118.4°C																																																																												
6	D1	EGP20J 2A/600V	88.6°C	112.8°C																																																																												
7	ZD1	P6KE180A	85.3°C	105.8°C																																																																												
8	D40	1A/100V 1N4002	88.2°C	111.2°C																																																																												
9	C40	47u/50V UL10Kh YXM	87.3°C	110.8°C																																																																												
10	T1	TF1775	86.1°C	109.6°C																																																																												
11	D100	FMX-12SL 10A/200V	79.8°C	102.6°C																																																																												
12	C105	330u/35V L7Kh YXG	69.4°C	92.3°C																																																																												
13	L100	RB010E	63.6°C	87.0°C																																																																												
14	CASE	UPCASE	67.4°C	98.6°C																																																																												
2	OVER LOAD BURN-IN TEST	NO DAMAGE 1 HOUR (MIN)	I/P: 230 VAC O/P: 130 % LOAD Ta:30.3°C	TEST : OK	P																																																																											
3	LOW TEMPERATURE TURN ON TEST	TURN ON AFTER 2 HOUR	I/P: 264 VAC O/P: 100 % LOAD Ta= -35 °C	TEST : OK	P																																																																											
4	HIGH HUMIDITY HIGH TEMPERATURE HIGH VOLTAGE TURN ON TEST	AFTER 12 HOURS IN CHAMBER ON CONTROL °C NO DAMAGE	I/P: 272 VAC O/P:FULL LOAD Ta= 60 °C HUMIDITY= 95 %R.H	TEST : OK	P																																																																											
5	TEMPERATURE COEFFICIENT	± 0.03 %(0~50°C)	I/P: 230 VAC O/P:FULL LOAD	± 0.006 %(0~50°C)	P																																																																											
6	VIBRATION TEST	1 Carton & 1 Set (1) Waveform: Sine Wave (2) Frequency:10~500Hz (3) Sweep Time:10min/sweep cycle (4) Acceleration:2G (5) Test Time:1 hour in each axis (X.Y.Z) (6) Ta:25°C		TEST : OK	P																																																																											

SAFETY TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	WITHSTAND VOLTAGE	I/P-O/P: 3 KVAC/min	I/P-O/P: 3.6 KVAC/min	I/P-O/P: 2.56 mA NO DAMAGE	P
2	ISOLATION RESISTANCE	I/P-O/P:500VDC>100MΩ	I/P-O/P: 500 VDC Ta:25°C / 70%RH	I/P-O/P: 30 GΩ NO DAMAGE	P
3	APPROVAL	TUV: Certificate NO : UL: File NO :			N/A

E.M.C TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	HARMONIC	EN61000-3-2 CLASS A	I/P: 230/240/220 VAC/50HZ O/P:100/75/50/25% LOAD Ta:25°C	PASS	P
2	CONDUCTION	EN55022 CLASS B	I/P: 230 VAC (50HZ) O/P:FULL/50% LOAD Ta:25°C	PASS Test by certified Lab	P
3	RADIATION	EN55022 CLASS B	I/P: 230 VAC (50HZ) O/P:FULL LOAD Ta:25°C	PASS Test by certified Lab	P
4	E.S.D	EN61000-4-2 LIGHT INDUSTRY AIR:8KV / Contact:4KV	I/P: 230 VAC/50HZ O/P:FULL LOAD Ta:25°C	CRITERIA A	P
5	E.F.T	EN61000-4-4 LIGHT INDUSTRY INPUT: 1KV	I/P: 230 VAC/50HZ O/P:FULL LOAD Ta:25°C	CRITERIA A	P
6	SURGE	IEC61000-4-5 LIGHT INDUSTRY L-N :1KV L,N-PE:2KV	I/P: 230 VAC/50HZ O/P:FULL LOAD Ta:25°C	CRITERIA A	P
7	Test by certified Lab & Test Report Prepare				

M.T.B.F & LIFE CYCLE CALCULATION

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	CAPACITOR LIFE CYCLE	LPV-60-24:SUPPOSE C105 IS THE MOST CRITICAL COMPONENT I/P: 230VAC O/P:FULL LOAD Ta= 25 °C LIFE TIME= 137172 HRS I/P: 230VAC O/P:FULL LOAD Ta= 50 °C LIFE TIME= 46522 HRS			P
2	MTBF	MIL-HDBK-217F NOTICES2 PARTS COUNT TOTAL FAILURE RATE: 732K HRS			P
3	ORT (Ongoing Reliability test)	I/P : 230VAC O/P : FULL LOAD TA=50°C Sample=10pcs TEST TIME=720HRS			P

COMPONENT STRESS TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	Power Transistor (D to S) or (C to E) Peak Voltage	Q1 Rated STP10NK60ZFP :600 V/10A	I/P:High-Line +3V = 267 V O/P: (1)Full Load Turn on (2) Output Short Ta:25℃	(1) 574 V (2) 578 V	P
2	Diode Peak Voltage	D100Rated MBR1545CT : 15A / 45V	I/P:High-Line +3V = 267 V O/P: (1)Full Load Turn on (2)Output Short Ta:25℃	(1) 37.4 V (2) 19 V	P
3	Clamp Diode Peak Voltage	D1 Rated EGP20J : 2A/600V	I/P:High-Line +3V = 267 V O/P: (1) Dynamic Load 90%Duty/1KHz Ta:25℃	(1) 536 V	P
4	Input Capacitor Voltage	C5 Rated 120u/400V 105℃	I/P:High-Line +3V = 267 V O/P: (1)Full Load Turn on /Off (2) Min load Turn on /Off (3)Full Load /Min load Change Ta:25℃	(1) 390 V (2) 394 V (3) 394 V	P
5	Control IC Voltage Test	U1 NCP1230/ 18V	I/P:High-Line +3V = 267 V O/P: (1)Full Load Turn on /Off (2) Min load Turn on /Off (3)Full Load /Min load Change Ta:25℃	(1) 10.89 V (2) 8.7 V (3) 10.89 V	P

DATE	SAMPLE	TEST RESULT	TESTER	APPROVAL
2008/4/9	RD SAMPLE	PASS	SANFORD SU	VINCENT TSENG
2008/8/7	PRODUCT SAMPLE W0806B58	PASS	SANFORD SU	VINCENT TSENG
2008/9/4	PRODUCT SAMPLE W0807D09	PASS	SANFORD SU	VINCENT TSENG

2003/12/12 A50-F023