







THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		- - -	
© COPYRIGHT -	By -	ALL RIGHTS RESERVED.			

1. TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.15
2. FOR APPLICATION INFORMATION SEE AMP SPEC. 114-19019.
3. FOR PERFORMANCE REQUIREMENTS SEE AMP SPEC. 108-19064



PRINTED CIRCUIT BOARD LAYOUT


[VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.05
PRINTED CIRCUIT BOARD THICKNESS: 1.6 mm NOMINAL.

LOC		DIST		REVISIONS			
H	—	P	LTR	DESCRIPTION	DATE	DMN	APD
		J4		ECR-14-008810	12JUN14	CW	SH
		J5		ECO-15-014053	24SEP2015	AD	SH
		J6		ECO-16-004330	24MAR2016	AD	SH

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLG 1 PLG 2 PLG 3 PLG 4 PLG	± ± ± ± ±
ANGLES	±
MATERIAL SEE TABLE	SEE TABLE





800 PCS. ON A 60cm. DIA. REEL	6 POSITIONS/ 6 CONTACTS.	IN CONTACT AREA: 1.2µm MIN. SEL. GOLD OVER 1.2µm MIN. NICKEL SOLDER TINES: 2.0µm MIN. TIN OVER 1.2µm MIN. NICKEL	HOUSING: PBT,UL 94V-HB COLOR: BLACK CONTACTS: PHOSPHOR BRONZE	216548-1
PACKAGING	REMARKS	FINISH	MATERIAL	PART NUMBER

DMN J.V.LIEMPT CHK C.STERKEN APD L.V.SOEST PRODUCT SPEC APPLICATION SPEC WEIGHT		22JAN92 — — — — —		NAME MODULAR JACK, 6 POS. TOP ENTRY, SMALL SIZE WITH PANEL STOPS, FOR PRINTED CIRCUIT BOARDS		SIZE A2	DWG CODE 00779	DRAWING NO 216548	SCALE —	SHEET 1 of 3	REV J6
CUSTOMER DRAWING											

16.0		13.5		16.4		5.9	
13.2		1.3					
							

LOC		DIST		REVISIONS			
H		—		P	LTR	DATE	DWN
				SEE SHEET 1/3			APRO

- NOTES:
1. TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.15
 2. FOR APPLICATION INFORMATION SEE AMP SPEC. 114–19019.
 3. FOR PERFORMANCE REQUIREMENTS SEE AMP SPEC. 108–19064



216548

B



B

C

C

D

D



PRINTED CIRCUIT BOARD LAYOUT

[VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.]
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.05
PRINTED CIRCUIT BOARD THICKNESS: 1.6 mm NOMINAL.

A





A

THIS DRAWING IS A CONTROLLED DOCUMENT.		FINISH		MATERIAL		PART NUMBER	
PACKAGING		REMARKS		IN CONTACT AREA: 1.2µm MIN. SEL. GOLD OVER 1.2µm MIN. NICKEL		HOUSING: PBT, UL 94V-HB COLOR: BLACK	
800 PCS. ON A 60cm. DIA. REEL		6 POSITIONS/ 4 CONTACTS.		SOLDER TINES: 2.0µm MIN. TIN OVER 1.2µm MIN. NICKEL		CONTACTS: PHOSPHOR BRONZE	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		MODULAR JACK, 6 POS. TOP ENTRY, SMALL SIZE WITH PANEL STOPS, FOR PRINTED CIRCUIT BOARDS	
0 PLG 1 PLG 2 PLG 3 PLG 4 PLG		± ± ± ± ±		APPRO		SIZE	
ANGLES		± ± ± ± ±		APPLICATION SPEC		CAGE CODE	
FINISH		± ± ± ± ±		WEIGHT		DRAWING NO	
SEE TABLE		SEE TABLE		—		A2	
MATERIAL		—		—		00779	
SEE TABLE		—		—		C=216548	
CUSTOMER DRAWING		SCALE		—		SHEET	
						2 OF 3	
						REV	
						J6	

STE TE Connectivity

LOC		DIST		REVISIONS			
H		—		P	LTR	DATE	DWN
				DESCRIPTION			
				SEE SHEET 1/3			

- NOTES:
1. TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.15
 2. FOR APPLICATION INFORMATION SEE AMP SPEC. 114–19019.
 3. FOR PERFORMANCE REQUIREMENTS SEE AMP SPEC. 108–19064



216548

B

B

C

C

D



D

A

A

PRINTED CIRCUIT BOARD LAYOUT

[VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.]
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.05
PRINTED CIRCUIT BOARD THICKNESS: 1.6 mm NOMINAL.



240 PCS. IN ONE TRAY		6 POSITIONS/4 CONTACTS.		IN CONTACT AREA: 1.2µm MIN. SEL. GOLD OVER 1.2µm MIN. NICKEL SOLDER TINES: 2.0µm MIN. TIN OVER 1.2µm MIN. NICKEL		HOUSING: PBT,UL 94V-HB COLOR: BLACK CONTACTS: PHOSPHOR BRONZE		1-216548-5	
240 PCS. IN ONE TRAY		6 POSITIONS/4 CONTACTS.		IN CONTACT AREA: 1.2µm MIN. SEL. GOLD OVER 1.2µm MIN. NICKEL SOLDER TINES: 2.0µm MIN. TIN OVER 1.2µm MIN. NICKEL		HOUSING: PBT,UL 94V-VO COLOR: GRAY CONTACTS: PHOSPHOR BRONZE		216548-6	
800 PCS. ON A 60cm. DIA. REEL		6 POSITIONS/4 CONTACTS.		IN CONTACT AREA: 1.2µm MIN. SEL. GOLD OVER 1.2µm MIN. NICKEL SOLDER TINES: 2.0µm MIN. TIN OVER 1.2µm MIN. NICKEL		HOUSING: PBT,UL 94V-HB COLOR: BLACK CONTACTS: PHOSPHOR BRONZE		216548-5	
PACKAGING		REMARKS		FINISH		MATERIAL		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DIM J.V.L.E.M.P.T 22JAN92		TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK C. STERKEN APRO L.V.S.O.F.S.T PRODUCT SPEC - NAME		 MODULAR JACK, 6 POS. TOP ENTRY, SMALL SIZE WITHOUT PANEL STOPS, FOR PRINTED CIRCUIT BOARDS			
		0 P.L.C 1 P.L.C 2 P.L.C 3 P.L.C 4 P.L.C		+ + + + + -					