

3



MATERIAL: BODY - MOUNTING BRACKETS, COVER & INTERNAL PANEL - 14 GA. STEEL LATCHES - 14 GA. STAINLESS STEEL LATCH BRACKETS - 14 GA. STAINLESS STEEL CONTINUOUS HINGE - 18 GA. STEEL WITH Ø .125 STEEL PIN GASKET - ROGERS CORPORATION PDORN 4701-41-15250 3M 9832 CLOSED CELL URETHANE FOAM WITH ADHESIVE ON ONE SIDE. SCREWS - STAINLESS STEEL

FINISH:

ENCLOSURE, INTERNAL PANEL - SMOOTH GRAY POWDERCOAT DUPONT PLYMER COATINGS PART NO. PFH-502-S8 OR EQUIVALENT UL TYPE D10V2. COATING TO BE APPLIED AND BAKED AT 8-10 MIN. AT 400°F. TO A MINIMUM DRY FILM THICKNESS OF 1.5 MILS (.0015 IN.) LATCHES & SCREWS - NATURAL

DIMENSIONS ARE INCH(MM)

PARTS LIST			
TOLERANCE UNLESS OTHERWISE SPECIFIED +/- .039" (1mm)	CAD GENERATED DRAWING. DO NOT MANUALLY UPDATE		BUD INDUSTRIES INC.
	APPROVALS DRAWN DP	DATE 1-3-06	
MATERIAL AS NOTED	CHECKED	NEMA SHEET METAL BOX	
FINISH AS NOTED	APPROVED	CONTING NO JL	SN-3700
DO NOT SCALE DRAWING		SCALE JL	CAD FILE: SHEET 1 OF 6 REV G

FINISH:
ENCLOSURE, INTERNAL PANEL - SMOOTH GRAY POWDERCOAT
DUPONT POWDER COATINGS PART NO. PFH-502-S8 OR EQUIVALENT
UL TYPE DTDV2, COATING TO BE APPLIED AND BAKED AT 8-10 MIN.
AT 400°F. TO A MINIMUM DRY FILM THICKNESS OF 1.5 MILS (0.0015 IN.)
LATCHES & SCREWS - NATURAL

DIMENSIONS ARE INCH[MM]

PARTS LIST									
TOLERANCE		C&D GENERATED DRAWING. DO NOT MANUALLY UPDATE		BUD INDUSTRIES INC.					
UNLESS OTHERWISE SPECIFIED ✓✓ .039" [1mm]		APPROVALS	DATE	NEMA SHEET METAL BOX					
MATERIAL		DRAWN							
		DP	1-3-06						
		DESIGNED							
FINISH		APPROVED		SHEET NO.		SN-3700		REV.	0
DO NOT SCALE DRAWING				SCALE		PLAN FILE#		SHEET 1 OF	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF BUD INDUSTRIES, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF BUD INDUSTRIES, INC. IS PROHIBITED.

DWG NO	SN-3700
ISSUE	REVISIONS
	SEE SHEET 1

