


B



Tactile Switches


B

**PTS645S Model**


PTS645V Model

Technical drawings of the 1000 Series 1/2" tool bit. The top view shows a square tool bit with a central circular hole and four corner holes. Dimensions include a central hole diameter of 0.7 TYP. (.028), a corner hole diameter of 1.8 (.071), a distance from the center to the corner hole of 6.5 (.256), and a distance from the center to the outer edge of 7.9 (.311). The side view shows the tool bit's profile with a height of 4.5 (.177) and a distance from the center to the outer edge of 3.5 (.138).


PCB LAYOUT




PCB LAYOUT



PCB LAYOUT



Technical drawing of the 1000 Series 1/2" component. The drawing shows a side view and a top view. The side view indicates a total height of 3.6 (0.142) and a top flange diameter of $\varnothing 3.5$ (0.138). The top view shows a square base with a side length of 9.0 (0.354). The top view also shows a central circular feature with a diameter of 6.0 S.Q. (0.236).



Dimensions are shown: mm (inches)
Specifications and dimensions subject to change

PTS645 Series 6 mm Tact Switches

ACTUATION FORCE




OPTION CODE	FORCE
L	130 grams
M	160 grams
H	200 grams
K	260 grams

ACTUATOR HEIGHT




OPTION CODE	HEIGHT "H" or LENGTH "L"	TERMINATION	SCHEMATIC	
			Without EMC pin	With EMC pin
43	4,3 (.169)	Thru-hole and SMT		
50	5,0 (.197)	Thru-hole and SMT		
70	7,0 (.275)	Thru-hole		
95	9,5 (.374)	Thru-hole		
31	3,15 (.124)	Vertical		
39	3,85 (.151)	Vertical		
58	5,85 (.230)	Vertical		
83	8,35 (.329)	Vertical		
15	15,85 (.624)	Vertical		


43




50




70




95




31




39




58



83



15



First Angle
Projection

