



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .429"
2. CONTACT PIN TO SOLDER

REV.	DATE	ECR NO.	DESCRIPTION
A	12/29/00	-	REVISE PLATING TO SILVER
B	07/30/06	-	REVISE PLATING TO NEXCOTE, UPDATE DRAWING FORMAT
C	07/27/08	-	REVISE MATING FACE TO 32 HEX NUT, FERRULE I.D.
D	04/13/09	-	COLOR OF GASKET IS UPDATED TO RED

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8						DRAWN	GRS	07/27/08						
7						CHECKED								
6	FERRULE	COPPER	NEXCOTE	1			ISSUED				PART DESCRIPTION 7/16 R/A CRIMP PLUG (FOR RG-8/U, 213/U, LMR400 CABLE)			
5	COVER	BRASS	NEXCOTE	1			SHEET	1 OF 1						
4	GASKET	SILICONE	RED	1							PART NO. 272115			
3	CONTACT PIN	BRASS	SILVER	1										
2	INSULATOR	PTFE	NATURAL	1							DWG. NO. 272113.DWG REV. D SIZE A SCALE NA			
1	BODY	BRASS	NEXCOTE	1										
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE C:/272/272113.DWG							