






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FX	00		C	REVISED PER ECO-15-003682	12MAR2015	DD	WW




POINT A


SECTION A-A



RECOMENDED CRIMP DIMENSIONS							
GRIP CODE	WIRE SIZE (AWG)	CCW (CONDUCTOR CRIMP WIDTH) TOL ±0.10	CCH (CONDUCTOR CRIMP HEIGHT) TOL ±0.05	ICW (INSULATION CRIMP WIDTH, THIN WALL) TOL ±0.10	ICH (INSULATION CRIMP HEIGHT, THIN WALL) TOL ±0.10	ICW (INSULATION CRIMP WIDTH, STD WALL) TOL ±0.10	ICH (INSULATION CRIMP HEIGHT, STD WALL) TOL ±0.10
18	20	2.05	1.20	2.40	2.00	2.80	2.40
	18	2.05	1.30	2.40	2.10	2.80	2.50
14	16	2.45	1.35	3.20	2.55	3.40	2.70
	14	2.45	1.50	3.20	2.90	3.40	3.05
13.1	16+18	3.05	1.8	5.69			
	16+20	3.05	1.70	5.69			
	18+18	3.05	1.70	5.69			
	18+20	3.05	1.65	5.69			
	20+20	3.05	1.50	5.69			




SECTION X-X




SECTION Y-Y

MATERIAL: UNS C26000 BRASS
FINISH: HOT TIN DIP (PRE TINNED STRIP)



STANDARD REELING DIRECTION

TERMINALS ARE TO BE REELED WITH THE CRIMP GRIPS UP AND TO THE NEAR SIDE. UNWIND DIRECTION FROM RIGHT TO LEFT



REWOUND REELING DIRECTION

TERMINALS ARE TO BE REELED WITH THE CRIMP GRIPS UP AND TO THE NEAR SIDE. UNWIND DIRECTION FROM LEFT TO RIGHT

1438244-8	1438244-7	14	3.80 [.150]	4.70 [.185]	0.66 [.026]	3.98 [.157]	7.52 [.296]	18.80 [.74]	2.00 [.079]
1438244-6	1438244-2	18	3.00 [.118]	3.80 [.150]	0.40 [.015]	3.75 [.148]	7.65 [.301]	18.80 [.74]	2.00 [.079]
-	1438244-1	13.1	3.50 [.140]	5.10 [.201]	1.50 [.059]	3.50 [.138]	7.75 [.305]	19.05 [.75]	1.75 [.069]
TE P/N REWOUND	TE P/N	GRIP CODE	A REF	B REF	L	M	N	T	W

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR BUSSARD 12 JUNE 2003	TE Connectivity	
DIMENSIONS: mm		CHK DM REVAK 12 JUNE 2003		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DM REVAK 12 JUNE 2003	NAME	
0 PLC ± -		PRODUCT SPEC	WIRE SNAP-ON TERMINAL - FEMALE	
1 PLC ± -		APPLICATION SPEC		
2 PLC ± 0.10		WEIGHT -	SIZE A2	CAGE CODE 00779
3 PLC ± REF		CUSTOMER DRAWING	DRAWING NO C=1438244	RESTRICTED TO -
4 PLC ± -			SCALE 4:1	SHEET 1 OF 1
ANGLES ± 3°				REV C
FINISH SEE NOTES				