




Bemerkungen:
NOTES

1 Geeignet für UMNL Stift- und Buchsenkontakte
BEEN SUITABLE FOR UMNL PIN- AND SOCKET CONTACTS

2 Empfohlene Blechstärke 0.75 - 2.3 mm
RECOMMEND SHEET METAL THICKNESS 0.75 - 2.3 mm

3 Gehäuse muß in Stanzrichtung eingeführt werden
HOUSING MUST BE INTRODUCED TO PUNCHING DIRECTION

4 Für verschlüsseltes Einsetzen der Gehäuse
FOR CODED USING OF THE HOUSING

5 Position von Kammer 1 bei Verschlüsseltem Einsetzen
POSITION OF CAVITY 1 FOR CODED USING

6 Neues Material (Phosphor und Halogen frei)
NEW MATERIAL (PHOSPHORUS AND HALOGENEOUS FREE)

7 Hersteller-Logo und Ländercode nach AMP-SPEZ. 115-18016
BRANDNAME AND MANUFACTURING LOCATION CODE ACCORDING AMP-SPEC. 115-18016

926682-6	C	PA6.6 UL94 V 2 (ZYTEL E 103 HSL)	natur/NATURAL
926682-5	C	PA6.6 UL94 V 2 (ZYTEL ...135F)	natur/NATURAL
926682-4	C	PA6.6 UL94 V 2 (ZYTEL ...135F)	weiß/WHITE
926682-3	C	PA6.6 UL94 V 0 (ULTRAMID C3U)	6 natur/NATURAL
926682-2	C	PA6.6 UL94 V 2 (ZYTEL ...135F)	schwarz/BLACK
926682-1	C	PA6.6 UL94 V 2 (ZYTEL E 101)	natur/NATURAL
PART NO	REV.	MATERIAL	COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIESSES ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT. ÄNDERUNGEN, DIE DEN TECHNISCHEN FORTSCHRITT DIENTEN, SIND VORBEHALTEN. DEN JENEMIS LETZTBESTEHENDEN ÄNDERUNGSSTAND BEFOLGEN SIE AUF ANFRAGE.		DWN Abraham, G. 11-MAR-03	tyco Electronics AMP GmbH	
DIMENSIONEN: mm		CHK Kampmann, H. 12-MAR-03	D - 64625 Bensheim	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 8015		APVD -	NAME	
1. DEC ± 0.2 mm		PRODUCT SPEC 108-1031	6-pol. UMNL Aufnahmegehäuse	
2. DEC ± 0.2 mm		APPLICATION SPEC 114-18011	UMNL 6-WAY CAP HOUSING	
3. DEC ± 0.2 mm		WEIGHT -	SIZE A2	CAGE CODE 00779
ANGLES/WINKEL ±		CUSTOMER DRAWING /KUNDENZEICHNUNG	DRAWING NO. 926682	RESTRICTED TO NUR FUER -
FINISH/OBERFLÄCHE/FARBE		MASSSTAB 5:1	BLATT 1 OF 1	REV C2