


QUAD OPERATIONAL AMPLIFIER


■ GENERAL DESCRIPTION

NJM2745 is the quad operational amplifier for the audio use.
Designed low noise, high gain-bandwidth, and low distortion,
the NJM2745 is suitable for audio applications and active filters.


■ PACKAGE OUTLINE



NJM2745D



NJM2745M



NJM2745E
(U.D.)




NJM2745V

■ FEATURES

- Operating Voltage ($\pm 2V$ to $\pm 7V$)
- Low Input Noise Voltage ($5nV/\sqrt{Hz}$ @ $1kHz$ typ.)
- Wide Gain Bandwidth Product ($15MHz$ typ.)
- Low Distortion (0.005% typ. @ $A_v=20dB, V_o=1V_{rms}, R_L=2k\Omega, f=1kHz$)
- Slew Rate ($5V/\mu s$ typ.)
- Package Outline DIP14, EMP14, SSOP14, DMP14
- Bipolar Technology


■ PIN CONFIGURATION



PIN ASSIGNMENT

1. A OUTPUT
2. A -INPUT
3. A +INPUT
4. V^+
5. B +INPUT
6. B -INPUT
7. B OUTPUT
8. C OUTPUT
9. C -INPUT
10. C +INPUT
11. V^-
12. D +INPUT
13. D -INPUT
14. D OUTPUT

■ EQUIVALENT CIRCUIT (1/4 Shown)



■ ABSOLUTE MAXIMUM RATINGS

(Ta=25°C)

PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	V^+ / V^-	± 7.5	V
Common mode Input Voltage	V_{IC}	± 7.5 (note 1)	V
Differential Input Voltage	V_{ID}	± 15 (note 1)	V
Power Dissipation	P_D	870(DIP14) 930(EMP14) (note 2) 700(DMP14) (note 2) 570(SSOP14) (note 2)	mW
Output Current	I_O	± 50	mA
Operating Temperature Range	T_{opr}	-40~+85	°C
Storage Temperature Range	T_{stg}	-40~+125	°C

(note 1)For supply voltages less than ± 7.5 V, the absolute maximum input voltage is equal to the supply voltage.

(note 2)Mounted on the EIA/JEDEC standard board (76.2 × 114.3 × 1.6mm, two layer FR-4).

■ RECOMMENDED OPERATING CONDITION

(Ta=25°C)

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT
Supply Voltage	V^+ / V^-	± 2	-	± 7	V

■ DC CHARACTERISTICS

(Ta=25°C, $V^+ / V^- = \pm 4.5$ V)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Operating Current	I_{CC}		-	12	18	mA
Input Offset Voltage	V_{IO}	$R_S \leq 10k\Omega$	-	0.3	3	mV
Input Bias Current	I_B		-	100	500	nA
Input Offset Current	I_{IO}		-	5	200	nA
Large Signal Voltage Gain	A_V	$R_L \geq 2k\Omega, V_O = \pm 1.5V$	90	110	-	dB
Common Mode Rejection Ratio	CMR	$R_S \leq 10k\Omega, -2.5V \leq V_{IC} \leq +2.5V$	70	110	-	dB
Supply Voltage Rejection Ratio	SVR	$R_S \leq 10k\Omega, V^+ / V^- = \pm 2V$ to $\pm 7V$	80	110	-	dB
Output Voltage Swing	V_{OM}	$R_L \geq 2k\Omega$	± 2.5	± 3	-	V
Input Common Mode Voltage Range	V_{ICM}	CMR ≥ 70 dB	-2.5	-	+2.5	V

■ AC CHARACTERISTICS

(Ta=25°C, $V^+ / V^- = \pm 4.5$ V)







PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Gain Bandwidth Product	GB	$f = 10kHz$	-	15	-	MHz
Total Harmonic Distortion	THD	$A_V = 20dB, V_O = 1V_{rms}, R_L = 2k\Omega, f = 1kHz$	-	0.005	-	%
Input Noise Voltage	V_{NI}	$R_S = 0\Omega$	-	5	-	nV/ $\sqrt{Hz}$

■ TRANSIENT CHARACTERISTICS







(Ta=25°C, $V^+ / V^- = \pm 4.5$ V)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Slew Rate	SR	$R_L \geq 2k\Omega$	-	5	-	V/ μs






■ TYPICAL CHARACTERISTICS









■ TYPICAL CHARACTERISTICS



■ TYPICAL CHARACTERISTICS



■ TYPICAL CHARACTERISTICS



■ NOTE

[CAUTION]

The specifications on this databook are only given for information , without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right including the industrial rights.